



Arteor™ Advance External DND/MUR for Hotel

Cat. No(s): AA27103MW/MB/MT - AA27108MW/MB/MT/CH/DB/RS
AC27103MW/MB/MT - AC27108MW/MB/MT/CH/DB/RS



AA27103MW/MB/MT
AA27108MW/MB/MT/CH/DB/RS



AC27103MW/MB/MT
AC27108MW/MB/MT/CH/DB/RS


1. USE

Hotel bedroom control units.
Enable the resident to inform hotel staff of the room status. Two settings are possible: "Do not disturb" or "Make up room".
Supplied with M3.5 screws for Flush mounting or surface mounting BS.

2. RANGE

Description	Type	Matt White	Matt Black	Matt Titanium	Champagne	Dark Bronze	Rose
DND/MUR PUSH LED 12V CORRIDOR	1-gang	AA27103MW	AA27103MB	AA27103MT			
DND/MUR/BELL PUSH W/ LED 230V	1-gang	AA27108MW	AA27108MB	AA27108MT	AA27108CH	AA27108DB	AA27108RS
DND/MUR PUSH LED 12V CORRIDOR	1-gang	AC27103MW	AC27103MB	AC27103MT			
DND/MUR/BELL PUSH W/ LED 230V	1-gang	AC27108MW	AC27108MB	AC27108MT	AC27108CH	AC27108DB	AC27108RS

3. DIMENSIONS (mm)



References	A	B	C	D
AA27103MW/MB/MT AA27108MW/MB/MT/CH/DB/RS AC27103MW/MB/MT AC27108MW/MB/MT/CH/DB/RS	45	45	40.2	31.7

4. CONNECTION

Types of terminals: with screws
Terminal capacity: 3x1 mm²
2x1.5 mm²
1x4 mm²
Stripping length: 8 mm

5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

Impact test: IK04
Protection against solids & liquids: IP20

■ 5.2 Material characteristics

Plate/Rocker: PC
Frame: PC
Base cover: PC
Self-extinguishing:
+ 850° C / 30 s for insulating parts holding live parts in place
+ 650° C / 30 s for other parts made of insulating materials

■ 5.3 Electrical characteristics

AA27108, AC27108

Voltage: 100-240V~
Current: 3A(Incandescent lamp),1A(Door bell)
Frequency: 50/60HZ

AA27103, AC27103

Voltage: 12V~

■ 5.4 Climatic characteristics

Usage temperature: -5°C to +35°C
Storage temperature: -10°C to +70°C

6. CARE

Clean the surface with a cloth.
Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Resistant to the following products: Hexane, methylated spirit, soapy water, diluted ammonia, bleach diluted to 10%, window-cleaning products, pre-impregnated wipes.

Caution: Always test before using special cleaning products.

7. STANDARDS AND APPROVALS

Compliant with installation and manufacturing standards, see e-catalogue.