


## Niloé™ STEP

### Socket outlets - German Standard

Cat. No(s): 3 982 08 - 3 982 09 - 3 982 10 - 8 631 22 - 8 633 22 - 8 635 22 - 8 641 64 - 8 643 64 - 8 645 64 - 8 646 64




#### 1. USE

Socket outlets with shutters.  
Mechanisms supplied with protection cover.  
To be equipped with plates one or several gangs.  
Flush-mounting.  
Screw or claw fixing.

#### 2. RANGE

Description	White	Aluminium	Black	Sand
2x2 P+E socket shutters automatic terminal	3 982 08, 8 631 22, 8 641 64	3 982 09, 8 633 22, 8 643 63	3 982 10, 8 635 22, 8 645 64	8 646 64

#### 3. DIMENSIONS (mm)



#### 4. CONNECTION

Terminal capacity: 2 x 2.5 mm<sup>2</sup>  
Type of terminals: automatic terminal  
Stripping length: 13mm  
Flexible or rigid cables compatible

#### 5. TECHNICAL CHARACTERISTICS

##### ■ 5.1 Mechanical characteristics

Protection against solid bodies and liquids: IP 20  
Protection against impact: IK 04

##### ■ 5.2 Material characteristics

Mat appearance  
Mechanism housing: PC  
Cover plate: PC  
UV-resistant  
Claws: steel  
Support: PC

Self-extinguishing:  
850°C/30 s for insulating components holding live parts in place  
650°C/30 s for other insulating components

##### ■ 5.3 Electrical characteristics

Voltage: 250 V~  
Current: 16 A  
Frequency: 50/60 Hz

##### ■ 5.4 Climate characteristics

Storage temperature: - 10° C to +70° C  
Usage temperature: - 5° C to + 40° C

## 6. MAINTENANCE

Surface cleaning with a cloth.

Do not use: acetone, tar remover, trichloroethylene.

Maintenance with the following products:

Hexane, methylated spirit, soapy water, diluted ammonia, pure bleach diluted to 10%, window-cleaning products.

**Caution:** Always test before using other special cleaning products

## 7. STANDARDS AND APPROVALS

The undersigned, LEGRAND, declares that the radio-electric equipment type (Cat. Nos 3 982 08 - 3 982 09 - 3 982 10 - 8 631 22 - 8 633 22 - 8 635 22 - 8 641 64 - 8 643 64 - 8 645 64 - 8 646 64) complies with directive 2014/53/EU.

The full text of the EU declaration of conformity is available on the following website: [www.legrand.com/ecatalogue](http://www.legrand.com/ecatalogue)