

P31 - DERIVATION UNIVERSELLE
P31 - UNIVERSAL BRANCH

 Reference(s) : **481173/2273/5173**
 Items(s) : **341174/3174/5174**


60 mm


1. GAMME/RANGE
P31-DERIVATION UNIVERSELLE H60 GS
P31-UNIVERSAL BRANCH H60 PG

Designation Description	Code	Poids Weight (Kg)	Épaisseur Thickness (mm)	Matière Raw Material	Norme matière Standard Raw Material	Finition Coating	Norme Finition Standard Coating
P31 - DERIVATION UNIVERSELLE H60 GS P31 - UNIVERSAL BRANCH H60 PG	481173	0,15	0,7	DX51D + Z200	EN 10346	GS/PG/Z	EN 10346
P31 - COUV. DERIVATION UNIVERSELLE H60 GS P31 - UNIVERSAL BRANCH COVER H60 PG	341174	0,05	0,7	DX51D + Z200	EN 10346	GS/PG/Z	EN 10346

 Classe de résistance contre la corrosion 3 (IEC 61537)
 Corrosion resistance classification 3 (IEC 61537)

P31-DERIVATION UNIVERSELLE H60 GC
P31-UNIVERSAL BRANCH H60 HDG

Designation Description	Code	Poids Weight (Kg)	Épaisseur Thickness (mm)	Matière Raw Material	Norme matière Standard Raw Material	Finition Coating	Norme Finition Standard Coating
P31 - DERIVATION UNIVERSELLE H60 GC P31 - UNIVERSAL BRANCH H60 HDG	482273	0,17	0,7	DC01	EN 10130	GC/HDG/C	ISO 1461
P31 - COUV. DERIVATION UNIVERSELLE H60 GC P31 - UNIVERSAL BRANCH COVER H60 HDG	343174	0,06	0,7	DC01	EN 10130	GC/HDG/C	ISO 1461

 Classe de résistance contre la corrosion 6 (IEC 61537)
 Corrosion resistance classification 6 (IEC 61537)

P31-DERIVATION UNIVERSELLE H60 RAL
P31-UNIVERSAL BRANCH H60 RAL

Designation Description	Code	Poids Weight (Kg)	Épaisseur Thickness (mm)	Matière Raw Material	Norme matière Standard Raw Material	Finition Coating	Norme Finition Standard Coating
P31 - DERIVATION UNIVERSELLE H60 RAL9010 P31 - UNIVERSAL BRANCH H60 RAL9010	485173	0,15	0,7	DX51D + Z200	EN 10346	RAL 9010	
P31 - COUV. DERIVATION UNIVERSELLE H60 RAL9010 P31 - UNIVERSAL BRANCH COVER H60 RAL9010	345174	0,05	0,7	DX51D + Z200	EN 10346	RAL 9010	

 Classe de résistance contre la corrosion 3 (IEC 61537)
 Corrosion resistance classification 3 (IEC 61537)

P31 - DERIVATION UNIVERSELLE
P31 - UNIVERSAL BRANCH

Reference(s) : **481173/2273/5173**
Items(s) : **341174/3174/5174**

2. DIMENSIONS (mm)

