



Arteor™


• Switch without contact - 2 ways

• 接近式感应开关

5720 51 - 5725 51 - 5734 55 - 5736 55







	 White / 白色	 Magnesium / 镁白色	 White / 白色	 Magnesium / 镁白色
	5720 51	5734 55	5725 51	5736 55

									
100 - 240 Vac 50/60 Hz	1 x 2,5 mm ² 2 x 1,5 mm ²								
240 Vac		1000 W	1000 W	500 VA	500 VA	500 VA	500 VA	100 VA	1 max. < 2 A
100 Vac		500 W	500 W	250 VA	250 VA	250 VA	250 VA	50 VA	1 max. < 1 A

(*) • Use only transformers which are intended for use with an electronic switch. /

• 只有那些使用电子开关的地方才使用变 压器





- Functions only in combination with touch-sensitive controls (5 maximum in parallel).
- 只与触摸式微动控制器组合的功能（最多可以并联五个）

• Caution :

When installed in combination these products must be protected by the same protection circuit.

• 特别注意:

在组合安装的时候，这些产品必须通过同一保护回路进行保护。

⚠ Safety instructions

This product should be installed in line with installation rules, preferably by a qualified electrician. Incorrect installation and use can lead to risk of electric shock or fire.

Before carrying out the installation, read the instructions and take account of the product's specific mounting location.

Do not open up, dismantle, alter or modify the device except where specifically required to do so by the instructions. All Legrand products must be opened and repaired exclusively by personnel trained and approved by Legrand. Any unauthorised opening or repair completely cancels all liabilities and the rights to replacement and guarantees. Use only Legrand brand accessories.

GB I E

⚠ 安全提示




本产品的安装要满足规范的要求，最好由持证电工完成，不正确的安装和使用会有触电或火灾的风险。



在安装前，请仔细阅读本手册的内容并充分考虑产品的具体安装位置。除非本手册有特别要求，切勿打开、拆卸、改动本装置。

所有罗格朗的产品必须由专门受过培训并得到罗格朗批准的专人打开和修理。任何擅自打开或修理，本公司概不负责更换和质量保证。


只能使用罗格朗的附件。



CH

				
مغنيزيوم	أبيض	مغنيزيوم	أبيض	
5720 51	5734 55	5725 51	5736 55	

										
										°35 م °0 م
1 كحد أقصى > 2 أمبير	100 فولط أمبير	500 واط	1000 واط	240 فولط 2,5 × 1 مم ² 1,5 × 2 مم ²	240-100 فولط 50/60 هرتز					
1 كحد أقصى > 1 أمبير	50 فولط أمبير	250 فولط أمبير	250 فولط أمبير	250 فولط أمبير	250 فولط أمبير	250 فولط أمبير	500 واط	500 واط	240 فولط	100 فولط


(*) لا تستخدم سوى محولات مخصصة للاستخدام مع مفتاح إلكتروني.





لا يعمل إلا مع أدوات تحكم لمسية (5 كحد أقصى على التوازي)

تحذير:
عند تركيبه مع هذه المنتجات تجب حمايته بدارة الحماية نفسها.



إرشادات الأمان:



يجب تركيب هذا المنتج طبقاً لقواعد التركيب ويفضل أن يقوم بالتركيب كهربائي مؤهل. فقد يؤدي التركيب والاستخدام غير الصحيح إلى مخاطر التعرض لصدمة كهربائية أو نشوب حريق. اقرأ النشرة قبل التركيب، وأقرأ مكدناً لتركيب المنتج خاصاً به. لا تفتح أو تعطل أو تحوّر المنتج ما لم يُشر إلى ذلك بشكل محدد في النشرة. فكل منتجات Legrand يجب فتحها وإصلاحها حصراً من قبل فنيين مدربين ومؤهلين لدى Legrand. وكل فتح أو إصلاح غير مسموح به يبطل المسؤولية وحقوق الاستبدال والضمانات. لا تستخدم سوى إكسسوارات من علامة Legrand حصراً.