


Requires prior installation of a connected starter pack "... with Netatmo".

Control Modul




OR


Gateway




Leave home/back home
general control



Contents:



OR



BS13 connected socket outlet
1-gang

BS13 connected socket outlet
2-gang

Frequency bands: 2.4 - 2.4835 GHz
Power level: < 100 mW

 **Safety instructions**


This product should be installed in compliance with installation rules, preferably by a qualified electrician. Incorrect installation and/or incorrect use can lead to risk of electric shock or fire.

Before carrying out the installation, read the instructions and take account of the product's specific mounting location.


Do not open up, dismantle, alter or modify the device except where specifically required to do so by the instructions. All Legrand products must be opened and repaired exclusively by personnel trained and approved by Legrand. Any unauthorised opening or repair completely cancels all liabilities and the rights to replacement and guarantees. Use only Legrand brand accessories.

Before you start


To control a power outlet, only use the following products:



AND



AND
/
OR



BS13 connected socket outlet 1-gang or 2-gang

Wireless switches 1-gang or 2-gang (peripherals) for all control points (not included in this pack)




Do not use: a connected switch (with dimmer option) to control a connected socket outlet or a traditional socket outlet.

If you are replacing socket outlet controlled by a switch:

Tip if replacing a switched power outlet:

old flush-mounted switch replaced by the wireless control.

Use a **connector** to connect the two wires.



The circuit must be protected by a 16 A circuit breaker.

① Necessary safety precautions

1



OFF



Switch OFF the power at the main circuit breaker


2




Make sure that the power is OFF before continuing with the installation.

② Install the connected socket outlet



1



3



② Wire the connected socket outlet



— N (neutral) = blue

— L (live) = any except blue and green/yellow

— ⊕ (earth) = green/yellow



2.5 mm² rigid wire recommended

Frequency bands: 2.4 - 2.4835 GHz

Power level: < 100 mW

**13 A - 240 V~
3120 W max.**

③ **To add a connected product to your connected installation, you should follow the instructions:**

- in the **Legrand Home + Control application** (Settings/Add a new product section)
- or consult the user manual on **legrand.fr**



www.legrand.fr/reference/574257

LEGRAND - Pro and Consumer Service - BP 30076
87002 LIMOGES CEDEX FRANCE • www.legrand.com

SIMPLIFIED EU DECLARATION OF CONFORMITY

The undersigned,

Legrand


declares that the radio-electric equipment referred to in these instructions
complies with directive 2014/53/UE.

The full text of the EU declaration of conformity is available on the following website:


www.legrandoc.com

يتطلب التركيب المسبق لحزمة بدء متصلة "مع Netatmo".


عناصر التحكم العامة لمغادرة المنزل/العودة إلى المنزل



بوابة




وحدة تحكم




أو

المحتويات:



أو



مخرج مقبس متصل BS13 - مجموعة واحدة

مخرج مقبس متصل BS13 - مجموعتان

نطاقات التردد: 2.4 - 2.4835 جيجا هرتز


مستوى الطاقة: > 100 ميغا واط

إرشادات الأمان:

يجب تركيب هذا المنتج طبقاً لقواعد التركيب ويفضل أن يقوم بالتركيب كهربائي مؤهل. فقد يؤدي التركيب الخاطئ و/أو الاستخدام الخاطئ إلى مخاطر التعرض لصدمة كهربائية أو نشوب حريق. اقرأ النشرة قبل التركيب، وأفرد مكاناً لتركيب المنتج خاصاً به. لا تفتح أو تفك أو تعطل أو تحوّل المنتج ما لم يُشر إلى ذلك بشكل محدد في النشرة. فكل منتجات Legrand يجب فتحها وإصلاحها حصراً من قبل فنيين مدربين ومؤهلين لدى Legrand. وكل فتح أو إصلاح غير مسموح به يُبطل المسؤوليات وحقوق الاستبدال والضمانات. لا تستخدم سوى إكسسوارات من ماركة Legrand حصراً.


قبل البدء

للتحكم في مخرج الطاقة، لا تستخدم إلا المنتجات التالية:




واحد
أو مجموعة

9
/ أو



واحد
أو مجموعة

9



واحد

مفاتيح لاسلكية - مجموعة واحدة أو مجموعتان
(طرفية) لجميع نقاط التحكم (غير مضمنة في هذه الحزمة)

مخرج مقبس متصل BS13 -
مجموعة واحدة أو مجموعتان



لا تستخدم: مفتاحاً متصلاً (مع خيار آلية ضبط شدة الإضاءة) للتحكم في مخرج مقبس متصل أو مخرج مقبس تقليدي.



إذا كنت تقوم باستبدال مخرج مقبس يتم التحكم فيه بمفتاح:

تلميح: في حالة استبدال مخرج طاقة يعمل بمفتاح:
يتم استبدال المفتاح القديم المركب بشكل مستوي على السطح
بواسطة وحدة التحكم اللاسلكية.

استخدم موصلًا
لتوصيل السلكين.



يجب حماية الدائرة بواسطة قاطع دائرة 16 أمبير.



1 احتياطات السلامة الضرورية

1 تأكد من إيقاف تشغيل الطاقة قبل متابعة التركيب.





2 قم بإيقاف تشغيل الطاقة عند قاطع الدائرة الرئيسي





إيقاف التشغيل

2 قم بتركيب مخرج المقبس المتصل



2 قم بتوصيل أسلاك مخرج المقبس المتصل



يوصى باستخدام سلك قوي بسمك 2.5 مم²

N (محايد) = أزرق
L (موصل بالكهرباء) = أي سلك باستثناء الأزرق والأخضر/الأصفر
⊥ (الأرضي) = الأخضر/الأصفر

13 أمبير - 240 فولت ~
3120 واط كحد أقصى

نطاقات التردد: 2.4 - 2.4835 جيجا هرتز
مستوى الطاقة: > 100 ميغا واط

③ لإضافة منتج متصل إلى التركيب المتصل لديك، يجب اتباع الإرشادات:

- في صفحة **Legrand** الرئيسية + تطبيق التحكم (قسم الإعدادات/إضافة منتج جديد)
- أو مراجعة دليل المستخدم في **legrand.fr**



www.legrand.fr/reference/574257

LEGRAND - خدمة المتخصصين والعملاء - BP 30076
87002 LIMOGES CEDEX FRANCE • www.legrand.com

SIMPLIFIED **EU** DECLARATION OF CONFORMITY

The undersigned,

Legrand

declares that the radio-electric equipment referred to in these instructions
complies with directive 2014/53/UE.

The full text of the EU declaration of conformity is available on the following website:

www.legrandoc.com