



Requires you to buy and install the «... with Netatmo» connected starter pack



Control Modul

Gateway power outlet control and Home/away wireless Master control


Pack contents:



Connected switch with neutral (with dimmer option)




Site protection



Finishing plate

Before starting: wiring precautions

If you plan to install two-way light switches, read the following precautions: To control a light with **two or more switches**, only use the following products:



Connected switch with neutral (with dimmer option)




or several

AND/OR



or several



Wireless switches for all control points (not included in this pack)

up to 20 push buttons (not included in this pack)

or several

Do not use: two connected switches (with dimmer option) to control the same lighting point.

Characteristics


In default operating mode (on/off), this switch works with the following bulbs :

+ 45° C			LED	CIEW	\$\langle \bar{\textsq}{\textsq}
100-240 VAC 50/60 Hz	2 x 2,5 mm²	.‡-	⊒ ZI⊗	⊒ ZI⊗	⊒ Z⊗
240 VAC	Maxi.	150 W	^(*) 150 W	150 W	150 W
100 VAC	Maxi.	75 W	^(*) 75 W	75 W	75 W


(*) For a good lighting comfort, it is recommended to use bulbs of the same type and the same manufacturer.

In dimmer option operating mode (which can be activated via the App), this switch functions only with dimmable bulbs (identifiable by the logo on packaging).





old flush-mounted switch replaced by the wireless switch.



Use a connector to connect all 3 wires together (travellers 1 and 2 and lamp return wire). Use an other connector for neutral wire.

2








Switch off the power at the main circuit breaker



is off before continuing with the installation.


(2) Make sure that the power is off before continuing with the installation.



Remove the old switch



Mire the connected switch




Frequency bands: 2.4 - 2.4835 GHz

N (neutral) = blue

Power level: < 100 mW

L (live) = any except blue and green/yellow (earth) = green/yellow



Attention, the dimmer must be installed on the lamp side



The connected light switch (with dimmer option) works with standard bulbs or dimmable bulbs including LEDs. Using dimmable LEDs is mandatory if dimmer mode is activated.



3

- 3 To add a connected product to your connected installation, you should follow the instructions:
- in the **Home + Control application** (Settings/Add a new product section)
- or consult the user manual on legrand.fr



LEGRAND - Pro and Consumer Service - BP 30076 87002 LIMOGES CEDEX FRANCE • www.legrand.com

Asfety instructions

This product should be installed in compliance with installation rules, preferably by a qualified electrician. Incorrect installation and/or incorrect use can lead to risk of electric shock or fire. Before carrying out the installation, read the instructions and take account of the product's specific mounting location.

Do not open up, dismantle, after or modify the device except where specifically required to do so by the instructions. All Legrand products must be opened and repaired exclusively by personnel trained and approved by Legrand. Any unauthorised opening or repair completely cancels all liabilities and the rights to replacement and guarantees. Use only Legrand brand accessories.

SIMPLIFIED **EU** DECLARATION OF CONFORMITY

The undersigned,

Legrand

declares that the radio-electric equipment referred to in these instructions complies with directive 2014/53/EU.

The full text of the EU declaration of conformity is available on the following website:

www.legrandoc.com