


This product is a connected accessory which **requires** you to buy and install the Arteor with Netatmo connected starter pack first.

Pack contents

Connected switch for rolling shutters 2 gang



Characteristics

+35°C +5°C	8 mm	Rolling shutter motor
110-240 VAC 50/60 Hz	1.5...4mm ²	1 x 250 VA
240 VAC max.		1 x 75 VA
110 VAC max.		

⚠ Safety instructions


This product should be installed in compliance with installation rules, preferably by a qualified electrician. Incorrect installation and/or incorrect use can lead to risk of electric shock or fire. Before carrying out the installation, read the instructions and take account of the products specific mounting location.

Do not open up, dismantle, alter or modify the device except where specifically required to do so by the instructions. All Legrand products must be opened and repaired exclusively by personnel trained and approved by Legrand. Any unauthorised opening or repair completely cancels all liabilities and the rights to replacement and guarantees. Use only Legrand brand accessories.

Before you start


If you plan to install switches for rolling shutters, read the following precautions:

To control a rolling shutter switch with one or more wireless controls, only use the products:



x 1

Connected switch for rolling shutters



or several

Wireless controls for rolling shutters (not included in this pack)

Ensure you have wireless controls for rolling shutters for each additional control point.

To create a centralized control:

- Use one or more connected switches for rolling shutters.
- Use a wireless control for rolling shutters.

① Necessary safety precautions

1



Switch OFF the power at the main circuit breaker

OFF

2




Make sure that the power is OFF before continuing with the installation.


② Install the connected switch for rolling shutters

1


Remove the existing switch



3



② Wire the connected switch for rolling shutters



- N (neutral) = blue
- L (live) = any except blue and green/yellow
- ⚡ (earth) = green/yellow

Frequency bands:
2.4 - 2.4835 GHz
Power level: < 100 mW

The Arteor with Netatmo solution is compatible with rolling shutters with a mechanical or electronic stop, controlled by a standard wired switch for rolling shutters. They are not compatible with motors directly controlled by radio control. To check it, refer to the rolling shutter instructions.

③ To add a connected product to your connected installation, you should follow the instructions:

- in the **user guide in your connected starter pack**
- in the **Legrand Home + Control application (Settings/Add a new product section)**
- or consult the user manual on **legrand.com**



www.legrand.com/reference/574633

LEGRAND - Pro and Consumer Service - BP 30076
87002 LIMOGES CEDEX FRANCE • www.legrand.com

SIMPLIFIED EU DECLARATION OF CONFORMITY

The undersigned,

Legrand

declares that the radio-electric equipment referred to in these instructions complies with directive 2014/53/EU.


The full text of the EU declaration of conformity is available on the following website:

www.legrandoc.com

هذا المنتج هو جهاز متصل يتطلب منك أولاً شراء وتركيب علبة المنتجات الأساسية المتصلة ماركة Arteor with Netatmo

محتويات العلبة

مفتاح متصل خاص
بالستائر اللفافة طقم 2



مواصفات المنتج

+35°C +5°C	8 mm	Rolling shutter motor
110-240 VAC 50/60 Hz	1.5...4mm ²	1 x 250 VA
240 VAC max.		1 x 75VA
110 VAC max.		


إرشادات الأمان:

يجب تركيب هذا المنتج طبقاً لقواعد التركيب ويفضل أن يقوم بالتركيب كهربائي مؤهل. فقد يؤدي التركيب الخاطئ و/أو الاستخدام الخاطئ إلى مخاطر التعرض لصدمة كهربائية أو نشوب حريق. اقرأ النشرة قبل التركيب، وأقرأ مكاناً لتركيب المنتج خاصة به. لا تفتح أو تفك أو تعطل أو تحوّر المنتج ما لم يُشر إلى ذلك بشكل محدد في النشرة. فكل منتجات Legrand يجب فتحها وإصلاحها حصراً من قبل فنيين مدربين ومؤهلين لدى Legrand. وكل فتح أو إصلاح غير مسموح به يُبطل المسؤوليات وحقوق الاستبدال والضمانات. لا تُستخدم سوى إكسسوارات من ماركة Legrand حصراً.

LE13225AA

5

2 قم بتوصيل أسلاك المفتاح المتصل الخاص بالستائر اللفافة



نطاقات التردد: 2.4 - 2.4835 جيجاهرتز
مستوى القدرة: > 100 ملي واط
م (محايد) = أزرق
ك خط كهربائي = أي واحد فيما عدا الأزرق والأخضر/الأسفر
⊕ (أرضي) = أخضر/أسفر


يتميز حل Arteor Netatmo with بالتوافق مع الستائر اللفافة ذات إيقاف ميكانيكي أو إلكتروني التي يتم التحكم فيها بواسطة مفتاح سلبي عادي للستائر اللفافة. وهو غير متوافق مع المواتير التي يتم التحكم فيها مباشرة بواسطة جهاز تحكم السلبي. للتحقق من التوافق، راجع الإرشادات الخاصة بالستارة اللفافة.

7

قبل بدء العمل


إذا كنت تنوي تركيب مفاتيح للستائر اللفافة، فافقراً الاحتياطات التالية:

للتحكم في مفاتيح الستائر اللفافة بواسطة وحدة تحكم السلبي واحدة أو أكثر، ال تستخدم سوى المنتجات التالية:



x 1

AND



أو أكثر

وحدات التحكم اللاسلكية الخاصة بالستائر اللفافة (ليست موجودة في هذه العلبة)

مفتاح متصل الخاص بالستائر اللفافة


تأكد من وجود وحدات تحكم السلبي للستائر اللفافة لكل موضع تحكم إضافي. لتوفير تحكم مركزي:

- استخدم واحداً أو أكثر من المفاتيح المتصلة الخاصة بالستائر اللفافة.
- استخدم وحدة تحكم السلبي للستائر اللفافة


1 احتياطات السلامة الضرورية



1 أفضل التيار الكهربائي من القاطع الرئيسي للدائرة الكهربائية



2 تأكد من فصل التيار الكهربائي قبل متابعة خطوات عملية التركيب




1

قم بإزالة المفتاح الموجود

2 تركيب المفتاح المتصل الخاص بالستائر اللفافة

3



6

3 لإضافة منتج متصل إلى المنتجات المتصلة المركبة لديك، يجب اتباع الإرشادات:

في دليل المستخدم في علبة المنتجات الأساسية المتصلة الموجودة في التطبيق Control + Home الخاص بشركة Legrand (القسم الإعدادات/إضافة منتج - أو راجع دليل المستخدم المتوفر على legrand.com

- in the user guide in your connected starter pack
- in the Legrand Home + Control application (Settings/Add a new product section)
- or consult the user manual on legrand.com



www.legrand.com/reference/574633

LEGRAND - Pro and Consumer Service - BP 30076
87002 LIMOGES CEDEX FRANCE • www.legrand.com

SIMPLIFIED EU DECLARATION OF CONFORMITY

The undersigned,

Legrand

declares that the radio-electric equipment referred to in these instructions complies with directive 2014/53/EU.

The full text of the EU declaration of conformity

is available on the following website:

www.legrandoc.com

8