


## Connected power outlet

8 636 20 - 8 637 20 - 8 638 20 - 8 639 20



This pack is a connected accessory which requires you to buy and install the Céliane with Netatmo connected starter pack first.

### Pack contents



Connected power outlet


### Safety instructions

This product should be installed in compliance with installation rules, preferably by a qualified electrician. Incorrect installation and/or incorrect use can lead to risk of electric shock or fire. Before carrying out the installation, read the instructions and take account of the product's specific mounting location. Do not open up, dismantle, alter or modify the device except where specifically required to do so by the instructions. All **Legrand** products must be opened and repaired exclusively by personnel trained and approved by **Legrand**. Any unauthorised opening or repair completely cancels all liabilities and the rights to replacement and guarantees. Use only **Legrand** brand accessories.

LET3859AA

## Before you start: wiring precautions


To control a power outlet, only use the products:



x 1

Connected power outlet

AND



x 1  
or several


Wireless switches for all control points (not included in this pack)



**Do not use:** a connected switch (with dimmer option) to control a connected power outlet or a traditional power outlet.

### If you are replacing a power outlet controlled by a switch:

**Tip if you are replacing an old flush-mounted switch (replaced with a wireless switch)**




Use a **connector** to connect the two wires.



The head protection must be 16 A

## 1 Necessary safety precautions

1



**OFF**

Switch off the power at the main circuit breaker


2



**Make sure that the power is off before continuing with the installation.**


## 2 Install the connected power outlet

1



Remove the existing power outlet

3




2

Wire the connected power outlet

2.5 mm<sup>2</sup> rigid wire recommended

**16 A - 230 V ~ 3680 W**  
**maxi cos 0,8**

Frequency bands: 2.4 - 2.4835 GHz Power level: < 100 mW



— N (neutral) = blue  
— L (live) = any except blue and green/yellow  
— ⊕ (earth) = green/yellow

## 3 To add a connected product to your connected installation, you should follow the instructions:

- in the **Legrand Home + Control** application (Settings/Add a new product section)
- or consult the user manual on **legrand.com**



[www.legrand.com](http://www.legrand.com)

LEGRAND - Pro and Consumer Service - BP 30076 87002 LIMOGES CEDEX FRANCE •  
[www.legrand.com](http://www.legrand.com)

## SIMPLIFIED EU DECLARATION OF CONFORMITY

The undersigned,

**Legrand**

declares that the radio-electric equipment referred to in these instructions complies with directive 2014/53/EU.

The full text of the EU declaration of conformity is available on the following website :

**[www.legrandoc.com](http://www.legrandoc.com)**