



Requires to install the connected starter pack and one or more «... with Netatmo» connected switch, micromodule or socket outlet.





Pack contents:

Wireless, batteryless lighting control

Stickers x2





Frequency bands: 2.4 - 2.4835 GHz
 Power level: < 20 mW




1 Start the configuration

Press the configuration button of gateways until its light briefly turns green, and then stop pressing. All wired products lights will turn green.




2 Pair the wireless, batteryless switch to control the connected products (switch, micromodule, socket-outlet, latching relay).

Make sure that the indicator lights on the wired products are green and not flashing. If not, go back to precedent step. 1.



- A** Tap 3 times the product to be controlled with the wireless, batteryless control. The light of the product to control flashes rapidly.
- B** While holding the "setup" button on the wireless, batteryless control, briefly press the "ON" or "OFF" button on the wireless batteryless control.
- C** The indicator light of the product to control will briefly turn blue, and then will turn green again. The pairing was successful.

Multiple pairing: You can control several switches with the same wireless, batteryless switch by repeating the operation for each product that you want to control.




www.legrand.com/ecatalogue
 LEGRAND - Pro and Consumer Service - BP 30076
 87002 LIMOGES CEDEX FRANCE - www.legrand.com

The undersigned, Legrand declares that the radio-electric equipment type (AA5206MT - AC5206MT - AA5206MB - AC5206MB - AA5206MW - AC5206MW) complies with directive 2014/53/EU. The full text of the EU declaration of conformity is available on the following website: www.legrand.com/ecatalogue

Download the app
 Your installation is ready. You can download the **Legrand Home + Control** application to control your lights remotely.




3 Complete the installation



To complete your installation, **briefly** press the configuration button of the gateways. **All the indicator lights on the products switch off**

If necessary, erase the configuration of the wireless batteryless control (factory reset)



While holding the "setup" button on the wireless, batteryless control, press the upper button for 5 seconds. **Confirm that your control is correctly reset by making an ON command, then OFF**

FCC ID: 2ACN8-ZLGP1X IC: 12132A-ZLGP1X Model: ZLGP17

This device contains licence-exempt transmitter(s)/receiver(s) that comply with FCC RF and Innovation, Science and Economic Development Canada's licence-exempt RSS(s). Operation is subject to the following two conditions: (1) this device may not cause interference, and (2) this device must accept any interference, including interference that may cause undesired operation of the device. This device complies with FCC and ISED radiation exposure limits set forth for general population. This device must not be co-located or operating in conjunction with any other antenna or transmitter. FCC Caution: the user that changes or modifications not expressly approved by the party responsible for compliance could void the user's authority to operate the equipment.



FCC NOTE: This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instruction, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception which can be determined by turning the equipment off and on, the user is encouraged to try to correct interference by one or more of the following measures:
 - Reorient or relocate the receiving antenna.
 - Increase the separation between the equipment and receiver.
 - Connect the equipment into an outlet on circuit different from that to which the receiver is connected.
 - Consult the dealer or an experienced radio/TV technician for help.

Safety instructions
 Make sure the power supply is disconnected before any intervention. Strictly comply with instructions for installation and use.



① بدء التكوين


اضغط على زر التكوين بالمنفذ حتى يتحول المصباح الموجود على الزر إلى اللون الأخضر لفترة وجيزة ثم توقف عن الضغط. تتحول كل مصابيح المنتجات الموصلة إلى اللون الأخضر.



② إقران المفتاح اللاسلكي بدون بطارية للتحكم في المنتجات الموصلة (المفتاح، أو الوحدة الصغيرة، أو المقبس، أو المرحلة ذو الدائر ة القابلة).

تأكد أن المصابيح المؤشرة بالمنتجات الموصلة مضاءة باللون الأخضر وغير وامضة. إذا لم تكن كذلك، فعد إلى الخطوة السابقة ①.

2



يمكنك أيضًا تثبيت مفاتيح التحكم اللاسلكية في الحائط باستخدام براغي.

www.legrand.com/ecatalogue
BP 30076 - LEGRAND - خدمة المتخصصين والمستهلكين -
www.legrand.com + FRANCE CEDEX LIMOGES 87002

تعلن شركة Legrand أن نوع الجهاز اللاسلكي الكهربائي (AA5206MW - AC5206MW - AA5206MT - AC5206MT - AA5206MB - AC5206MB) متوافق مع التوجيه 2014/53/EU.
النص الكامل لإعلان المطابقة الخاص بالاتحاد الأوروبي متوفر على موقع الويب التالي:
www.legrand.com/ecatalogue

قم بتنزيل التطبيق
التركيب الخاص بك جاهز. يمكنك تنزيل تطبيق Legrand Home + Control للتحكم في أنظمة الإضاءة لديك عن بُعد.

FCC ID: 2ACN8-ZLGP1X IC: 12132A-ZLGP1X Model: ZLGP17

This device contains licence-exempt transmitter(s)/receiver(s) that comply with FCC RF and Innovation, Science and Economic Development Canada's licence-exempt RSS(s). Operation is subject to the following two conditions: (1) this device may not cause interference, and (2) this device must accept any interference, including interference that may cause undesired operation of the device.
This device complies with FCC and ICSE radiation exposure limits set forth for general population. This device must not be co-located or operating in conjunction with any other antenna or transmitter.
FCC Caution: the user that changes or modifications not expressly approved by the party responsible for compliance could void the user's authority to operate the equipment.


FCC NOTE: This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instruction, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception which can be determined by turning the equipment off and on, the user is encouraged to try to correct interference by one or more of the following measures:
- Reorient or relocate the receiving antenna.
- Increase the separation between the equipment and receiver.
- Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.
- Consult the dealer or an experienced radio/TV technician for help.

إرشادات السلامة
تأكد من فصل مصدر إمداد التيار قبل أي إجراء.
التركيب باستخدام إرشادات التركيب والاستخدام.


green power
certified by connectivity standards alliance
Model: ZLGP17

4

يستلزم تركيب مجموعة بادئ التشغيل الموصلة ومفتاح موصل من طراز "with Netatmo...", أو وحدة صغيرة، أو مقبس واحد أو أكثر.



محتويات العبوة :




ضغط قصيرة -- ON/OFF
ضغط طويلة -- < رفع 25%
ضغطتان قصيرتان -- OFF




ضغط قصيرة ON/OFF
ضغط طويلة -- < تخفيض 25%
ضغطتان قصيرتان -- OFF

نطاقات التردد: 2.4 - 2.4835 جيجاهرتز
مستوى الطاقة: < 20 ملي واط



LE15142AA-AR



أ) اضغط 3 مرات على المنتج المراد التحكم فيه باستخدام مفتاح التحكم اللاسلكي بدون بطارية. يومض مصباح المنتج المراد التحكم فيه وميضًا سريعًا.


ب) أثناء الضغط مع الاستمرار على زر "الإعداد" بمفتاح التحكم اللاسلكي بدون بطارية، اضغط لفترة وجيزة على زر "ON" أو "OFF" بمفتاح التحكم اللاسلكي بدون بطارية.

ج) يتحول المصباح المؤشر بالمنتج المراد التحكم فيه إلى اللون الأزرق لفترة وجيزة ثم إلى اللون الأخضر مجددًا. يعني ذلك إتمام عملية الإقران بنجاح.

تحقق من صحة عملية الإقران بواسطة الضغط على زر ON/OFF


الإقران المتعدد: يمكنك التحكم في مفاتيح متعددة باستخدام نفس المفتاح اللاسلكي بدون بطارية وذلك عن طريق تكرار العملية لكل منتج تريد التحكم فيه.

③ إكمال التركيب



لإكمال عملية التركيب، اضغط لفترة وجيزة على زر التكوين بالمنفذ. تنطفئ كل المصابيح المؤشرة بالمنتجات

مسح تكوين مفتاح التحكم اللاسلكي بدون بطارية (إعادة الضبط على إعدادات المصنع) عند الضرورة



أثناء الضغَط مع الاستمرار على زر "الإعداد" بمفتاح التحكم اللاسلكي بدون بطارية، اضغط على الزر العلوي لمدة 5 ثوان. تأكد من إعادة ضبط مفتاح التحكم لديك بشكل صحيح عن طريق إصدار أمر ON ثم أمر OFF

3