Part Number: M30040



ALPIMATIC - Automatic power factor correction



Alpimatic capacitor bank, standard type, is an automatic PFC system, with electromechanical contactors to switch on or off each step. Contactors are controlled by ALPTEC power factor controller. M30040 is made of Alpimatic standard type rack.

Contents	Page
1. Technical data	1
2. Description	1
3. Additional equipment	1
4. Installation instructions	1

1. Technical data

ALPIMATIC Range: Type: Standard Nominal power: 300 kVAr

Steps: $(25 + 50) + 3 \times 75 \text{ kVAr}$ 400 V - 50 Hz - Tri Nominal voltage: Max permissible voltage: 470 V (capacitor) Insulation class: 6 / 25 kV (capacitor) Harmonic level: THDU < 2% & THDI < 5%

> SH/ST ≤ 15% 2 W/kVAr

Loss factor: -10℃ / +45℃ Temperature class:

> Average over 24H: +40 ℃ Annual average : +35°C

Weight: 200 kg

Dimensions (W x D x H mm): 600 x 500 x 1400

Type: Indoor -30℃ / +60℃ Storage:

Environment: Drv

Dust-free Non-corrosive Vibration-free IEC 61439-1 and 2

2. Description

Standard:

This automatic capacitor bank includes:

5 Steps made of:

- 1 ALPIVAR3 capacitor:
 - Totally dry unit (without oil impregnation)
 - Double insulation or class II
 - Internal electrical protection by self-healing film, electrical fuse and disconnection device in case of overpressure
 - With discharge resistors (discharging time 3 minutes)
 - Complies with international standard (IEC 60831-1 & 2)
- 1 electromechanical contactor suitable for capacitive currents, with pre-insertion resistive contacts to limit inrush current. (coil 400 Vac).
- 1 protection by 3 HRC fuses, gG type. (common base fuse for the steps (25+50) kVAr).

1 digital Power Factor controller – Alptec5.2:

- LCD backlight display
- Optical communication port
- Switching by electromechanical relays
- Displays: $\cos \varphi$, U, I, temperature, $\Delta kVAr$...
- Displays alarms: under compensation, over compensation, low current, high current, low voltage ...
- Disconnection on current overload and over temperature
- 1 single-phase power supply for auxiliary circuits.
- 1 three-phase power connection (copper busbar 30 x 5 mm with M10 screw).
- 1 NC dry contact to disconnect the capacitor bank when operation with GenSet (to be wired on site).
- 1 cubicle in which are mounted and wired the above components:
 - IP 31-IK 05
 - Power cable entry from the bottom of the cabinet (from the top on request)
 - Ventilation louvers on the front, sides and rear
 - RAL 7035 grey, black base (height = 100 mm)

3. Additional equipment

The capacitor bank must be protected against overloads and short circuits with a thermal-magnetic circuit breaker 630 A, set at 600 A.

Power connecting cables with minimum cross section of 2 x 95 mm² Cu/phase.

1 CT (Current Transformer) to be located on phase L1 of the general installation, primary current to be defined / secondary 5 A, Class 1-10 VA (Supply on request).

4. Installation instructions

External environment for the cubicle:

- Dry and dust free
- Non-corrosive atmosphere
- Maximum temperature: +40 ℃
- Average over 24 hours: +35℃
- Annual average: +25°C

A minimum clearance distance of 200 mm must be respected against any obstacle (wall, distribution board) to insure good ventilation.

For more details on the commissioning and maintenance, refer to installation instructions.

Technical data sheet: M30040 Updated: 11/07/2014 Created: 01/12/2011