

DPX³ 250 thermal magnetic

MCCBs from 100 to 250 A



4 202 05



4 202 25

Electrical characteristics **see e-catalogue**
Dimensions **see e-catalogue**

Can be mounted on rail or on plate in XL³ cabinets and enclosures
MCCBs for switching, control isolation and protection of low voltage electrical lines
Supplied with fixing screws, connection plates for bars and cable lugs and insulated shileds (phase barriers)
Can be fitted with cage terminals 120 mm² max. (flexible cable) or 150 mm² max. rigid cable (p. 141)
and with DPX³ 160 and 250 common auxiliaires and accessories (p. 142)
Conform to IEC 60947-2

Pack	Cat.Nos		MCCBs - fixed version Thermal adjustable from 0,8 to 1 In Magnetic adjustable from 5 to 10 In Breaking capacity Icu 25 kA (400 V\sim) In (A)
	3P	4P	
1	4 202 05	4 202 15	100
1	4 202 07	4 202 17	160
1	4 202 08	4 202 18	200
1	4 202 09	4 202 19	250
Breaking capacity Icu 36 kA (400 V\sim)			
1	4 202 35	4 202 45	100
1	4 202 37	4 202 47	160
1	4 202 38	4 202 48	200
1	4 202 39	4 202 49	250
Breaking capacity Icu 50 kA (400 V\sim)			
1	4 202 65	4 202 75	100
1	4 202 67	4 202 77	160
1	4 202 68	4 202 78	200
1	4 202 69	4 202 79	250

Pack	Cat.Nos	MCCBs with electronic earth leakage module - fixed version Thermal adjustable from 0,8 to 1 In Magnetic adjustable from 5 to 10 In Equipped with earth leakage module with LCD screen Adjustable sensitivity: 0.03 - 0.3 - 1 - 3 A Adjustable tripping: 0 - 0.3 - 1 - 3s (with 0.03 A possible only 0s) Breaking capacity Icu 25 kA (400 V\sim) In (A)
	4P	
1	4 202 25	100
1	4 202 27	160
1	4 202 28	200
1	4 202 29	250
Breaking capacity Icu 36 kA (400 V\sim)		
1	4 202 55	100
1	4 202 57	160
1	4 202 58	200
1	4 202 59	250
Breaking capacity Icu 50 kA (400 V\sim)		
1	4 202 85	100
1	4 202 87	160
1	4 202 88	200
1	4 202 89	250

