

Auxiliaries, accessories and fixing devices for DMX³ 1600



0 281 39




0 281 23



0 281 78



0 281 81



0 281 75

Pack	Cat.Nos	Control and signalling auxiliaries
		Shunt trip When energised the circuit breaker will be tripped
1	0 281 31	24 V~/=
1	0 281 32	48 V~/=
1	0 281 33	110 - 130 V~/=
1	0 281 34	220 - 250 V~/=
1	0 281 35	415 - 440 V~
		Undervoltage releases When the coil is de-energised, the circuit breaker will be tripped
1	0 281 36	24 V~/=
1	0 281 37	48 V~/=
1	0 281 38	110 - 130 V~/=
1	0 281 39	220 - 250 V~/=
1	0 281 40	415 - 440 V~
		Module for delayed tripping To be used with above undervoltage releases
1	0 288 62	110 V~/=
1	0 288 63	230 V~/=
		Motor operators To motorize a DMX ³ , it is possible to attach, to the motor operators, a release coil (undervoltage or trip on energising) and a closing coil
1	0 281 20	24 V~/=
1	0 281 21	48 V~/=
1	0 281 22	110 - 130 V~/=
1	0 281 23	220 - 250 V~/=
1	0 281 24	415 - 440 V~
		Closing coils Enables remote closing of the circuit breaker if the closing spring is charged
1	0 281 26	24 V~/=
1	0 281 27	48 V~/=
1	0 281 28	110 - 130 V~/=
1	0 281 29	220 - 250 V~/=
1	0 281 30	415 - 440 V~
		Signalling contact for draw-out version Inserted / test / draw-out signalling contact 1 changeover contact per position (up to 2 contacts with double accessory if the safety button for test position cat no. 0 281 87 is not mounted)
1	0 281 73	

Pack	Cat.Nos	Locking
		Key locking in «open» position
1	0 281 78	1 lock + 1 Ronis type flat key (n° ABA90GEL6149) random
1	0 281 79	1 lock + 1 Ronis type flat key (n° ABA90GEL6149) fixed (cod. EL43525)
1	0 281 80	1 lock + 1 Ronis type flat key (n° ABA90GEL6149) fixed (cod. EL43363)
1	0 281 81	1 lock + 1 Profalux type star key (n° HBA90GPS6149) random
		Key locking in the draw-out position Mounting of the lock on the base
1	0 281 82	1 lock with star type key (n° HBA90GPS6149) random
1	0 281 83	1 lock with flat type key (n° ABA90GEL6149) random

Pack	Cat.Nos	Locking (continued)
		Door locking Prevents opening of the door with the circuit breaker closed Left-hand and right-hand side mounting
1	0 281 84	
		Padlock Padlock for buttons
1	0 281 77	
		Accessories
1	0 281 88	Mechanical counter Counts total number of operation cycles of the device
1	0 281 74	Contact «ready to close» with charged springs
1	0 281 75	Module with 6 auxiliary contacts
1	0 281 87	Inserted /test /draw-out lock button
1	0 281 89	Rating mis-insertion device Prevents the insertion of a draw-out circuit breaker in an incompatible base
		Front terminals
		For frontal connection For DMX ³ Frame 1600 fixed version
1	3P 0 281 55 4P 0 281 56	
		N
1	0 281 57 0 281 58	For DMX ³ Frame 1600 draw-out version
		Spreaders for DMX³ Frame 1600 fixed and draw-out versions
		To be fixed onto orientable rear terminals of the circuit breaker
		For connection with bars (horizontal use)
		3P 0 281 59 4P 0 281 60
		Insulation shields
		For fixed version For DMX ³ /DMX ³ -I Frame 1600
1	3P 0 281 49 4P 0 281 50	
		For draw-out version For DMX ³ /DMX ³ -I Frame 1600
1	0 281 51 0 281 52	