


Blade type cartridge fuses

HRC blade type cartridge fuses

gG/gL and aM types



Conform to IEC 60269-2

Pack	Cat.Nos		Bases for blade type cartridge fuses				
			Self-extinguishing plastic bases Contact points are sprung				
			Bare				
		1P 3P	Size	In (A)	Mounting	Connection	
3 1	0 199 42	0 199 43 ¹	000/00	100	screw or	M8	
3 1	0 199 44	0 199 45 ¹	000/00	160	└ rail	M8	
	1P						
3	0 199 46		0	160	screw or	M8	
3	0 199 48		1	250	└ rail	M10	
3	0 199 50		2	400	└ rail	M10	
			With micro-switch				
			Equipped with "present cartridge" and "blown fuse" indicator for cartridge fuses with stricker				
	1P						
3	0 199 47		0	160	screw or	M8	
1	0 199 49		1	250	└ rail	M10	
1	0 199 51		2	400	└ rail	M10	

Pack	Cat.Nos	Handle
5	0 199 02	For all sizes

Pack	Cat.Nos	Accessories			
		Separation dividers and joining accessories kits			
		Base Size	Number of dividers	Number of joining accessories	For base Cat.No
5	0 199 30 ²	000/00	2	0	0 199 42/44
5	0 199 31	0	2	2	0 199 46/47
5	0 199 32	1/2	2	2	0 199 48/49 /50/51

Pack	Cat.Nos	Protection kits
		For protection against accidental contacts, Kits consisting of : separation dividers, joining accessories, terminal shields and fuse covers
	1P	
5	0 199 35 ²	For bases size 00 Cat.No 0 199 42/44
5	0 199 36	For bases size 0 Cat.No 0 199 46
5	0 199 37	For bases size 1 Cat.No 0 199 48
5	0 199 38	For bases size 2 Cat.No 0 199 50
	3P	
5	0 199 39 ²	For bases size 00 Cat.No 0 199 43/45

1: Supplied with 2 separation dividers
2: Supplied without joining accessories (separation dividers are fixed directly on the base of)

Pack	Cat.Nos	Type gG / gL		
		Conform to IEC 60269-2 For protection against accidental contacts, use terminal shields and fuse covers supplied with protection kits		
		Size 00		
		Rating (Amps)	Voltage ~ (Volts)	Breaking capacity (Amps)
10	0 163 18	25	500	120000
10	0 163 20	32		
10	0 163 22	35		
10	0 163 25	40		
10	0 163 30	50		
10	0 163 35	63		
10	0 163 40	80		
10	0 163 45	100		
10	0 163 50	125		
10	0 163 55	160		
		Size 0		
3	0 168 35	63	500	120000
3	0 168 40	80		
3	0 168 45	100		
3	0 168 50	125		
3	0 168 55	160		
		Size 1		
3	0 173 50	125	500	120000
3	0 173 55	160		
3	0 173 60	200		
3	0 173 65	250		
		Size 2		
3	0 178 60	200	500	120000
3	0 178 65	250		
3	0 178 70	315		
3	0 178 75	400		

Pack	Cat.Nos	Type aM (motor rated)		
		Conform to EN 60269-1 IEC 60269-1, 2 and VDE 0636-1 Fully insulated end plate and handle lugs		
		Size 00		
		Rating (Amps)	Voltage ~ (Volts)	Breaking capacity (Amps)
3	0 160 35	63	500	120000
3	0 160 40	80		
3	0 160 45	100		
3	0 160 50	125		
3	0 160 55	160		
		Size 0		
3	0 166 35	63	500	120000
3	0 166 40	80		
3	0 166 45	100		
3	0 166 50	125		
3	0 166 55	160		
3	0 166 55	160		
		Size 1		
3	0 171 50	125	500	120000
3	0 171 55	160		
3	0 171 60	200		
3	0 171 65	250		
3	0 171 65	250		
		Size 2		
3	0 176 60	200	500	120000
3	0 176 65	250		
3	0 176 70	315		
3	0 176 75	400		
3	0 176 75	400		

For technical data and dimensions, see e-catalogue

