

Distribution enclosures XL³ 6300



0 211 37

Assembly consisting of:
 - Roof-base Cat.No 0 211 35
 - Structural uprights Cat.No 0 211 36
 - Functional uprights Cat.No 0 211 37
 - Rear panel Cat.No 0 211 41
 - Support frame for faceplates Cat.No 0 208 55
 - Lifting rings Cat.No 0 205 82



0 208 00



0 211 40




0 211 39

IP 30 - IK 07

Consist of the combination of a "roof-base" assembly, structural uprights, rear and side panels RAL 7035, plinths RAL 7004
 Height 2200 mm, usable faceplate height 2000 mm

Pack	Cat.Nos	Enclosures modular metal	
1	0 211 36	Structural uprights Fit onto the "roof-base" assembly Take the side and rear panels Set of 4 uprights	
		"Roof-base" for enclosure Fitted with cable entry plates Take the structural uprights	
		Depth (mm)	Width (mm)
			external usable
1	0 211 33	475	1425 1300
1	0 211 34	725	1425 1300
1	0 211 35	975	1425 1300
		Side panels Fixed with screws	
1	0 208 57	Width 475 mm	
1	0 208 58	Width 725 mm	
1	0 208 59	Width 975 mm	
		Rear panel Fixed with screws	
1	0 211 41	Width 1300 mm (supplied in two parts)	
		Finishing panels IP 30 1300 x 2000 mm	
1	0 211 48		
		Plinths that can be placed side by side	
		Height (mm)	Depth (mm) Width (mm)
1	0 211 30	100	475 1425
1	0 211 31	100	725 1425
1	0 211 32	100	975 1425
		Equipment	
		Functional uprights For fixing mounting equipment (faceplate, rails...)	
1	0 211 37	Set of 2 functional uprights	
		Support frame for faceplates Fixed for enclosure width 725 mm or enclosure width 975 mm	
1	0 208 55		
		Isolating supports for busbars 6300 A Supports for 3 bars 200 x 10 mm (per phase)	
1	0 373 12	Fixed support	
1	0 373 13	Additional support	
		Mounted in addition to fixed support Cat.No 0 373 12 to comply with the distances (depending on the Isc)	

Pack	Cat.Nos	Mounting equipment	
		Joining	
1	0 205 86	Screws for structural joining	
1	0 205 88	Set of 2 L-shaped reinforcement plates	
1	0 205 89	Set of 2 flat reinforcement plates	
		Lifting rings	
1	0 205 82	Set of 4 Max. load: 480 kg per ring	
		Fixing modular devices on rail	
		Rail Comprising: an aluminium profile rail and two 2-position fixing brackets Fit onto functional uprights	
1	0 211 42	For fixing on XL ³ 6300 functional uprights 36 modules	
		Metal faceplate for rail equipment Height 200 mm	
1	0 208 00		
		Fixing devices for DMX³ 6300	
		Fixing plates For 1 DMX ³ 6300 3P/4P fixed version For 1 DMX ³ 6300 3P/4P draw-out version	
1	0 211 38		
1	0 211 40		
		Metal faceplate For 1 DMX ³ 6300 3P/4P fixed or draw-out version	
1	0 211 39		
		Metal solid faceplates	
1	0 211 44	Height 200 mm, width 1300 mm	
1	0 211 45	Height 400 mm, width 1300 mm	
		Forms of separation equipment	
1	0 211 46	DMX ³ 6300 compartment kit (form 4b)	
1	0 211 47	Partitioning for 6300 A busbars	
1	0 211 49	Kit for horizontal separation (up and down)	



Download XL³ 4000/6300
 Workshop specifications on
www.docexport.legrand.com

