

Valena™ IN'MATIC mechanisms

dimmers



7 520 60 + 7 548 80 + 7 540 01
(Valena Life - White)



7 520 62 + 7 548 92 + 7 541 31
(Valena Life - Aluminium)



7 520 67 + 7 520 87 + 7 543 91
(Valena Allure - Aluminium)



0 401 49

Valena In'Matic mechanisms are supplied with metal support, for claw or screw mounting
To be equipped with Valena Life or Valena Allure cover plates and plates
Supplied with mounted dust protection transparent shield. Packaged in boxes

Pack	Cat.Nos	Dimmers 240 V~ - 50 Hz
1	7 520 60	<p>Equipped with overvoltage and short-circuit protection. When switched on, light up at the level set before last switch-off Can be remotely controlled via non-illuminated push-buttons (Cat.No 7 520 11), with each push-button able to perform the ON/OFF and dimming function Screw terminals</p> <p>Rotary dimmer without neutral For all types of lamps: - dimmable LEDs: 5 W to 75 W (10 lamps max.) - dimmable compact fluorescent lamps: 5 W to 75 W (10 lamps max.) - halogen with ferromagnetic or electronic transformer: 5 VA to 300 VA - fluorescent tube - ballast: 5 VA to 300 VA - halogen and incandescent 240 V~: 5W to 300W When switched on, gradually (2 seconds) lights up at the level set before last switch-off</p>
1	7 520 62	<p>Push-dimmer without neutral For all types of lamps: - dimmable LEDs: 5 W to 75 W (10 lamps max.) - dimmable compact fluorescent lamps: 5 W to 75 W (10 lamps max.) - halogen with ferromagnetic or electronic transformer: 3 VA to 400 VA - fluorescent tube - ballast: 3 VA to 200 VA - halogen and incandescent 240 V~: 3W to 400W When switched on, gradually (2 seconds) lights up at the level set before last switch-off Functioning: - dimming mode - pre-set level mode (0%, 33%, 66%, 100%) - nightlight mode: dimming down of the lamp for 1 hour</p>

Pack	Cat.Nos	Dimmers 240 V~ - 50 Hz (continued)
1	7 520 67	<p>Screw terminals Dimmer, with neutral, for 1-10 V ballast For fluorescent lamps with 1-10 V ballast: 600 VA</p>
1	0 401 49	<p>Active Power Compensator Allows 2-wire electronic switches without neutral to be compatible with all loads (LED, fluocompact...)</p>

