

Valena™ Life

data and telephone sockets with cover plate



7 533 48 + 7 541 31
(Aluminium)



7 531 43 + 7 540 71
(Terracotta)

Valena In'Matic mechanisms supplied with cover plates and support frames. To be equipped with plates
Supplied with mounted dust protection transparent shield
Flowpack packaging: robust protection to ensure optimum operation

Pack	Cat.Nos	Data sockets Cat. 6 _A
		With LCS ² connector with fast connection thanks to integrated crimping Take AWG 22 single-core cables up to AWG 26 and AWG multicore cables Contacts marked with dual colour code and wiring schemes 568 A and 568 B Conform to standards ISO/IEC 11801 Ed. 2.0, amendment 2, EN 50173-1 and TIA/EIA 568 C2
		RJ 45 socket Cat. 6_A STP
5	7 531 48	<input type="checkbox"/> White
5	7 532 48	<input type="checkbox"/> Ivory
5	7 533 48	<input type="checkbox"/> Aluminium
		Double RJ45 socket Cat. 6_A STP
5	7 531 49	<input type="checkbox"/> White
5	7 532 49	<input type="checkbox"/> Ivory
5	7 533 49	<input type="checkbox"/> Aluminium
		Data sockets Cat. 6
		With LCS ² connector with fast connection thanks to integrated crimping Take AWG 22 single-core cables up to AWG 26 and AWG multicore cables Contacts marked with dual colour code and wiring schemes 568 A and 568 B Conform to standards ISO/IEC 11801 Ed. 2.0, amendment 2, EN 50173-1 and TIA/EIA 568 C2
		RJ 45 socket Cat. 6 UTP
5	7 531 42	<input type="checkbox"/> White
5	7 532 42	<input type="checkbox"/> Ivory
5	7 533 42	<input type="checkbox"/> Aluminium
		RJ 45 socket Cat. 6 STP
5	7 531 46	<input type="checkbox"/> White
5	7 532 46	<input type="checkbox"/> Ivory
5	7 533 46	<input type="checkbox"/> Aluminium
		Double RJ 45 socket Cat. 6 UTP
5	7 531 43	<input type="checkbox"/> White
5	7 532 43	<input type="checkbox"/> Ivory
5	7 533 43	<input type="checkbox"/> Aluminium
		Double RJ 45 socket Cat. 6 STP
5	7 531 47	<input type="checkbox"/> White
5	7 532 47	<input type="checkbox"/> Ivory
5	7 533 47	<input type="checkbox"/> Aluminium

Pack	Cat.Nos	Data sockets Cat. 5e
		With LCS ² connector with fast connection thanks to integrated crimping Take AWG 22 single-core cables up to AWG 26 and AWG multicore cables Contacts marked with dual colour code and wiring schemes 568 A and 568 B Conform to standards ISO/IEC 11801 Ed. 2.0, amendment 2, EN 50173-1 and TIA/EIA 568 C2
		RJ 45 socket Cat. 5e UTP
5	7 531 40	<input type="checkbox"/> White
5	7 532 40	<input type="checkbox"/> Ivory
5	7 533 40	<input type="checkbox"/> Aluminium
		RJ 45 socket Cat. 5e FTP
5	7 531 53	<input type="checkbox"/> White
5	7 532 53	<input type="checkbox"/> Ivory
5	7 533 53	<input type="checkbox"/> Aluminium
		Double RJ45 socket Cat. 5e UTP
5	7 531 41	<input type="checkbox"/> White
5	7 532 41	<input type="checkbox"/> Ivory
5	7 533 41	<input type="checkbox"/> Aluminium
		Double RJ45 socket Cat. 5e FTP
5	7 531 54	<input type="checkbox"/> White
5	7 532 54	<input type="checkbox"/> Ivory
5	7 533 54	<input type="checkbox"/> Aluminium
		Telephone sockets
		Equipped with a modular Jack connector with 1/4 turn terminal for fast connection. Tap-off possible
		RJ 11 socket
5	7 531 38	<input type="checkbox"/> White
5	7 532 38	<input type="checkbox"/> Ivory
5	7 533 38	<input type="checkbox"/> Aluminium