

## MyHOME\_Up

### BUS Arteor and Valena temperature control



0 674 59 + plate Cube  
5 714 02



7 521 31 + plate Aluminium  
7 541 31



7 527 31 + plate White  
7 543 01

Pack	Cat.Nos	Display thermostats
1	0 674 59	Flush mounting thermostat with backlit display Can be used to control the temperature of an individual zone Features a temperature probe and an input for connecting a contact line (e.g. window contact) Can be used to manage different types of systems, and to adjust the fan speed when fan coils are used Possibility of automatic operation (summer/winter), with compatible systems 2 modules
1	7 521 31	Arteor version To be equipped with support frame and plates (p. 480-487)
1	7 527 31	Valena Life To be equipped with support frame and plates (p. 526)
1	7 527 31	Valena Allure To be equipped with support frame and plates (p. 527)
1	F430/2	<b>DIN rail actuators 100/240 V~ - 50/60 Hz</b> <b>Actuator with 2 independent relays</b> For single and double loads: 6 A resistive, 3 A motorised valves and pumps 2 DIN modules 17.5 mm
1	F430/4	<b>Actuator with 4 independent relays</b> For single, double or mixed loads: 6 A resistive, 3 A motorised valves, pumps and fan-coils 2 DIN modules 17.5 mm
1	F430R8	<b>DIN actuators for the control of ON/OFF valves, motorised valves, pumps and fan coils with 0-10V proportional valves</b> Actuator with 8 independent relays for the control of on-off valves, motorised valves (open-close and three-point valves), pumps and fan coils with 2 and 4 tubes 4 A resistive, 1 A motorised valves, pumps and fan coils 4 DIN modules 17.5 mm
1	F430R3V10	Actuator with 3 independent relays and 2 x 0-10 Volt outputs for the control of fan coils with 2 and 4 tubes with 0-10 Volt proportional valves 4 A resistive, 1 A fan coils 4 DIN modules 17.5 mm
1	F430V10	Actuator with 2 x 0-10 Volt outputs for the control of 0-10 V proportional valves 2 DIN modules 17.5 mm

## MyHOME\_Up

### BUS common accessories



E46ADCN



F425



F422

Load selection charts p. 425

Pack	Cat.Nos	BUS power supplies
1	E46ADCN	<b>27 V<sub>DC</sub> - 1.2 A</b> Maximum consumption: 300 mA Maximum current supplied: 1.2 A 8 DIN modules 17.5 mm Input voltage: 127 V <sub>AC</sub> - output voltage 27 V <sub>DC</sub> Input voltage: 230 V <sub>AC</sub> - output voltage 27 V <sub>DC</sub> Input voltage: 127 V <sub>AC</sub> - output voltage 27 V <sub>DC</sub>
1	E46ADCN/127	
1	E49	<b>27 V<sub>DC</sub> - 0.6 A</b> Maximum current supplied: 0.6 A 2 DIN modules 17.5 mm Input voltage: 230 V <sub>AC</sub> - output voltage 27 V <sub>DC</sub>
1	346020	<b>Additional power supply</b> Provides power for Webserver 2 DIN modules 17.5 mm
1	L4669	<b>BUS/SCS cables</b> Conform to IEC 45-5 and IEC 20-20 Grey Length 100 m
1	L4669/500	Length 500 m
1	L4669KM1	Length 1000 m Supplied on wooden reels
10	3515	<b>BUS spare clamp</b> Used to connect the various system components (controls, dimmers, etc) to the BUS line Male connector
5	7 520 44	<b>In'matic support for Valena Life/Allure mechanisms</b> Accepts 2-module Valena Life/Allure mechanisms Supplied with mounted dust protection transparent shield
1	F425	<b>Additional DIN devices</b> <b>Memory module for actuators</b> Restore the last state of an actuator in case of a power failure 2 DIN modules 17.5 mm
1	F422	<b>SCS-SCS gateway (extension)</b> Allows the extension of the installation or the integration between different functions Suitable for larger installations 2 DIN modules 17.5 mm