

Synergy™

British standard socket outlets - white



Front plates: white thermoset
Terminal screws captive and backed off ready for cabling - large angled terminal entries
Compact mechanism for maximised wiring space
Supplied with faceplate screw caps

Pack	Cat.Nos	Socket outlets 13 A - 250 V~
10	7 300 65	<p>Conform to BS 1363: Part. 2 For flush-mounting, back box to be min. 25 mm deep With safety shutter mechanism ASTA licence </p> <p>Unswitched 1 gang Nominal plate dimensions: 86 x 86 mm</p>
5	7 300 75	<p>2 gang Nominal plate dimensions: 86 x 146 mm</p>
10	7 300 66	<p>Single pole - switched 1 gang Nominal plate dimensions: 86 x 86 mm</p>
5	7 300 76	<p>2 gang Nominal plate dimensions: 86 x 146 mm</p>

Pack	Cat.Nos	Double pole socket outlets 13 A - 250 V~
10	7 300 60	<p>Conform to BS 1363: Part. 2 With safety shutter mechanism For flush-mounting, back box to be min. 25 mm deep ASTA licence </p> <p>Switched 1 gang Nominal plate dimensions: 86 x 86 mm</p>
5	7 300 70	<p>2 gang Nominal plate dimensions: 86 x 146 mm</p>
10	7 300 61	<p>Switched with red LED power indicator LED invisible until activated 1 gang Nominal plate dimensions: 86 x 86 mm</p>
5	7 300 71	<p>2 gang Nominal plate dimensions: 86 x 146 mm</p>

1	7 300 78	<p>Socket outlets 13 A - 250 V~ with USB charger Conform to BS 1363-2 USB charger conform to IEC 60950-1</p> <p>Single pole switched 1 gang USB Type-A 2.4 A - 5 V_{DC} - 12 W Consumption in passive mode < 0.08</p>
1	7 300 79	<p>2 gang USB Type-A + Type-C™ 3 A - 5 V_{DC} - 15 W Consumption in passive mode < 0.08 W</p>

10	7 300 67	<p>Socket outlets 13 A - 250 V~ Special earth pin With safety shutter mechanism For flush-mounting, back box to be min. 25 mm deep</p> <p>Double pole - switched 1 gang Nominal plate dimensions: 86 x 86 mm</p>
5	7 300 77	<p>2 gang Nominal plate dimensions: 86 x 146 mm</p>