



7 300 74















7 300 89




7 300 69

Front plates: white thermoset  
Terminal screws captive and backed off ready for cabling - large angled terminal entries  
Compact mechanism for maximised wiring space  
Supplied with faceplate screw caps

Pack	Cat.Nos	<b>Double pole socket outlets 13 A - 250 V~ (continued)</b>
		Conform to BS 1363: Part. 2 With safety shutter mechanism For flush-mounting, back box to be min. 25 mm deep ASTA licence 
		<b>Switched for standard and clean earth applications</b>
10	7 300 64	 1 gang Nominal plate dimensions: 86 x 86 mm
5	7 300 74	 2 gang Nominal plate dimensions: 86 x 146 mm
		<b>Switched with red rocker</b>
10	7 301 62	 1 gang Nominal plate dimensions: 86 x 86 mm
5	7 301 61	 2 gang Nominal plate dimensions: 86 x 146 mm

Pack	Cat.Nos	<b>Socket outlets 15 A - 250 V~</b>
		Conform to BS 546 Patented 3 pin safety shutter mechanism For flush-mounting, back box to be min. 35 mm deep Nominal plate dimensions: 86 x 86 mm
10	7 300 88	 1 gang - unswitched
10	7 300 89	 1 gang - switched, single pole
		<b>Socket outlets 15 A - 127 V~</b>
		Standard terminal screws For flush-mounting, back box to be min. 35 mm deep
5	7 300 85	 1 gang unswitched Nominal plate dimensions: 86 x 86 mm
5	7 300 86	 2 gang unswitched Nominal plate dimensions: 86 x 146 mm
		<b>Socket outlets 5 A - 250 V~</b>
		Conform to BS 546 Patented 3 pin safety shutter mechanism For flush-mounting, back box to be min. 25 mm deep Nominal plate dimensions: 86 x 86 mm
10	7 300 68	 1 gang - unswitched
10	7 300 69	 1 gang - switched, single pole
		<b>Socket outlet 2 A - 250 V~</b>
		Conform to BS 546 For flush-mounting, back box to be min. 25 mm deep Nominal plate dimensions: 86 x 86 mm
10	7 300 59	 1 gang - unswitched

 British standard multi-outlet extensions, **p. 638**



 BS plugs, **p. 637**

