



8 321 31



8 323 32



8 325 33



8 321 51



8 323 57



8 325 50

Sleek design. BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L
 PSS: Plates made of Stainless Steel + rust resistance. GG: Plates made of Stainless Steel + rust resistance
 Terminal screws captive and backed off ready for cabling - large angled terminal entries. Compact mechanism for maximum wiring space

| Pack | Cat.Nos | Single pole plate switches 10 AX - 250 V~ |
|------|----------|--|
| | | Conform to BS EN 60669-1 For flush-mounting, back box to be min. 35 mm deep Nominal plate dimensions: 86 x 86 mm |
| 1 | 8 320 01 | 1 gang - 2-way switches |
| 1 | 8 322 01 | ● Brushed stainless steel |
| 1 | 8 324 01 | ● Polished stainless steel |
| | | ● Glossy gold |
| 1 | 8 320 02 | 2 gang - 2-way switches |
| 1 | 8 322 02 | ● Brushed stainless steel |
| 1 | 8 324 02 | ● Polished stainless steel |
| | | ● Glossy gold |

| Pack | Cat.Nos | Single pole plate switches 20 AX - 250 V~ |
|------|----------|--|
| | | Conform to BS EN 60669-1 For flush-mounting, back box to be min. 35 mm deep Nominal plate dimensions: 86 x 86 mm |
| 1 | 8 321 31 | 1 gang - 2-way switches |
| 1 | 8 323 31 | ● Brushed stainless steel |
| 1 | 8 325 31 | ● Polished stainless steel |
| | | ● Glossy gold |
| 1 | 8 321 32 | 2 gang - 2-way switches |
| 1 | 8 323 32 | ● Brushed stainless steel |
| 1 | 8 325 32 | ● Polished stainless steel |
| | | ● Glossy gold |
| 1 | 8 321 33 | 3 gang - 2-way switches |
| 1 | 8 323 33 | ● Brushed stainless steel |
| 1 | 8 325 33 | ● Polished stainless steel |
| | | ● Glossy gold |
| 1 | 8 321 34 | 4 gang - 2-way switches |
| 1 | 8 323 34 | ● Brushed stainless steel |
| 1 | 8 325 34 | ● Polished stainless steel |
| | | ● Glossy gold |

| Pack | Cat.Nos | Single pole intermediate 10 AX - 250 V~ |
|------|----------|--|
| | | Conform to BS EN 60669-1 For flush-mounting, back box to be min. 35 mm deep |
| 1 | 8 320 05 | ● Brushed stainless steel |
| 1 | 8 322 05 | ● Polished stainless steel |
| 1 | 8 324 05 | ● Glossy gold |

| Pack | Cat.Nos | Single pole push switches 10 A - 250 V~ |
|------|----------|--|
| | | Conform to BS EN 60669-1 For flush-mounting, back box to be min. 35 mm deep Nominal plate dimensions: 86 x 86 mm |
| 1 | 8 320 07 | 1 gang - 2-way push switches |
| 1 | 8 322 07 | ● Brushed stainless steel |
| 1 | 8 324 07 | ● Polished stainless steel |
| | | ● Glossy gold |

| Pack | Cat.Nos | Push on/off rotary universal dimmers 5 W/300 W 100 - 240 V~ - 50/60 Hz |
|------|----------|--|
| | | 1 gang - 2-way push switches Conform to IEC 60669-2-1 For flush-mounting back box to be min. 40 mm deep Equipped with overvoltage and short-circuit protection Screw terminals For all types of lamps: - dimmable LEDs: 5 W to 75 W - dimmable compact fluorescent lamps: 5 W to 75 W - halogen with ferromagnetic or electronic transformer: 5 VA to 300 VA - fluorescent tube - ballast: 5 VA to 300 VA - halogen and incandescent 230 V: 5 W to 300 W When switched on, gradually (2 seconds) lights up at the level set before last switch-off Nominal plate dimensions: 86 x 86 mm |
| 1 | 8 321 51 | ● Brushed stainless steel |
| 1 | 8 323 51 | ● Polished stainless steel |
| 1 | 8 325 51 | ● Glossy gold |
| 1 | 0 401 49 | Active Power Compensator Allows 2-wire electronic switches without neutral to be compatible with all loads (LED, fluocompact...) |
| | | |

| Pack | Cat.Nos | Push on/off rotary dimmers 400 W 100 - 240 V~ - 50/60 Hz |
|------|----------|--|
| | | Conform to BS EN 60669-1 For flush-mounting, back box to be min. 35 mm deep Nominal plate dimensions: 86 x 86 mm |
| 1 | 8 321 56 | 1 gang - 2 way |
| 1 | 8 323 56 | ● Brushed stainless steel |
| 1 | 8 325 56 | ● Polished stainless steel |
| | | ● Glossy gold |
| 1 | 8 321 57 | 2 gang - 2 way |
| 1 | 8 323 57 | ● Brushed stainless steel |
| 1 | 8 325 57 | ● Polished stainless steel |
| | | ● Glossy gold |

| Pack | Cat.Nos | Push on/off rotary dimmers 1000 W 250 V~ - 50/60 Hz |
|------|----------|---|
| | | Conform to BS EN 60669-1 - For flush-mounting back box to be min. 40 mm deep - 60-1000 W (230 V) - 60-500 W(127 V) for incandescent and halogen lamps 60-600 VA (230 V) - 60-300 VA (127 V) for halogen lamps with electronic transformers 60-100 VA (230 V) - 60-500 VA (127 V) for halogen lamps with ferromagnetic transformers Nominal plate dimensions: 86 x 86 mm |
| 1 | 8 321 50 | 1 gang - 2-way push switches |
| 1 | 8 323 50 | ● Brushed stainless steel |
| 1 | 8 325 50 | ● Polished stainless steel |
| | | ● Glossy gold |