


# Flush version floor boxes - sockets in horizontal position

## technical characteristics


### ■ Dimensions



| Cat.No   | A (mm) | B (mm) | C (mm) |
|----------|--------|--------|--------|
| 0 881 20 | 181    | 265    | 92     |
| 0 881 21 | 219    |        |        |
| 0 881 22 | 264    |        |        |

For heights of more than 122 mm, use feet  
Cat.No 0 881 42


### ■ For installation in raised floor




| Cat.No   | A (mm) | B (mm) |
|----------|--------|--------|
| 0 881 20 | 182    | 265    |
| 0 881 21 | 220    |        |
| 0 881 22 | 265    |        |

### ■ Installation principle in concrete floor

With auto-adjusting  
backbox




With universal adjustable  
backbox




# Flush version floor boxes - sockets in vertical position

## technical characteristics


### ■ Dimensions



Installation in a raised floor with electrical insulation kits  
Cat.Nos 0 880 26/27/28




Installation in a backbox for concrete floor



| Cat.No   | A (mm) | B (mm) | C (mm) | D (mm) |
|----------|--------|--------|--------|--------|
| 0 881 23 | 181    | 265    | 92     | 80     |
| 0 881 24 | 219    |        |        |        |
| 0 881 25 | 264    |        |        |        |


For heights of more than 122 mm, use feet  
Cat.No 0 881 42

### ■ For installation in raised floor



| Cat.No   | A (mm) | B (mm) |
|----------|--------|--------|
| 0 880 23 | 181    | 264    |
| 0 880 24 | 219    |        |
| 0 880 25 | 264    |        |



For use with electrical insulation kits Cat.Nos 0 880 26/27/28



x 2



### ■ Installation principle in concrete floor

With auto-adjusting  
backbox



H min. = 80 mm  
H max. = 125 mm

With universal adjustable  
backbox




H min. = 80 mm

# Flush version floor boxes - metal lid and finishing plate


## technical characteristics

### ■ Dimensions



| Cat.No      | A (mm) | B (mm) |
|-------------|--------|--------|
| 0 881 03/06 | 259    | 127    |
| 0 881 04/07 |        | 165    |
| 0 881 05/08 |        | 210    |

### ■ Dimensions



| Cat.No      | A (mm) | B (mm) |
|-------------|--------|--------|
| 0 881 45/48 | 257    | 125    |
| 0 881 46/49 |        | 163    |
| 0 881 47/50 |        | 208    |

