


Plexo™ mechanisms

controls and socket outlets IP 55



Mechanisms supplied with cover plate
Installation with surface-mounting boxes or flush-mounting support frames (p. 607)

Pack	Cat.Nos	Light sensitive switch, 230 V~
5	0 695 17	<p>Light sensitive switch 1 function Can be used to switch a lighting circuit "ON" and "OFF" based on light conditions (nightfall, daybreak) Supplied in one piece, including photoelectric cell Maximum load: - 1400 W incandescent and halogen lamps 230 V~ - 400 VA fluorescent tubes Luminosity threshold: 0,5 to 1500 lux IP 55 - IK 07</p> <ul style="list-style-type: none"> ● Grey

Pack	Cat.Nos	Key-operated switches 3 A - 250 V~
1	0 695 34	<p>Supplied with RONIS key n° 455 Key removable in all position 2 N/O contacts</p> <p>2 positions marked "0 - I"</p> <ul style="list-style-type: none"> ● Grey
1	0 695 35	<p>3 positions marked "I - 0 - II"</p> <ul style="list-style-type: none"> ● Grey

Pack	Cat.Nos	Emergency stop functions 3 A - 250 V~
1	0 695 47	<p>Supplied with "emergency stop" label in 8 languages. Yellow cover plate, red button</p> <p>Emergency stop button - 1 N/C contact</p> <ul style="list-style-type: none"> ● Grey/yellow
1	0 695 48	<p>Emergency stop with key for reset - N/O + N/C contact</p> <p>Key RONIS n° 455 supplied Key removable in 0 position</p> <ul style="list-style-type: none"> ● Grey/yellow
1	0 695 49	<p>Emergency stop - stay put 1/4 release - N/O + N/C contact</p> <p>Key removable in 0 position</p> <ul style="list-style-type: none"> ● Grey/yellow

Pack	Cat.Nos	Illuminated time lag switches - 250 V~
5	0 696 04	<p>Electronic time lag switch - IP 55 2-wire connection Supplied with lamp Temporization: 25 s to 15 min. Maximum loads: - 1000 W incandescent and halogen 230 V~ - 400 W halogen 130 V - 400 VA ELV halogen lamps - 400 VA fluorescent lamps - 2300 W resistive (heating)</p> <ul style="list-style-type: none"> ○ White ● Grey
5	0 695 04	

Pack	Cat.Nos	German standard socket outlets 16 A - 250 V~
10	0 696 39	<p>With earth lateral contact</p> <p>2P+E screw terminals</p> <ul style="list-style-type: none"> ○ White ● Grey ○ White antimicrobial⁽¹⁾
10	0 695 71	
5	0 707 22	
5	0 696 40	<p>2P+E automatic terminals</p> <ul style="list-style-type: none"> ○ White ● Grey
10	0 695 70	

Pack	Cat.Nos	British standard socket outlet 13 A - 250 V~
10	0 695 85	<p>2P+E screw terminals</p> <ul style="list-style-type: none"> ● Grey

Pack	Cat.Nos	French standard socket outlets 16 A - 250 V~
10	0 696 21	<p>2P+E automatic terminals</p> <p>With shutters for child protection</p> <ul style="list-style-type: none"> ○ White ● Grey ○ White antimicrobial⁽¹⁾
10	0 695 51	
5	0 707 21	
5	0 695 53	<p>2P+E tamperproof-screw terminals</p> <ul style="list-style-type: none"> ● Grey
5	0 695 55	<p>2P+E with flap-automatic terminals</p> <p>Automatic opening of the flap</p> <ul style="list-style-type: none"> ● Grey

Pack	Cat.No	Tamperproof insert for Cat.No 0 695 53
10	0 502 99	<p>Tamperproof insert for socket Fits directly into the plug</p>

1: Contains a silver compound to prevent the growth of bacteria on the surface

Green'Up Access socket outlets for electric vehicles, p. 373

