



# DLPlus mini-trunking 20 x 12.5 and 32 x 12.5

## profiles and finishing accessories



Selection chart **p. 796-797**  
Wiring capacity chart **see e-catalogue**

Pack	Cat.Nos		Mini-trunking
			EN 50085-2-1 approved
			<b>Without central partition</b>
			Mini-trunking with cable grip
			Equipped with an integrated device for holding cables in place
			Length 2.10 m
120 <sup>1</sup>   80	20 x 12.5	32 x 12.5	Without adhesive
120 <sup>1</sup>	0 300 08	0 300 15	With adhesive
	6 489 05		
120 <sup>1</sup>   80 <sup>1</sup>	0 300 07	0 300 14	<b>With central partition</b>
			Length 2.10 m
			<b>Finishing accessories</b>
20	20 x 12.5	32 x 12.5	End cap
	0 312 02	0 312 03	
10	0 302 21	0 302 51	Changeable internal-external angle
10	0 302 23	0 302 53	Changeable flat angle
20	0 336 02	0 336 03	Cover joint
10	0 302 24	0 302 54	Flat T-junction



1: Number of metres in pack

Pack	Cat.Nos	Special frames
		Supplied with end cap and divider for separation of currents
		<b>Installation alongside the mini-trunking</b>
		For vertical or horizontal mounting of surface mounting wiring accessories (p. 804)
10	0 314 04	1 gang
5	0 314 14	2 gang
		<b>Adaptors</b>
		<b>Adaptor for mounting Mosaic frames at end of the mini-trunking</b>
10	0 316 40	For 20 x 12.5 mini-trunking
10	0 316 41	For 32 x 12.5 mini-trunking
		<b>Adaptor for mounting Mosaic frames alongside the mini-trunking</b>
10	0 317 01	For Mosaic frames Cat.No 0 316 11 (p. 801)
10	0 317 02	For Mosaic frames Cat.Nos 0 316 13 and 0 316 21 (p. 801)
5	0 317 03	For Mosaic frames Cat.Nos 0 316 14 and 0 316 22 (p. 801)

- Connection of luminaires **p. 801**
- Other frames for wiring accessories **p. 801**
- Surface-mounting wiring accessories **p. 804**