


### 1. USE

Cable for high-speed VDI transmission networks

802.3 bt PoE++ up to type 4 applications compatible according to installation standards ISO/IEC 14763-2 : 2019 and EN 50174-2 : 2018

### 2. DESCRIPTION



Note : The conductive part of the shielding is located on the wire side

### 3. MARKING AND PACKAGING

Marking of Legrand cables

- LEGRAND
- Catalogue number
- Number of pairs
- Gauge
- Type
- Impedance
- Type of sleeve
- Category
- Conformity to standards
- EUROCLASS
- Velocity of propagation
- Traceability
- Measurement (remaining length in metres).

Complementary marking (on label)

- Designation
- Made in....

### 4. PERFORMANCE AT 250 MHZ (STAND. ANSI/TIA 568.2-D)

Reference	0 327 59
Maximum attenuation (dB/100 m)	32,8
Minimum NEXT (dB)	38,3
PS NEXT (dB)	36,3
ACRF (dB / 100 m)	18,8
PS ACRF (dB / 100 m)	16,8
Return Loss (dB)	17,3

### 5. TECHNICAL AND MECHANICAL FEATURES

Catalogue number	0327 59
Type	SF/UTP
Type of sleeve	PVC
Number of pairs	4
Assembly	Pairs
Diameter over insulation (mm)	1,16±
Average nominal diameter of the cable (mm)	8,1±0.3
Weight of cable (kg/km)	54 à 66
Min. bending radius when laying (mm)	65
AWG gauge*	24

\* According to UL 444 ed.3 table 4

**6. ELECTRICAL FEATURES AT 20°C**

Catalogue number	0 327 59
Type	SF/UTP
Maximum linear resistance (ohm/km)	95 *
DC dielectric strength	1 KV / 1 min *
Minimum insulation resistance (Mohm.km)	5000
Minimum propagation speed	> 65%
Characteristic impedance at 100 MHz	100 ±5Ω

\* According to standard IEC 61156-5

**7. ORDERING INFORMATION**

Catalogue number	0 327 59
Type	SF/UTP
Colour	Blue RAL 5015
Pack (m)	500
Packaging	Reel

**8. ENVIRONMENTAL FEATURES**

Transport and storage temperature: -20 at + 60 °C  
 Storage temperature before installation: 10°C during 24h (if stock ≤ 5°C)  
 Usage temperature: - 20 to + 60 °C

Fire rating : IEC 60332-1-2, EN 60332-1-2

EUROCLASS EN 13501-6 = Class Eca  
 Also compliant with Eca

**9. STANDARDS AND APPROVALS**

Cat 6, 250 MHz  
 Electrical performances and characteristics :  
 - ANSI/TIA 568.2-D  
 - EN 50173-1  
 - EN 50288-5-1  
 - ISO/IEC 11801 (ed. 2.2)  
 - IEC 61156-5  
 IEEE 802.3bt : PoE++