

FR\_710382

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

## **CB TEST CERTIFICATE Product** Multiple cord extension set Name and address of the applicant **LEGRAND FRANCE** 128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY, 87045 LIMOGES CEDEX - FRANCE Name and address of the manufacturer **LEGRAND FRANCE** 128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY, 87045 LIMOGES CEDEX - FRANCE Name and address of the factory NINGBO BANMEN ELECTRIC APPLIANCE CO., LTD East Industrial Zone, Guanhaiwei Cixi City 315314 ZHEJIANG PROVINCE - CHINA Note: When more than one factory, please report on page 2 ☐ Additional Information on page 2 Ratings and principal characteristics See Annex Trademark / Brand (if any) legrand Customer's Testing Facility (CTF) Stage used Model / Type Ref. RNC10V Reference 0 494 30 Additional information (if necessary may also be ☐ Additional Information on page 2 reported on page 2) A sample of the product was tested and found to IEC 60884-1:2002(ed.3) +A1:2006 +A2:2013 be in conformity with IEC 60884-2-7:2011 +A1:2013 As shown in the Test Report Ref. No. which ABND-ESH-P20072849-1 forms part of this Certificate ABND-ESH-P20072849-2

This CB Test Certificate is issued by the National Certification Body



LCIE – Laboratoire Central des Industries Electriques 33, avenue du Général Leclerc – BP8 FR 92 266 Fontenay aux Roses Cedex www.lcie.fr

Date: 22/12/2020





FR\_710382

## **ANNEX**

## **RATING AND MAIN CHARACTERISTICS**

Model	Reference	Number of 16A socket-outlets	Number of 6A socket- outlets	Color of enclosure
RNC10V	0 494 30	4	4	BLACK

## CLASSIFICATION

CLASSIFICATION		
standard Sheet:	Standard sheet V of CEE 7 (16A socket-outlet) / Standard sheet VIII of NF C 61-314 (6A socket-out-let) / Standard sheet VII of CEE 7 (Plug)	
rated current (A)	16A	
rated load (W)	3680W	
rated voltage (V)	250V	
household voltage (V)	230V	
degree of protection	IP20	
provision for earthing	with earthing contact (Solid earthing pin)	
method of connecting the cable	Non-rewirable	
type of terminals	-	
type of connections	soldered / other (riveted)	
colour	Black	
socket-outlets		
multiple socket-outlets	6A: 2	
number of socket-outlets	16A: 2	
degree of protection against electric shock	normal protection	
existence of shutters	with shutters	
method of application - mounting	portable type	
plugs:		
class of equipment	1	
entry of cable	lateral	

type of components	manufacturer	Conformity
Plug	Legrand France	NF 666578/M1
Flug	Legianu i iance	CB FR 558589/M1
Cable	Legrand France	VDE 40017697
Built-in switch module	Legrand France	LCIE test report No.:
		ABND-ESH-P20072873
SPD	Legrand France	LCIE test report No.:
		ABND-ESH-P20072863
Socket-outlets	Legrand France	LCIE test report No.:
		ABND-ESH-P20072849-1



LCIE – Laboratoire Central des Industries Electriques 33, avenue du Général Leclerc – BP8 FR 92 266 Fontenay aux Roses Cedex www.lcie.fr

Date: 22/12/2020

