

IEC**IECEE**

®

TM

Ref. Certif. No.

FR_719465**IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME****CB TEST CERTIFICATE**

Product

Socket-outlet for fixed-electrical installations

Name and address of the applicant

LEGRAND FRANCE
128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY
87045 LIMOGES CEDEX
FRANCE

Name and address of the manufacturer

LEGRAND FRANCE
128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY
87045 LIMOGES CEDEX
FRANCE

Name and address of the factory

LEGRAND FRANCE
128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY
87045 LIMOGES CEDEX
FRANCE

Note: When more than one factory, please report on page 2

 Additional Information on page 2

Ratings and principal characteristics

See Annex

Trademark / Brand (if any)



Customer's Testing Facility (CTF) Stage used

/

Model / Type Ref.

Series PLEXO66
See Annex

Additional information (if necessary may also be reported on page 2)

Supersedes CBTC FR 651132B dated 21/01/2015. Update further to the evolution of the standard(s)

 Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 60884-1:2022


As shown in the Test Report Ref. No. which forms part of this Certificate

20804276-796164

This CB Test Certificate is issued by the National Certification Body

**LCIE**

LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE

33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCEwww.lcie.frSignature: **Jérôme REYSSON**
Certification Officer

Date: 04/07/2024

ANNEX

References, ratings and main characteristics:

Type	References	Function	IP	IK	Specificity
0 904 71	0 904 71	2P+T/2P+E	IP66	IK08	Electric vehicle Charging with accessory 0 904 78
	0 904 76	2P+T/2P+E	IP66	IK08	0 904 71 sold with accessory 0 904 78 and RCCB reference 4 107 54
	0 904 77	2P+T/2P+E	IP66	IK08	0 904 71 sold with specific over-packaging
	0 904 66	2P+T/2P+E	IP66	IK08	Complete product
	0 904 86	2P+T/2P+E	IP66	IK08	Modular socket-outlet


Accessories

Reference	Characteristics
0 904 78	Hook of attachment
0 904 91	Modular box

<i>Standard Sheet</i>	<i>I</i>
<i>Rated current (A)</i>	<i>16 A</i>
<i>Rated voltage (V)</i>	<i>250 V~</i>
<i>Degree of protection</i>	<i>IP66</i>
<i>Provision for earthing</i>	<i>with earthing contact</i>
<i>Method of connecting the cable</i>	<i>rewirable</i>
<i>Type of terminals</i>	<i>screw-type</i>
<i>Colour</i>	<i>Grey</i>
<i>Pins</i>	<i>not solid</i>
Socket-outlets	
<i>Degree of protection against electric shock</i>	<i>normal protection</i>
<i>Existence of shutters</i>	<i>with shutters</i>
<i>Method of application - mounting</i>	<i>surface - type</i>
<i>Method of installation</i>	<i>design A</i>



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
 33 avenue du Général Leclerc
 92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr



Date: 04/07/2024

Signature: Jérôme REYSSON
 Certification Officer