

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Device for connecting a luminaire (DCL)
Temporary DCL lampholder

Name and address of the applicant

LEGRAND FRANCE
128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY
87045 LIMOGES CEDEX
FRANCE

Name and address of the manufacturer

LEGRAND FRANCE
128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY
87045 LIMOGES CEDEX
FRANCE

Name and address of the factory

ILIRIA ELECTRIC SH.P.K.
Autostrada Tirana Durazzo Km 5
TIRANA
ALBANIA

Note: When more than one factory, please report on page 2

☐ Additional Information on page 2

Ratings and principal characteristics

See Annex

Trademark / Brand (if any)



Customer's Testing Facility (CTF) Stage used

/

Model / Type Ref.

0 601 35

Additional information (if necessary may also be reported on page 2)

Supersedes CBTC 595661B dated 23/03/2010. Update further to the evolution of the standard(s)

☐ Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 61995-1:2005 + A1:2016

As shown in the Test Report Ref. No. which forms part of this Certificate

167159-750766


This CB Test Certificate is issued by the National Certification Body



LCIE – Laboratoire Central des Industries Electriques
33, avenue du Général Leclerc – BP8
FR 92 266 Fontenay aux Roses Cedex
www.lcie.fr

Date: 27/08/2020

Signature: 
Certification Officer



ANNEX

DCL Temporary Lampholder ref. 0 601 35

Classification

Conformity to	EN 60238:2004 + A1:2008 + A2: 2011 E27 lampholder Test report N° LCI-ESH-P20060165
Rated current Rated voltage	4 A 75 W 250 V ~
Class of equipment	II
Material of the external parts	lampholder of insulating material
Degree of protection against ingress of water	ordinary lampholder
Method of fixing	for connection to a DCL socket-outlet
Protection against electric shock	independent lampholder
Resistance to heat	lampholder T marked (210°C)
Type of terminals	terminal for connection to a DCL socket-outlet
Colour	white

Provided with DCL plug ref. 0 601 34

Classification

Standard sheet	NF EN 61995-2 : 1-2
Rated current (A) Rated voltage (V)	6 A 250 V ~
Connecting the cable	rewirable
Type of terminals	screw-type
Class of luminaire	I
Degree of protection	IP20
Provision of signal contacts	without provision
Conformity	LCIE (NF)



LCIE – Laboratoire Central des Industries Electriques
33, avenue du Général Leclerc – BP8
FR 92 266 Fontenay aux Roses Cedex
www.lcie.fr

Date: 27/08/2020

Signature



Certification Officer