



Ref. Certif. No.

ES2591-M1-AENOR

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

LED LUMINAIRES FOR EMERGENCY LIGHTING

Name and address of the applicant

LEGRAND GROUP ESPAÑA, S.L.
HIERRO, 56
28850 TORREJON DE ARDOZ (Madrid - Spain)

Name and address of the manufacturer

SAME AS ABOVE

Name and address of the factory

SAME AS ABOVE

Note: When more than one factory, please report on page 2

Additional Information on page 2

Ratings and principal characteristics

SEE ANNEX

Trademark (if any)

LEGRAND

Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

SEE ANNEX

Additional information (if necessary may also be reported on page 2)

Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 60598-1:2020
IEC 60598-2-22:2014
IEC 60598-2-22:2014/AMD1:2017
IEC 62262:2002

As shown in the Test Report Ref. No. which forms part of this Certificate

2022010001B1-M2

This CB Test Certificate is issued by the National Certification Body

AENOR INTERNACIONAL S.A.U.
CI Génova, 6
ES-28004 MADRID (SPAIN)

Date: 2023-04-10

Signature: 
Rafael GARCÍA MEIRO
CEO

ANNEX TO CB CERTIFICATE N° ES2591-M1-AENOR

CERTIFIED REFERENCES AND THEIR PRINCIPAL CHARACTERISTICS

LED LUMINAIRES FOR EMERGENCY LIGHTING

Type reference	Trade Mark	Rated voltage and frequency	N° lamps x rated power, type and lampholder	IP degree of protection	Power supply connection means	Classif. per holding surface material	Protection against electric shocks (class)	Rated lumen output and duration	Battery features	Additional information	General data
660032	LEGRAND	230 V~; 50/60 Hz	2 x 0,25W; módulo module LED	IP42; IK 07	Bornes Terminals	Apta para superficies normalment e inflamables Suitable for normally flammable surfaces	Clase II Class II	100 lm - 1h	NiCd 3,6 V 0,7 Ah	No permanente Non maintained; Puesta en reposo remota Remote rest	Protección electrónica Electronic Protection; URA SPOT PRO / X-LIGHT 360 (STD)
660042	LEGRAND	230 V~; 50/60 Hz	4 x 0,25W; módulo module LED	IP42; IK 07	Bornes Terminals	Apta para superficies normalment e inflamables Suitable for normally flammable surfaces	Clase II Class II	100 lm - 1h	NiCd 3,6 V 0,7 Ah	No permanente/ Permanente Non maintained/ Maintained; Puesta en reposo remota Remote rest	Protección electrónica Electronic Protection; URA SPOT PRO / X-LIGHT 360 (STD)
660044	LEGRAND	230 V~; 50/60 Hz	4 x 0,25W; módulo module LED	IP42; IK 07	Bornes Terminals	Apta para superficies normalment e inflamables Suitable for normally flammable surfaces	Clase II Class II	200 lm - 1h	NiCd 3,6 V 1,1 Ah	No permanente/ Permanente Non maintained/ Maintained; Puesta en reposo remota Remote rest	Protección electrónica Electronic Protection; URA SPOT PRO / X-LIGHT 360 (STD)
660045	LEGRAND	230 V~; 50/60 Hz	8 x 0,25W; módulo module LED	IP42; IK 07	Bornes Terminals	Apta para superficies normalment e inflamables Suitable for normally flammable surfaces	Clase II Class II	350 lm - 1h	NiMH 3,6 V 1,5 Ah	No permanente/ Permanente Non maintained/ Maintained; Puesta en reposo remota Remote rest	Protección electrónica Electronic Protection; URA SPOT PRO / X-LIGHT 360 (STD)
660047	LEGRAND	230 V~; 50/60 Hz	6 x 0,25W; módulo module LED	IP42; IK 07	Bornes Terminals	Apta para superficies normalment e inflamables Suitable for normally flammable surfaces	Clase II Class II	200 lm - 2h	NiMH 3,6 V 1,5 Ah	No permanente/ Permanente Non maintained/ Maintained; Puesta en reposo remota Remote rest	Protección electrónica Electronic Protection; URA SPOT PRO / X-LIGHT 360 (STD)
660048	LEGRAND	230 V~; 50/60 Hz	4 x 0,25W; módulo module LED	IP42; IK 07	Bornes Terminals	Apta para superficies normalment e inflamables Suitable for normally flammable surfaces	Clase II Class II	100 lm - 3h	NiCd 3,6 V 1,1 Ah	No permanente/ Permanente Non maintained/ Maintained; Puesta en reposo remota Remote rest	Protección electrónica Electronic Protection; U22 ROND / X-LIGHT 360 (STD)
660142	LEGRAND	230 V~; 50/60 Hz	4 x 0,25W; módulo module LED	IP42; IK 07	Bornes Terminals	Apta para superficies normalment e inflamables Suitable for normally flammable surfaces	Clase II Class II	100 lm - 1h	NiMH 3,6 V 0,5 Ah	No permanente/ Permanente Non maintained/ Maintained; Puesta en reposo remota Remote rest	Protección electrónica Electronic Protection; URA SPOT PRO / X-LIGHT 360 (Autotest)
660144	LEGRAND	230 V~; 50/60 Hz	6 x 0,25W; módulo module LED	IP42; IK 07	Bornes Terminals	Apta para superficies normalment e inflamables Suitable for normally flammable surfaces	Clase II Class II	200 lm - 1h	NiMH 3,6 V 1,1 Ah	No permanente/ Permanente Non maintained/ Maintained; Puesta en reposo remota Remote rest	Protección electrónica Electronic Protection; URA SPOT PRO / X-LIGHT 360 (Autotest)

ANNEX TO CB CERTIFICATE N° ES2591-M1-AENOR

CERTIFIED REFERENCES AND THEIR PRINCIPAL CHARACTERISTICS

Type reference	Trade Mark	Rated voltage and frequency	N° lamps x rated power, type and lampholder	IP degree of protection	Power supply connection means	Classif. per holding surface material	Protection against electric shocks (class)	Rated lumen output and duration	Battery features	Additional information	General data
660145	LEGRAND	230 V~; 50/60 Hz	8 x 0,25W; módulo module LED	IP42; IK 07	Bornes Terminals	Apta para superficies normalment e inflamables Suitable for normally flammable surfaces	Clase II Class II	350 lm - 1h	NiMH 3,6 V 1,5 Ah	No permanente/ Permanente Non maintained/ Maintained; Puesta en reposo remota Remote rest	Protección electrónica Electronic Protection; URA SPOT PRO / X- LIGHT 360 (Autotest)
660146	LEGRAND	230 V~; 50/60 Hz	4 x 0,25W; módulo module LED	IP42; IK 07	Bornes Terminals	Apta para superficies normalment e inflamables Suitable for normally flammable surfaces	Clase II Class II	100 lm - 3h	NiMH 3,6 V 1,1 Ah	No permanente/ Permanente Non maintained/ Maintained; Puesta en reposo remota Remote rest	Protección electrónica Electronic Protection; U22 ROND / X-LIGHT 360 (Autotest)
660147	LEGRAND	230 V~; 50/60 Hz	6 x 0,25W; módulo module LED	IP42; IK 07	Bornes Terminals	Apta para superficies normalment e inflamables Suitable for normally flammable surfaces	Clase II Class II	200 lm - 2h	NiMH 3,6 V 1,5 Ah	No permanente/ Permanente Non maintained/ Maintained; Puesta en reposo remota Remote rest	Protección electrónica Electronic Protection; URA SPOT PRO / X- LIGHT 360 (Autotest)