



Ref. Certif. No.

FR_706217/M1

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Shaver transformers and shaver supply units

Name and address of the applicant

Legrand Intelligent Electrical (Huizhou) Co., Ltd.
Bldg. B1-B3, East No. 39 Hechang 6th Rd.,
HZZK Hi-tech Industrial Development Zone,
Huizhou 516001, Guangdong - CHINA

Name and address of the manufacturer

LEGRAND FRANCE
128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY,
87045 LIMOGES CEDEX - FRANCE

Name and address of the factory

Note: When more than one factory, please report on page 2

☒ Additional Information on page 2

Ratings and principal characteristics

See Annex

Trademark / Brand (if any)

legrand

Customer's Testing Facility (CTF) Stage used

/

Model / Type Ref.

See Annex

Additional information (if necessary may also be reported on page 2)

Supersedes CBTC FR_706217 dated 28/06/2019.
Addition of factories
Change the licence holder and trademark
Update the list of components
Update the list of product references

☐ Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 61558-1:2005 +A1:2009(ed.2)
IEC 61558-2-5:2010(ed. 2)

As shown in the Test Report Ref. No. which forms part of this Certificate

ARLI-ESH-P24110874

This CB Test Certificate is issued by the National Certification Body



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 11/06/2025

Signature

LABORATOIRE CENTRAL DES
INDUSTRIES ELECTRIQUES
S.A.S au capital de 15.745.984 €
R.C.S. Nanterre 5174
33 avenue du Général Leclerc
92260 FONTENAY-AUX-ROSES

Julien GAUTHIER
Certification Officer

ANNEX

Name and address of the factories:

Legrand Intelligent Electrical (Huizhou) Co., Ltd.

Bldg. B1-B3, East No. 39 Hechang 6th Rd., HZZK Hi-tech Industrial Development Zone, Huizhou 516001, Guangdong - CHINA

LEGRAND

AVENUE DU PARC ALATA - 60550 VERNEUIL EN HALATTE – FRANCE

LEGRAND FRANCE

128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY, 87045 LIMOGES CEDEX – FRANCE

RAIS HASSAN SAADI Logistics Dubai

Jebel Ali Free Zone, P.O. Box 7 Dubai - UNITED ARAB EMIRATES

NOVATEUR ELECTRICAL & DIGITAL SYSTEMS PVT. LTD

A-2, MIDC AREA, MALEGAON VILLAGE, SINNAR, DIST. NASHIK - 422113, MAHARASHTRA - INDIA

References, ratings and main characteristics:

Model list:

Reference	Rated voltage		Class of Shaver supply unit	Color of enclosure
	Supply	Output		
5 721 53	230V	120/230V	I	White - with earth terminal
5 721 55	230V	120/230V	II	White
5 726 53	230V	120/230V	I	Magnesium - with earth terminal
5 726 55	230V	120/230V	II	Magnesium
5 726 65	230V	120/230V	II	Matte chrome
5 726 66	230V	120/230V	II	Champagne
5 727 62	230V	120/230V	I	Matte chrome - with earth terminal
5 727 64	230V	120/230V	I	Champagne - with earth connector
5 736 53	230V	120/230V	I	Graphite color (code C008A) - with earth terminal
AC360MW	230V	120/230V	II	Matt White
AC360MT	230V	120/230V	II	Matt Titanium
AC360MB	230V	120/230V	II	Matt Black
AC360CH	230V	120/230V	II	Champagne
AC360DB	230V	120/230V	II	Dark Bronze
AC360RS	230V	120/230V	II	Rose - with earth terminal
AC361MW	230V	120/230V	I	Matt White - with earth terminal
AC361MT	230V	120/230V	I	Matt Titanium - with earth terminal
AC361MB	230V	120/230V	I	Matt Black - with earth terminal
AC361CH	230V	120/230V	I	Champagne - with earth terminal
AC361DB	230V	120/230V	I	Dark Bronze - with earth terminal
AC361RS	230V	120/230V	I	Rose - with earth terminal



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE

33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE

www.lcie.fr

Date: 11/06/2025

Signature:



ANNEX

Shaver supply unit 5 7*** series can be equipped with the following cover plates:

Reference	Other information		
	Color	Finish	Material
5 750 70	White	Neutral	Insulating material
5 750 71	Pearl Alu		
5 750 72	Graphite		
5 713 05	Soft Alu		
5 713 15	Magnesium		
5 713 25	Champagne		
5 713 35	Dark Bronze		
5 750 73	Mirror Black	Mirror	Metal + insulating material
5 750 74	Mirror White		
5 761 65	Mirror Taupe		
5 761 66	Mirror Red	Wood	Metal + insulating material
5 750 75	Wenge Style		
5 761 69	Light Oak		
5 713 95	Grey Oak		
5 750 76	Stainless Steel	Brushed metal	Metal + Insulating material
5 761 60	Gold Brass		
5 713 45	Black		
5 713 55	Pink Champagne		
5 713 65	Reflective Stainless Steel	Reflective metal	Metal + insulating material
5 713 75	Reflective Gold		
5 713 85	Reflective Black		
5 761 61	Casual	Graphic	Metal + insulating material
5 761 62	Formal		
5 761 63	Club	Leather	Metal + insulating material
5 761 64	Galuohat		
5 761 67	Woven Metal	Signature	Metal + insulating material
5 714 05	Cube		
5 761 68	Edition 1	Tattoo	Insulating material

Additional information for AC360** and AC361 series:

All the commercial references listed below may be supplemented with a prefix of type LG-, BT-, ... (to indicate the brand) and/or suffix of type 0, 1, 2, 3, 4, FI, EX, ... In this case, the products are technically the same.

REFERENCES

	Matt White	Matt Titanium	Matt Black	Champagne	Dark Bronze	Rose
Type reference	Commercial ref	Commercial ref	Commercial ref	Commercial ref	Commercial ref	Commercial ref
0461TQ650	AC361MW	AC361MT	AC361MB	AC361CH	AC361DB	AC361RS
0461TQ650	AC360MW	AC360MT	AC360MB	AC360CH	AC360DB	AC360RS



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 11/06/2025

Signature: 



ANNEX

COVER PLATES

Commercial ref									Designation
Matt White	Matt Titanium	Matt Black	Frosted White	Frosted Black	Dark Aluminium	Brushed Stainless Steel	Night Blue	Solid Aluminium	
Classic									
AC1105 MW	AC1105 MT	AC1105MB	AC1105 FW	AC1105F B	AC1105DA	AC1105B S	AC1105NB	AC1105SA	3M BS PLATE FOR 2G BOX

CLASSIFICATION

Frequency	50 / 60 Hz
Supply	230 V~
Output	120 / 230 V
Power output	20 VA
Class	I & II, see table above
Short-circuit protection	Non-inherently short-circuit proof
Degree of protection	IP24
Mobility	Stationary
Time of operation	Continuous
Intended use	Associated for specific use
Rated maximum ambient temperature	25°C
Windings	Class A
Output connection	Socket
Terminals (Supply)	Screwless



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 11/06/2025

Signature: 
