

IEC**IECEE**

Ref. Certif. No.

FR_716555/A1

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Socket-outlet for fixed-electrical installations

Name and address of the applicant

LEGRAND FRANCE
128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY
87045 LIMOGES CEDEX
FRANCE

Name and address of the manufacturer

LEGRAND FRANCE
128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY
87045 LIMOGES CEDEX
FRANCE

Name and address of the factory

LEGRAND FRANCE
128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY
87045 LIMOGES CEDEX
FRANCE

Note: When more than one factory, please report on page 2

 Additional Information on page 2

Ratings and principal characteristics

See Annex

Trademark / Brand (if any)



Customer's Testing Facility (CTF) Stage used

/

Model / Type Ref.

PLEXO serie
0 697 85L - 0 698 85L

Additional information (if necessary may also be reported on page 2)

Supersedes CBTC FR_716555 dated 03/03/2023. Editorial correction

 Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 60884-1:2002(ed.3) +A1:2006 +A2:2013

As shown in the Test Report Ref. No. which forms part of this Certificate

14332190-776572

This CB Test Certificate is issued by the National Certification Body

LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCEwww.lcie.frLABORATOIRE CENTRAL DES
INDUSTRIES ELECTRIQUES
S.A.S au capital de 15.745.984 €
RCS Nanterre B 408 363 174
33 avenue du Général Leclerc
F - 92266 FONTENAY AUX ROSESSignature:
Julien GAUTHIER
Certification Officer

Date: 09/03/2023

ANNEX

Type reference	References Anthracite	Funtion	Characteristic	Type of terminals	IP	Mounting	specificities
EVFV1	0 697 85L	2P+T	16A - 250V~	Screw type (rigid and flexible)	IP55	Surface type	Mechanism with box
EVFV1	0 698 85L	2P+T	16A - 250V~	Screw type (rigid and flexible)	IP55	/	Mechanism only

Accessories


References Anthracite	Designation
0 696 01L	Box 1 gang with membrane cable gland
0 700 56	Box 1 gang with membrane cable gland
0 696 06L	Frame 1 gang
0 694 94L	Peg fixation

Standard sheet	I (NF C 61314) / V (CEE7)
Rated current (A)	16A
Rated voltage (V)	250V~
Degree of protection	IP55
Provision for earthing	With earthing contact
Method of connecting the cable	Rewirable
Type of terminals	Screw-type
Color	Grey
Pins	Not solid
Degree of protection against electric shock	Increased protection
Existence of shutters	With shutters
Method of mounting	Flush-type or surface-type
Method of installation	Design A



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
 33 avenue du Général Leclerc
 92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 09/03/2023



Signature: 
Julien GAUTHIER
 Certification Officer