

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Flexible conduits system

Name and address of the applicant

bticino S.p.A.
Viale Borri, 231, 21100 Varese (VA)
Italy

Name and address of the manufacturer

bticino S.p.A.
Viale Borri, 231, 21100 Varese (VA)
Italy

Name and address of the factory

LEGRAND FRANCE LORRAINE SA
89 Chemin de Montrichard Boite Postale 89, 54704 Pont à Mousson Cedex
France*Note: When more than one factory, please report on page 2* Additional information on page 2

Ratings and principal characteristics

Nominal diameter: 7, 8 or 10 mm
Conduits classification coding: 1 1 4 2 4 0 6 6 – 1 1 1
Black colour
(see also pages 5 and 7 of Test Report No. MI22-0082234-01).

Trademark / Brand (if any)

RTA 

RTA LEGRAND

Customer's Testing Facility (CTF) Stage used

CTF Stage 2

Model / Type Ref.

LGP-Robotica series
(see also Additional Sheet)

Additional information (if necessary may also be reported on page 2)

 Additional information on page 2

A sample of the product was tested and found to be in conformity with

IEC 61386-1:2008, IEC 61386-1:2008/AMD1:2017, IEC 61386-23:2021

National differences:
EU Group Differences

As shown in the Test Report Ref. No. which forms part of this Certificate

MI22-0082234-01

This CB Test Certificate is issued by the National Certification Body

IMQ S.p.A.
Via Quintiliano 43
Milano, 20138
Italy

Date: 2024-01-31

Signature: Fabio Taormina

Description of the components of the flexible conduits system LGP-Robotica series

| Code | Description | Nominal diameter | Colour |
|--------|--------------------------------------|------------------|--------|
| 666430 | Flexible conduit | 7 mm | Black |
| 666431 | Flexible conduit | 8 mm | Black |
| 667005 | Flexible conduit | 10 mm | Black |
| 666468 | Straight connector with M12 thread | 7 mm | Black |
| 666469 | Straight connector with M16 thread | 7 mm | Black |
| 666470 | Straight connector with M16 thread | 8 mm | Black |
| 666471 | Straight connector with M12 thread | 10 mm | Black |
| 666472 | Straight connector with M16 thread | 10 mm | Black |
| 666565 | 90° connector with M12 thread | 7 mm | Black |
| 666566 | 90° connector with M16 thread | 8 mm | Black |
| 666567 | 90° connector with M16 thread | 10 mm | Black |
| 666610 | 90° connector with M12 thread | 7 mm | Black |
| 666611 | 90° connector with M16 thread | 8 mm | Black |
| 666612 | 90° connector with M12 thread | 10 mm | Black |
| 666613 | 90° connector with M16 thread | 10 mm | Black |
| 666698 | 45° connector with M12 thread | 7 mm | Black |
| 666699 | 45° connector with M16 thread | 8 mm | Black |
| 666700 | 45° connector with M12 thread | 10 mm | Black |
| 666701 | 45° connector with M16 thread | 10 mm | Black |
| 666935 | Parallel "Y" fitting | 10 mm → 2×7 mm | Black |
| 666938 | "Y" fitting | 8 mm → 2×7 mm | Black |
| 666959 | Gasket | 7 mm | Black |
| 666960 | Gasket | 8 mm | Black |
| 666961 | Gasket | 10 mm | Black |
| 666981 | Fixing clip | 7 mm | Black |
| 666982 | Fixing clip | 8 mm | Black |
| 666983 | Fixing clip | 10 mm | Black |
| 666995 | Top hat rails 35 mm wide fixing clip | 7 mm to 10 mm | Black |