



L C I E

Licence / License



N° : NF012_3779/M2

Titulaire :
License Holder:

LEGRAND FRANCE
128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY
87045 LIMOGES CEDEX
FRANCE

Site de fabrication :
Factory:

0010AP

Produit :
Product:

**Interrupteur pour installations électriques fixes
domestiques et analogues**
Switch for household and similar fixed electrical installations

Marque commerciale (s'il y a lieu) :
Trade mark (if any):



Modèle, type, référence :
Model, type, reference:

Voir Annexe / See Annex

Caractéristiques principales :
Main characteristics:

Voir Annexe / See Annex

Informations complémentaires :
Additional information:

/

Le produit est conforme à :
The product is in conformity with:

EN 60669-1:2018

Documents pris en compte :
Relevant documents:

TR n° 30416255-820675

Annule et remplace (s'il y a lieu) :
Cancels and replaces (if necessary):

La licence / License NF012_3779/M1 du/of 09/10/2024 Mise
à jour de la liste des références produit/update the list of
product references

En vertu de la présente décision notifiée par le LCIE
organisme mandaté, AFNOR Certification accorde le
droit d'usage de la Marque NF à la société qui en est
titulaire pour les produits visés ci-dessus, dans les
conditions définies par les règles générales de la
Marque NF et par les règles de certification NF, pour
autant que les contrôles réguliers de la fabrication et les
vérifications par tierce partie soient satisfaisants.

On the strength of the present decision notified by LCIE
mandated certification body, AFNOR Certification grants the right to use the NF
Mark to the license holder for the above mentioned products, within
the frame of the general rules of the NF Mark and of the NF
certification rules, as far as the regular checking and third party
verifications of the production are satisfactory.

Fontenay-aux-Roses, 30/09/2026


Date de fin de validité / Expiry date
:

La validité de la présente licence cesse dès
l'annulation de l'une des normes sur lesquelles elle
est fondée /

The present license is valid until the cancellation of one of the
standards on which it is based.

Julien GAUTHIER

Responsable Certification / Certification Officer



La reproduction de ce document n'est autorisée que sous sa forme intégrale / Reproduction of this document is authorized only in its integral form

Page 1 / 4



Annexe de la licence / Annex of license NF012_3779/M2

L C I E

Reference		Univers	Method of mounting	Finition	Type reference	Rated current / Voltage	Actuating	Specificity
Complete	Modular							
67001		MEMORY	B	CRISTAL	A	10AX, 250V~	T	
67002					2 x A	10AX, 250V~	T	
67004					2 x A	10AX, 250V~	T	
67006					3 x A	10AX, 250V~	T	
67007					A	10AX, 250V~	T	Locator
67008					4 x A	10AX, 250V~	T	
67012					B + H	6A, 250V~	TM	
67015					B	6A, 250V~	TM	
67017					B	6A, 250V~	TM	Locator
67101					A	10AX, 250V~	T	
67102				BRUSHED STEEL	2 x A	10AX, 250V~	T	
AR67103					A + B	10AX, 250V~ and 6A, 250V~	T + TM	
67104					2 x A	10AX, 250V~	T	
AR67105					H + A	10AX, 250V~ and 6A, 250V~	TM + T	
67106					3 x A	10AX, 250V~	T	
67107					A	10AX, 250V~	T	Locator
67108					4 x A	10AX, 250V~	T	
67112					B + H	6A, 250V~	TM	
67115					B	6A, 250V~	TM	
67117					B	6A, 250V~	TM	Locator
67201				BRUSHED GOLD	A	10AX, 250V~	T	
67202					2 x A	10AX, 250V~	T	
AR67203					A + B	10AX, 250V~ and 6A, 250V~	T + TM	
67204					2 x A	10AX, 250V~	T	
AR67205					H + A	10AX, 250V~ and 6A, 250V~	TM + T	
67206					3 x A	10AX, 250V~	T	
67207					A	10AX, 250V~	T	Locator
67208					4 x A	10AX, 250V~	T	
67212					B + H	6A, 250V~	TM	
67215					B	6A, 250V~	TM	
67217					B	6A, 250V~	TM	Locator
67301		EPURE	A	STEEL	A	10AX, 250V~	T	
67302					2 x A	10AX, 250V~	T	
67304					2 x A	10AX, 250V~	T	
67306					3 x A	10AX, 250V~	T	
67307					A	10AX, 250V~	T	Locator
67308					4 x A	10AX, 250V~	T	
67312					B + H	6A, 250V~	TM	
67315					B	6A, 250V~	TM	
67317					B	6A, 250V~	TM	Locator
67401	ARM67401			BRUSHED STEEL	A	10AX, 250V~	T	
67402	ARM67402				2 x A	10AX, 250V~	T	
	ARM67403				A + B	10AX, 250V~ and 6A, 250V~	T + TM	
67404					2 x A	10AX, 250V~	T	
	ARM67405				H + A	10AX, 250V~ and 6A, 250V~	TM + T	
67406					3 x A	10AX, 250V~	T	

Reference		Univers	Method of mounting	Finition	Type reference	Rated current / Voltage	Actuating	Specificity
Complete	Modular							
67407		EPURE	A	BRUSHED STEEL	A	10AX, 250V~	T	Locator
67408					4 x A	10AX, 250V~	T	
67412	ARM67412				B + H	10AX, 250V~ and 6A, 250V~	TM	
67415	ARM67415				B	6A, 250V~	TM	
67417				SATIN STEEL	B	6A, 250V~	TM	Locator
67501					A	10AX, 250V~	T	
67502					2 x A	10AX, 250V~	T	
67504					2 x A	10AX, 250V~	T	
67506					3 x A	10AX, 250V~	T	
67507					A	10AX, 250V~	T	Locator
67508					4 x A	10AX, 250V~	T	
67512					B + H	6A, 250V~	TM	
67515					B	6A, 250V~	TM	
67517					B	6A, 250V~	TM	Locator
67601				MIRROR STEEL	A	10AX, 250V~	T	
67602					2 x A	10AX, 250V~	T	
67604					2 x A	10AX, 250V~	T	
67606					3 x A	10AX, 250V~	T	
67607					A	10AX, 250V~	T	Locator
67608					4 x A	10AX, 250V~	T	
67612					B + H	6A, 250V~	TM	
67615					B	6A, 250V~	TM	
67617					B	6A, 250V~	TM	Locator
67701	ARM67701			GOLD MIRROR	A	10AX, 250V~	T	
67702	ARM67702				2 x A	10AX, 250V~	T	
	ARM67703				A + B	10AX, 250V~ and 6A, 250V~	T + TM	
67704					2 x A	10AX, 250V~	T	
	ARM67705				H + A	10AX, 250V~ and 6A, 250V~	TM + T	
67706					3 x A	10AX, 250V~	T	
67707					A	10AX, 250V~	T	Locator
67708					4 x A	10AX, 250V~	T	
67712	ARM67712				B + H	6A, 250V~	TM	
67715	ARM67715				B	6A, 250V~	TM	
67717					B	6A, 250V~	TM	Locator
67801	ARM67801			BLACK MAT	A	10AX, 250V~	T	
67802	ARM67802				2 x A	10AX, 250V~	T	
	ARM67803				A + B	10AX, 250V~ and 6A, 250V~	T + TM	
67804					2 x A	10AX, 250V~	T	
	ARM67805				H + A	10AX, 250V~ and 6A, 250V~	TM + T	
67806					3 x A	10AX, 250V~	T	
67807					A	10AX, 250V~	T	Locator
67808					4 x A	10AX, 250V~	T	
67812	ARM67812				B + H	6A, 250V~	TM	
67815	ARM67815				B	6A, 250V~	TM	
67817					B	6A, 250V~	TM	Locator
67901	ARM67901			WHITE SATIN	A	10AX, 250V~	T	
67902	ARM67902				2 x A	10AX, 250V~	T	
	ARM67903				A + B	10AX, 250V~ and 6A, 250V~	T + TM	
67904					2 x A	10AX, 250V~	T	

Reference		Univers	Method of mounting	Finition	Type reference	Rated current / Voltage	Actuating	Specificity
Complete	Modular							
	ARM67905	EPURE	A	WHITE SATIN	H + A	10AX, 250V~ and 6A, 250V~	TM + T	
67906					3 x A	10AX, 250V~	T	
67907					A	10AX, 250V~	T	Locator
67908					4 x A	10AX, 250V~	T	
67912	ARM67912				B + H	6A, 250V~	TM	
67915	ARM67915				B	6A, 250V~	TM	
67917					B	6A, 250V~	TM	Locator

T : Toggle, TM : Momentary Toggle

All the commercial references listed above may be supplemented with a prefix of type LG-, BT-, ... (to indicate the brand) and/or suffix of type 0, 1, 2, 3, 4, FI, EX, ...

Characteristics

Terminals :	Screw-type
Patern	6
Contact Opening (gap) :	Normal gap
Protection Degree :	IP20
Method of mounting :	Flush-type
Method of installation :	A or B, See table

Accessories

Reference	Designation	Univers	Finition
ARP7301	PLATE 1 GANG FOR TOGGLE	EPURE	BRONZE
ARP67302	PLATE 1 GANG 2 TOGGLES	EPURE	BRONZE
ARP67308	PLATE 2 GANG 2 TOGGLES	EPURE	BRONZE
ARP67401	PLATE 1 GANG FOR TOGGLE	EPURE	BRUSHED STEEL
ARP67402	PLATE 1 GANG 2 TOGGLES	EPURE	BRUSHED STEEL
ARP67408	PLATE 2 GANG 2 TOGGLES	EPURE	BRUSHED STEEL
ARP67801	PLATE 1 GANG FOR TOGGLE	EPURE	BLACK MAT
ARP67802	PLATE 1 GANG 2 TOGGLES	EPURE	BLACK MAT
ARP67808	PLATE 2 GANG 2 TOGGLES	EPURE	BLACK MAT
ARP67901	PLATE 1 GANG FOR TOGGLE	EPURE	WHITE SATIN
ARP67902	PLATE 1 GANG 2 TOGGLES	EPURE	WHITE SATIN
ARP67908	PLATE 2 GANG 2 TOGGLES	EPURE	WHITE SATIN