

AENOR

Confía

ENEC Certification Body registered under ID # 01. For further information, please consult www.enec.com

LICENCE

to use the European Mark



Licence Nr. ENEC/000910

Under the conditions given in the following pages of this document, the licence to use the ENEC Mark in conjunction with the suffix 01, as shown above, has been issued to:

LEGRAND GROUP ESPAÑA, S.L.
CL HIERRO, 56
28850 TORREJON DE ARDOZ (Madrid – España / Spain)

For the product(s):

LED luminaires for emergency lighting

Trade name(s):

LEGRAND

Complying with the following European Standards:

EN IEC 60598-1:2021; EN 60598-2-22:2014;
EN 60598-2-22:2014/A1:2020; EN 62262:2002

Date: 2022-11-08

Signature:

A handwritten signature in blue ink, appearing to read 'Rafael García'.

Name: Rafael García
Position: Chief Executive Officer

This licence has been issued under the presumption and conditional on the fact that the licensee holds all necessary legal rights with regard to the product presented for testing and certification.

AENOR INTERNACIONAL, S.A.U.
Cl Génova, 6
28004 MADRID (Spain)

CERTIFICATE OF THE ENEC EUROPEAN MARK

Type of Product	LED LUMINAIRES FOR EMERGENCY LIGHTING
r1) Certificate n°	ENEC/000910
r2) Date of the Certificate	2022-11-08
r3) report n°	2017010021B1, 2022070427B1
r4) Name and address of the licensee	LEGRAND GROUP ESPAÑA, S.L. CL HIERRO, 56 28850 TORREJON DE ARDOZ (Madrid - España / Spain)
r5) Address of the factory	ZA DES GREFFIÈRES; 1, RUE EUGÈNE FREEYSSINET F17140 LAGORD (Francia / France)
r6) European Standard	EN IEC 60598-1:2021; EN 60598-2-22:2014; EN 60598-2-22:2014/A1:2020; EN 62262:2002
r7) Type reference	See above for details
r8) Trade Mark	LEGRAND
r9) Rated voltage and frequency	230 V~; 50/60 Hz
r10) N° lamps x rated power, type and lampholder	See above for details
r11) IP degree of protection	IP 66; IK 08
r12) Power supply connection means	Bornes / terminals
r13) Classif. per holding surface material	Apta para superficies normalmente inflamables / suitable for normally flammable surfaces
r14) Protection against electric shocks (class)	Clase / class II
r15) Rated lumen output and duration	See above for details
r16) Battery features	See above for details
r17) Additional information	Con indicadores de estado / with state indicators; protección electrónica / electronic protection
r18) General data	See above for details
Date of expiry: 2025-04-30	This certificate supersedes certificate 007/000910, dated 2017-05-17.

CERTIFICATE OF THE ENEC EUROPEAN MARK

Type reference	N° lamps x rated power, type and lampholder	Rated lumen output and duration	Battery features	General data
661541	6 x 0,5 W; LED; módulo / panel	100 Lm - emergencia / emergency; 1 h	Ni-MH 2,4 V 2,2 Ah 2 elementos / cells	Permanente / maintained; puesta en reposo remota / remote rest. B-66
661543	6 x 0,5 W; LED; módulo / panel	250 Lm - emergencia / emergency; 1 h	Ni-MH 3,6 V 2,2 Ah 3 elementos / cells	Permanente / maintained; puesta en reposo remota / remote rest. B-66
661545	6 x 1 W; LED; módulo / panel	450 Lm - emergencia / emergency; 1 h	Ni-MH 7,2 V 2,2 Ah 6 elementos / cells	Permanente / maintained; puesta en reposo remota / remote rest. B-66
662543	6 x 0,5 W; LED; módulo / panel	250 Lm - emergencia / emergency; 1 h	Ni-MH 3,6 V 2,2 Ah 3 elementos / cells	Permanente / maintained; puesta en reposo remota / remote rest. B-66 LVS2
662545	6 x 1 W; LED; módulo / panel	450 Lm - emergencia / emergency; 1 h	Ni-MH 7,2 V 2,2 Ah 6 elementos / cells	Permanente / maintained; puesta en reposo remota / remote rest. B-66 LVS2