

## IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

## CB TEST CERTIFICATE

Product

Presence sensor switch  
(Automatic switch without neutral - 2 wires)

Name and address of the applicant

LEGRAND France  
128 Avenue du Maréchal de Lattre de Tassigny  
87045 Limoges Cedex  
France

Name and address of the manufacturer

LEGRAND France  
128 Avenue du Maréchal de Lattre de Tassigny  
87045 Limoges Cedex  
France

Name and address of the factory

Note: When more than one factory, please report on page 2

See additional page(s) for the listing of 6 factories

Ratings and principal characteristics

110 V ~ 75 W max or 240 V ~ 150 W max  
0,63 A max.  
50/60 Hz  
Standby consumption: < 0,010 W  
IP 20, IP44

Trademark / Brand (if any)

LEGRAND

Customer's Testing Facility (CTF) Stage used

N/A

Model / Type Ref.

CXG36  
For detailed Type nomenclature see additional page(s).

Additional information (if necessary may also be reported on page 2)

See additional page(s) for further Additional information.

For the accessories (cover plates, covers and boxes) and for the places of production for types and accessories see CB Test Report.

A sample of the product was tested and found to be in conformity with

IEC 60669-2-1:2021  
IEC 60669-1:2017  
See Test Report for National Differences

As shown in the Test Report Ref. No. which forms part of this Certificate

HU24CXG6 001

This CB Test Certificate is issued by the National Certification Body

TÜV Rheinland InterCert Kft., MEEI Division  
H-1143 Budapest, Gizella út 51-57., Hungary  
Web: www.tuv.com

Date: 2024-11-07

Signature:



Tötös Tamás László

**Additional information :**

Type nomenclature  
-----

Range	Override Function	Reference	Color	IP	Specifies
CELIANE	Without	0 488 96A	White	IP20	Complete product
	/	0 670 26A	/	IP20	Mechanism only
CELIANE	/	CM0050	/	IP20	Mechanism only
	Without	CB9050	White	IP20	Complete product
	With	CG0050	White	IP20	Complete product
		CX0050	White	IP20	Without cover plate
		CY0050	Titan.	IP20	Without cover plate
	CZ0050	Black	IP20	Without cover plate	
DOOXIE	Without	0 950 14A	White	IP20	Square complete prod.
		0 950 34A	Alum.	IP20	Square complete prod.
		0 950 54A	White	IP20	Round complete prod.
		0 950 74A	Alum.	IP20	Round complete prod.
		0 952 11A	White	IP20	Without cover plate
		0 952 41A	Alum.	IP20	Without cover plate
		0 952 71A	Black	IP20	Without cover plate
		6 000 64A	White	IP20	Without cover plate
		6 001 64A	Alum.	IP20	Without cover plate
		6 002 64A	Black	IP20	Without cover plate

< The list continues next page. >



Date: 2024-11-07

Signature:

as on page 1

**Additional information :**

Range	Override Function	Reference	Color	IP	Specifies	
MOSAIC	Without	0 784 58A	White	IP20	Without frame/cover pl.	
		0 792 47A	Alum.	IP20	Without frame/cover pl.	
		0 791 58LA	Black	IP20	Without frame/cover pl.	
	With	0 784 59A	White	IP20	Without frame/cover pl.	
		0 992 14A	White	IP20	Complete product	
		0 996 22A	White	IP20	Without frame/cover pl.	
	NILOE	Without	6 651 22A	White	IP20	Without cover plate
			6 652 22A	Ivory	IP20	Without cover plate
			6 653 22A	Alum.	IP20	Without cover plate
6 654 22A			Anthr.	IP20	Without cover plate	
6 657 22A			White	IP20	Without cover plate	
6 658 22A			Ivory	IP20	Without cover plate	
7 645 83A			White	IP20	Without cover plate	
7 646 83A			Ivory	IP20	Without cover plate	
7 647 83A			Narrow	IP20	Without cover plate	

< The list continues next page. >



Date: 2024-11-07

Signature:

as on page 1

**Additional information :**

Range	Override Function	Reference	Color	IP	Specifies
NILOE STEP	Without	3 982 05A	White	IP20	Complete product
		3 982 38A	White	IP20	Without cover plate
		3 982 39A	Alum.	IP20	Without cover plate
		3 982 40A	Black	IP20	Without cover plate
		7 621 83A	White	IP20	Without cover plate
		7 624 83A	Alum.	IP20	Without cover plate
		7 622 83A	Black	IP20	Without cover plate
		7 623 83A	Grey	IP20	Without cover plate
		8 631 48A	White	IP20	Without cover plate
		8 633 48A	Alum.	IP20	Without cover plate
		8 634 48A	Black	IP20	Without cover plate
		8 631 50A	White	IP20	Without cover plate
		8 633 50A	Alum.	IP20	Without cover plate
		8 635 50A	Black	IP20	Without cover plate
		8 634 50A	Grey	IP20	Without cover plate
		8 640 10A	/	IP20	Without cover/cover pl.
8 635 48A	White	IP20	Without cover plate		
ARTEOR	Without	5 740 09A	White	IP20	Without frame/cover pl.
		5 740 59A	Magne.	IP20	Without frame/cover pl.
CREO	With	7 757 72A	White	IP20	Without cover plate
NEPTUNE	Without	0 913 28A	White	IP20	Complete product
GALEA	With	7 756 72A	White	IP20	Without cover plate

< The list continues next page. >



Date: 2024-11-07

Signature:

as on page 1

**Additional information :**

Range	Override Function	Reference	Color	IP	Specifies
RAVENTI	Without	7 681 13A	White	IP20	Without cover plate
		7 682 13A	Black	IP20	Without cover plate
		7 683 13A	Grey	IP20	Without cover plate
		7 685 13A	White	IP20	Without cover plate
		7 686 13A	Black	IP20	Without cover plate
		7 688 13A	Grey	IP20	Without cover plate
		7 689 13A	Alum.	IP20	Without cover plate
SUNO	With	7 211 35A	White	IP44	Without cover plate
		7 213 35A	Alum.	IP44	Without cover plate
		7 214 35A	Black	IP44	Without cover plate
		7 211 76A	White	IP20	Without cover plate
		7 212 76A	Ivory	IP20	Without cover plate
		7 213 76A	Alum.	IP20	Without cover plate
		7 214 76A	Black	IP20	Without cover plate
VALENA	With	7 742 29A	White	IP20	Without cover plate
		7 741 29A	Ivory	IP20	Without cover plate
VALENA ALLURE	Without	7 527 70A	White	IP20	Without cover plate
		7 528 70A	Ivory	IP20	Without cover plate
		7 529 70A	Alum.	IP20	Without cover plate
VALENA INMATIC	/	7 520 70A	/	IP20	Without cover/cover pl.

< The list continues next page. >



Date: 2024-11-07

Signature:

as on page 1

**Additional information :**

Range	Override Function	Reference	Color	IP	Specifies		
VALENA LIFE	With	7 521 72A	White	IP20	Without cover plate		
		7 522 72A	Ivory	IP20	Without cover plate		
		7 523 72A	Alum.	IP20	Without cover plate		
	Without	7 521 77A	White	IP20	Without cover plate		
		7 522 70A	Ivory	IP20	Without cover plate		
		7 523 70A	Alum.	IP20	Without cover plate		
		7 563 73A	Black	IP20	Without cover plate		
		7 521 70A	White	IP20	Without cover plate		
		VALENA NEXT	Without	1 965 06A	White	IP20	Without cover plate
				1 965 26A	Alum.	IP20	Without cover plate
1 965 46A	Black			IP20	Without cover plate		
7 412 60A	White			IP20	Without cover plate		
7 413 60A	Alum.			IP20	Without cover plate		
7 414 60A	Black			IP20	Without cover plate		
7 415 62A	White			IP20	Without cover plate		
7 416 62A	Alum.			IP20	Without cover plate		
7 417 62A	Black			IP20	Without cover plate		
With	7 415 61A		White	IP20	Without cover plate		
7 416 61A	Alum.	IP20	Without cover plate				
7 417 61A	Black	IP20	Without cover plate				

< For details see CB Test Report. >



Date: 2024-11-07

Signature:

as on page 1

**Factories :**

1. LEGRAND France  
128 Avenue du Maréchal de Lattre de Tassigny  
87045 Limoges Cedex  
France
2. LEGRAND Magyarország Villamossági Rendszerek ZRt.  
Ipartelepi út 14.  
6600 Szentés  
Hungary
3. LEGRAND Elektrik Sanayi A.S.  
Gebze Organize Sanayi Bolgesi, Ihsan Dede Caddesi 112  
41480 Kocaeli  
Türkiye
4. LEGRAND  
BP 21 Avenue du Parc Alata  
60550 Verneuil-en-Halatte  
France
5. CARDONAPLAST SAU  
Pol. Ind. la Cort C/Forn 4-5  
08261 Cardona  
Spain
6. NOVATEUR ELECTRICAL & DIGITAL SYSTEMS PRIVATE LTD  
A-2, SINNAR - MALEGAON VILLAGE MIDC, NASHIK PUNE ROAD, NASHIK district,  
MAHARASHTRA. 422113  
India