

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Uninterruptible Power Systems

Name and address of the applicant

Legrand S.N.C.
128 Avenue de Lattre De Tassigny FR-87045, Limoges
Cedex - France

Name and address of the manufacturer

BTicino S.p.A. - Legrand Group
Viale Borri 231, IT-21100 Varese (VA), Italy

Name and address of the factory

PAD Elettronica
Viale Europa 22, IT-52018 Castel San Niccolò (AR), Italy*Note: When more than one factory, please report on page 2* Additional Information on page 2

Ratings and principal characteristics

See page 2

Trademark (if any)

Legrand

Customer's Testing Facility (CTF) Stage used

/

Model / Type Ref.

Keormod xxx kW;
where xxx: means the different type of power (could be
125 = 125 kW or 250 = 250 kW);Additional information (if necessary may also
be reported on page 2)

/

 Additional Information on page 2A sample of the product was tested and found
to be in conformity with

IEC 62040-1:2017

As shown in the Test Report Ref. No. which
forms part of this Certificate546/18/191528BT issued by laboratory Crei Ven on
2019-07-10

This CB Test Certificate is issued by the National Certification Body

SIQ Ljubljana, Tržaška cesta 2, SI-1000 Ljubljana, Slovenia
T +386 1 4778 100, F +386 1 4778 444, info@siq.si, www.siq.si

Date: 2019-07-11

Signature: Zoran Svetik

Ratings and principal characteristics:

Model	Input Ratings	Output Ratings	Battery In/Out
Keormod 125 kW	380/400/415 V _{AC} 3W+N+PE; 50/60 Hz; 235 A I _{cw} 10 kA	380/400/415 V _{AC} 3W+N+PE; 50/60 Hz; 180 A 125 kVA/125 kW	-264V _{DC} + 264V _{DC} to -312V _{DC} + 312V _{DC} 325 A
Keormod 250 kW	380/400/415 V _{AC} 3W+N+PE; 50/60 Hz; 470 A I _{cw} 10 kA	380/400/415 V _{AC} 3W+N+PE; 50/60 Hz; 360 A 250 kVA/250 kW	-264V _{DC} + 264V _{DC} to -312V _{DC} + 312V _{DC} 650 A

Additional information (if necessary)

Date: 2019-07-11

Signature: Zoran Svetik

