EÚ Vyhlásenie o zhode

vydané podľa zákona 56/2018 Z.z. o technických požiadavkách na výrobky a o posudzovaní zhody

Názov organizácie: **LEGRAND Slovensko, s.r.o.**
Adresa: **Panónska cesta 7, 851 04 BRATISLAVA**
IČO: **35835907**
IČ DPH: **SK2020287192**

Výrobca: **Legrand France**
128 Avenue du Marechal de Lattre de Tassigny
87045 Limoges Cedex

Výrobok: **Plexo™ Zásuvky 2P+T 16A-250V + príslušenstvo**
- obj.č.: - viď.príloha

Výrobca vyhlasuje, že

- uvedený výrobok je pri určenom použití bezpečný a prijaté opatrenia, ktorými je zabezpečená zhoda všetkých výrobkov uvádzaných na trh s technickou dokumentáciou, so základnými požiadavkami nariadení vlády, ktoré sa na ne vzťahujú a požiadavkami technických predpisov

- vlastnosti tohto výrobku spĺňajú technické požiadavky, ktoré sa na tento výrobok vzťahujú a ktoré sú uvedené v príslušných nariadeniach vlády, príp. v iných technických predpisoch

Posúdenie zhody bolo vykonané podľa:

európskych smerníc

- 2014/35/EU
o harmonizácii právnych predpisov členských štátov týkajúcich sa sprístupnenia elektrického zariadenia určeného na používanie v rámci určitých limitov napätia na trhu
- 2014/30/EU
o harmonizácii právnych predpisov členských štátov vzťahujúcich sa na elektromagnetickú kompatibilitu

a nariadení vlády SR

- č.325/2019 Z.z.
o sprístupňovaní elektrického zariadenia určeného na používanie v rámci určitých limitov napätia na trhu
- č.331/2019 Z.z.
o elektromagnetickej kompatibilite zariadení

Pri posudzovaní zhody boli použité tieto normy:

STN IEC 60884-1:2002(ed.3) + A1:2006 + A2:2013

Identifikácia: LCIE - Laboratoire Central des Industries Electriques
33, avenue du Général Leclerc, 92260 Fontenay-aux-Roses, France

Číslo certifikátu: FR_715939

Vyhlasovateľ:
Meno: Ján Hupka
Funkcia: General Manager Slovakia
Adresa: Mlynské Nivy 5, 821 09 Bratislava
Dátum: 14.8.2024

Podpis:

legrand
LEGRAND Slovensko, s.r.o.
Panónska cesta 7, 851 04 Bratislava
IČO: 35835907 IČ DPH: SK2020287192

Mechanisms

References	References Grey	References Whit	References Anthracite	References Sand	Function	Nominal characteristics	Type of terminals	Mounting	Specificity
MIFA	0 695 51L	0 696 21L	0 698 91L	0 698 28L	2P+T	16A 250V~	Screwless	/	mechanism only
	0 700 42		0 700 47		2P+T	16A 250V~	Screwless	/	mechanism only
			0 698 07L		2P+T	16A 250V~	Screwless	flush-type	mechanism only and marking flap
			0 700 77		2P+T	16A 250V~	Screwless	flush-type	mechanism only and marking flap
	0 697 31L	0 697 81L	0 697 91L	0 697 76L	2P+T	16A 250V~	Screwless	surface type	mechanism with box
			0 697 87L		2P+T	16A 250V~	Screwless	surface type	mechanism with box and marking flap
	0 700 03 0 700 04	0 700 24	0 700 27	0 700 69	2P+T	16A 250V~	Screwless	surface type	mechanism with box
	0 698 31L	0 698 70L	0 698 60L		2P+T	16A 250V~	Screwless	flush-type	mechanism with frame
	0 700 31	0 700 34	0 700 38	0 700 75	2P+T	16A 250V~	Screwless	flush-type	mechanism with claw frame
	0 693 98L				2P+T	16A 250V~	Screwless	/	mechanism only
	0 693 78L				2P+T	16A 250V~	Screwless	surface type	mechanism with box
	0 693 88L				2P+T	16A 250V~	Screwless	flush-type	mechanism with frame
MIFV	0 695 52L	0 696 24L	0 698 40L		2P+T	16A 250V~	Screw-type	/	mechanism only
/	0 695 53L	0 696 23L			2P+T	16A 250V~	Screw-type	/	mechanism only tamperproof
MIFA2H	0 695 62L	0 696 42L	0 698 42L		2 x 2P+T	16A 250V~	Screwless	/	mechanism only pre-wired
	0 697 68L	0 697 78L	0 697 88L		2 x 2P+T	16A 250V~	Screwless	surface type	mechanism pre-wired with box
	0 700 05	0 700 25	0 700 64		2 x 2P+T	16A 250V~	Screwless	surface type	mechanism pre-wired with box
	0 693 76L				2 x 2P+T	16A 250V~	Screwless	flush-type	mechanism pre-wired with frame
			0 697 49L		2 x 2P+T	16A 250V~	Screwless	surface type	garden piquet
MIFA3H	0 695 64L	0 696 44L	0 698 44L		3 x 2P+T	16A 250V~	Screwless	/	mechanism only pre-wired
	0 697 63L				3 x 2P+T	16A 250V~	Screwless	surface type	mechanism pre-wired with box
	0 700 14		0 700 66		3 x 2P+T	16A 250V~	Screwless	surface type	mechanism pre-wired with box
MIFA2V	0 695 63L	0 696 43L	0 698 43L		2 x 2P+T	16A 250V~	Screwless	/	mechanism only pre-wired
	0 700 13	0 700 18	0 700 65		2 x 2P+T	16A 250V~	Screwless	surface type	mechanism pre-wired with box

Accessories

References Grey	References White	References Anthracite	References Sand	Designation
0 696 51L	0 696 89L	0 696 01L	0 698 63L	box 1 gang with membrane cable gland
0 700 50		0 700 56		box 1 gang with membrane cable gland
0 696 72L	0 696 90L	0 696 02L	0 698 67L	box 2 gangs with membrane cable gland
0 700 51		0 700 57		box 2 gangs with membrane cable gland
0 696 80L	0 696 88L	0 696 03L		box 3 gangs with membrane cable gland
0 700 52		0 700 58		box 3 gangs with membrane cable gland
0 696 52L				box 1 gang with PG16 cable gland on the top
0 696 56L	0 696 86L	0 696 28L		box 1 gang with ISO20 cable gland on the top
0 698 46L				box 1 gang with 2 ISO20 cable gland on the top
0 696 68L	0 698 66L	0 696 10L		box 2 gangs vertical with 2 ISO20 cable gland on the top
0 695 96L				membrane cable gland 1 entry
0 695 99L				membrane cable gland 2 entries
0 696 65L				coupling cable gland
0 696 48L				PG16 cable gland 1 entry
0 696 50L				PG16 cable gland 2 entries
0 696 53L				PG16 cable gland
0 696 60L	0 696 62L	0 696 63L		ISO20 cable gland 1 entry
0 696 70L	0 696 71L	0 696 73L		ISO20 cable gland 2 entries
0 695 98L				set of 4 caps
0 696 81L	0 696 92L	0 696 06L	0 698 90L	frame 1 gang
0 696 83L	0 696 94L	0 696 07L	0 698 53L	frame 2 gangs
0 700 54		0 700 94		frame 2 gangs
0 696 87L	0 696 98L	0 696 08L		frame 3 gangs
0 700 90		0 700 95		frame 3 gangs
0 695 79L		0 698 45L		Mosaic / Arteor adaptator with smoked flap lockable
0 919 45				Security tool
0 695 80L	0 696 95L	0 698 80L	0 698 38L	Mosaic / Arteor adaptator with smoked flap
0 695 84L	0 696 84L	0 698 30L		Mosaic / Arteor adaptator with flap
0 695 82L				Mosaic / Arteor adaptator without flap