

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Box for accessories

Name and address of the applicant

LEGRAND FRANCE128, avenue du Maréchal de Lattre de Tassigny B.P. 523
87045 LIMOGES CEDEX - France

Name and address of the manufacturer

LEGRAND FRANCE128, avenue du Maréchal de Lattre de Tassigny B.P. 523
87045 LIMOGES CEDEX - France

Name and address of the factory

LEGRAND MAGYARORSZAG VILLAMOSSAGI RENDSZEREK ZRTIpartelepi ut 14 pf 10
6600 SZENTES - Hungary

Note: When more than one factory, please report on page 2

 Additional Information on page 2

Ratings and principal characteristics

450 V~, IP40 ; 850 °C
see Annex

Trademark (if any)

BTICINO

Customer's Testing Facility (CTF) Stage used

/

Model / Type Ref.

PB502N, PB503N, PB504N, PB506N, PB526N

Additional information (if necessary may also be reported on page 2)

 Additional Information on page 2


A sample of the product was tested and found to be in conformity with

IEC 60670-1:2002(ed.1) +A1:2011

As shown in the Test Report Ref. No. which forms part of this Certificate

147883-701672

This CB Test Certificate is issued by the National Certification Body

LCIE – Laboratoire Central des Industries Electriques
33, avenue du Général Leclerc – BP8
FR 92 266 Fontenay aux Roses Cedex
www.lcie.frLABORATOIRE CENTRAL DES
INDUSTRIES ELECTRIQUES
S.A.S au capital de 130745000 €
RCS Nanterre 4408363174
33 Avenue du Général Leclerc
F - 92266 FONTENAY AUX ROSES

Date: 05/05/2017

Signature: **Jean-François BRUEL**
Certification Officer

ANNEX

References, ratings and main characteristics:**Mechanisms**


References	Capacity	Depth (mm)	Diameter axes (mm)
	modules		
PB502N	2	50	71 x 71
PB503N	3	50	71 x 110
PB504N	4	50	71 x 132
PB506N	6	50	71 x 183
PB526N	3 + 3	50	111 x 116

Rated insulation voltage	450 V~
Nature of material	Insulating
Method of installation	Flush in :
	Hollow walls, hollow ceiling, hollow floors or furniture
	Placement :
	Suitable for all types of installation except into concrete
Type of inlets (outlets)	With inlets for plain or corrugated conduits
Clamping means	without clamping means
Minimum and maximum temperatures during installation	-5 °C to +60 °C
Boxes and enclosures for hollow walls	Degree of protection of the part mounted in the hollow wall : IP40
The provision of fixing accessories to boxes	Boxes intended to receive screws Boxes intended to receive other means
Glow-wire test made at	850 °C

For more information relating to the ratings and the main characteristics please refer to the CB Test Report: 147883-701672



LCIE – Laboratoire Central des Industries Electriques
33, avenue du Général Leclerc – BP8
FR 92 266 Fontenay aux Roses Cedex
www.lcie.fr



LABORATOIRE CENTRAL DES
INDUSTRIES ELECTRIQUES
S.A.S au capital de 13745000 €
RCS Nanterre 408363174
33 Avenue du Général Leclerc
F – 92266 FONTENAY AUX ROSES

Date: 05/05/2017

Signature: **Jean-François BRUEL**
Certification Officer