

IEC**IECEE**

®

™

Ref. Certif. No.

FR_714689

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Switches for fixed electrical installations combined with switched socket-outlet
SWITCHED SOCKET

Name and address of the applicant

Legrand Intelligent Electrical (Huizhou) Co., Ltd.
Bldg. B1-B3, East No. 39 Hechang 6th Rd., HZZK Hi-tech Industrial Development Zone, Huizhou, Guangdong, 516001 - CHINA

Name and address of the manufacturer

LEGRAND FRANCE
128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY
87045 LIMOGES CEDEX - FRANCE

Name and address of the factory

Legrand Intelligent Electrical (Huizhou) Co., Ltd.
Bldg. B1-B3, East No. 39 Hechang 6th Rd., HZZK Hi-tech Industrial Development Zone, Huizhou, Guangdong, 516001 - CHINA

Note: When more than one factory, please report on page 2

 Additional Information on page 2

Ratings and principal characteristics

See Annex

Trademark / Brand (if any)


tenby

Customer's Testing Facility (CTF) Stage used

/

Model / Type Ref.

See Annex

Additional information (if necessary may also be reported on page 2)

 Additional Information on page 2


A sample of the product was tested and found to be in conformity with

IEC 60884-1:2002(ed.3) +A1:2006 +A2:2013
IEC 60884-2-3:2006

As shown in the Test Report Ref. No. which forms part of this Certificate

ARLI-ESH-P22011269





This CB Test Certificate is issued by the National Certification Body

**LCIE**LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCEwww.lcie.frLABORATOIRE CENTRAL DES
INDUSTRIES ELECTRIQUES
S.A.S au capital de 15.745.984 €
RCS Nanterre B.408 363 174
33 avenue du Général Leclerc
F - 92266 FONTENAY AUX ROSESSignature: 
Julien GAUTHIER
Certification Officer

Date: 24/05/2022

ANNEX

References, ratings and main characteristics:


REFERENCE	TRADEMARK	DESCRIPTION	INSERT TYPE
618054		1 GANG BS 5A SINGLE POLE SWITCHED SOCKET	AG13283
838052	tenby	1 GANG BS 5A SINGLE POLE SWITCHED SOCKET	
618051		1 GANG BS 15A SINGLE POLE SWITCHED SOCKET	AG13111
618053		2 GANG BS 15A SINGLE POLE SWITCHED SOCKET	
618052		1 GANG BS 15A SINGLE POLE SWITCHED + NEON	
838055	tenby	1 GANG BS 15A SINGLE POLE SWITCHED SOCKET	

CLASSIFICATION

standard Sheet:	standard sheet of BS 546
rated current (A)	15A or 5A
rated voltage (V)	250V
degree of protection	IP20
provision for earthing	with earthing contact
method of connecting the cable	rewirable
type of terminals	screw-type
colour	White
socket-outlets	
multiple socket-outlets	15A : 1 or 2
number of socket-outlets	5A: 1
degree of protection against electric shock	normal protection
existence of shutters	with shutters
method of application - mounting	flush-type
method of installation	design A
Intended for circuits where	a single earthing circuit provides protective earthing
Switched socket-outlets without interlock	
According to the method of actuating the switch	rocker
According to the switching of the neutral	Unswitched neutral



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
 33 avenue du Général Leclerc
 92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr



Signature: 
Julien GAUTHIER
 Certification Officer

Date: 24/05/2022