Internal

Ref. Certif. No.

FR_725598

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	**Boxes and enclosures for electrical accessories for household and similar fixed electrical installations** Boxes and enclosures for electrical accessories
Name and address of the applicant	**LEGRAND FRANCE** 128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY 87045 LIMOGES CEDEX - FRANCE
Name and address of the manufacturer	**LEGRAND FRANCE** 128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY 87045 LIMOGES CEDEX - FRANCE
Name and address of the factory	
Note: *When more than one factory, please report on page 2*	☒ Additional Information on page 2
Ratings and principal characteristics	See Annex
Trademark / Brand (if any)	legrand
Customer's Testing Facility (CTF) Stage used	/
Model / Type Ref.	Series: BATIBOX masonry boxes References: See Annex
Additional information (if necessary may also be reported on page 2)	Supersedes CBTC FR_707397/A1 dated 09/12/2022. Update further to the evolution of the standard(s), modification and deleting references, change of factories site ☐ Additional Information on page 2
A sample of the product was tested and found to be in conformity with	IEC 60670-1:2024
As shown in the Test Report Ref. No. which forms part of this Certificate	TR N° 32674906-824869

This CB Test Certificate is issued by the National Certification Body

LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 13/10/2026

Signature: Julien GAUTHIER
Certification Officer

LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES
33 avenue du Général Leclerc
92260 FONTENAY AUX ROSES

ANNEX

Name and address of the factories:

ERP ELBROMPLAST
STRADA SIEMENS NR 3
300704 TIMISOARA – ROMANIA

MIO CONTO Kft.
ELEGE 72-76
6630 Mindszent
Csongrad – HUNGARY

LEGRAND FRANCE
128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY
87045 LIMOGES CEDEX – FRANCE

LEGRAND MAGYARORSZAG VILLAMOSSAGI RENDSZEREK ZRt
IPARTELEPI UT 14
6600 SZENTES - HUNGARY

ANNEX

References, ratings and main characteristics:

Mechanisms

Reference	Capacity Gang	Capacity modules	Depth (mm)	Dimension (mm)	Distance between centres (mm)	Specifity
0 801 40	-	1	40	35 x 74	-	-
0 801 49	-	3	40	67 x 113	-	-
0 801 55	1	-	50	70 x 136	-	-
0 801 84	1	-	40	85 x 85	-	-
0 905 38	1	-	40	85 x 85	-	-
0 801 85	1	-	50	85 x 85	-	-
0 801 31	1	-	30	71 x 71	-	joined
0 905 30	1	-	30	71 x 71	-	joined
0 801 41	1	-	40	71 x 71	-	joined
0 905 31	1	-	40	71 x 71	-	joined
0 801 17L	1	-	40	71 x 71	-	joined
0 801 70	1	-	40	71 x 71	-	for fixing on jamb
0 905 37	1	-	40	71 x 71	-	for fixing on jamb

LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 13/10/2026

Signature: **Julien GAUTHIER**
Certification Officer

LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES
RCS Nanterre B 408 363 174
33 avenue du Général Leclerc
F - 92266 FONTENAY AUX ROSES

ANNEX

Reference	Capacity Gang	Capacity modules	Depth (mm)	Dimension (mm)	Distance between centres (mm)	Specifity
0 801 51	1	-	50	71 x 71	-	joined
0 801 61	1	-	60	71 x 71	-	joined
391 996	1	-	60	71 x 71	-	joined
0 801 42	2	4/5	40	71 x 145	71	-
0 905 32	2	4/5	40	71 x 145	71	-
0 801 43	3	6/8	40	71 x 216	71	-
0 905 33	3	6/8	40	71 x 216	71	-
0 801 44	4	8/10	40	71 x 287	71	-

LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 13/10/2026

Signature: **Julien GAUTHIER**
Certification Officer

LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES
S.A.S. au capital de 15.745.984 €
33 avenue du Général Leclerc
F - 92266 FONTENAY AUX ROSES

ANNEX

Accessories

References	Designation / Function
0 800 71	Removable divider for multi-gang boxes depth 40mm
0 801 80	Round cover
0 905 80	Round cover
0 892 81	Square cover 85 mm
0 919 58	Square cover 85 mm
0 892 85	Square cover 100 mm
0 905 81	Square cover 100 mm
0 801 82	2 gang cover
0 801 99	Anti-plaster screen
0 801 97	Long screw 40 mm

Nature of material		Insulating
Method of installation	Flush type	Non-combustible walls, ceilings or floors
		Combustible walls, ceilings or floors
	Placement	Suitable for all types of installation except into concrete
Type of inlets (outlets)		With inlets for plain or corrugated conduits
Clamping means		Without clamping means
Minimum and maximum temperatures during installation		From -5°C to +60°C
The provision for fixing accessories to boxes		Boxes supplied with screws