

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Socket-outlets with side earthing contacts

Name and address of the applicant

LEGRAND Magyarország Villamossági Rendszerek ZRt.

Ipartelepi út 14. 6600 Szentes

Hungary

Name and address of the manufacturer

LEGRAND Magyarország Villamossági Rendszerek ZRt.

Ipartelepi út 14. 6600 Szentes

JOOU SZEIN

Hungary

Name and address of the factory

Ratings and principal characteristics

Note: When more than one factory, please report on page 2

LEGRAND Magyarország Villamossági Rendszerek ZRt.

Ipartelepi út 14. 6600 Szentes

Hungary

For new design (SEANO) types:

250 V~; 16 A

IP44 (SUS12 / 7 65x 24)

IP21 (SUS12 / 7 65x 23)

IP20 (for all other types)

Trademark / Brand (if any)

legrand

Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

SUS11, SUS12 and Tamper Proof with "SEANO" design For detailed type differences and designation see page 2 of this CB Test Certificate. For available accessories see CB Test Report.

Additional information (if necessary may also be reported on page 2)

See additional page(s) for further Additional information. This CB Test Certificate is modification No.1 for HU-004319, dated 2023-03-16 and it is issued due to additional new design: "SEANO".

In this CB Test Certificate only the new added types and their ratings have been listed.

A sample of the product was tested and found to be in conformity with

IEC 60884-1:2002+A1+A2

As shown in the Test Report Ref. No. which forms part of this Certificate

HU21DTFK 002

This CB Test Certificate is issued by the National Certification Body



TÜV Rheinland InterCert Kft., MEEI Division H-1143 Budapest, Gizella út 51-57., Hungary Web: www.tuv.com

Date: 2023-03-20

Tötös Tamás László

Signature:



Page 2 of 2

Additional information:

Type differences and designation:

Type reference: SUS12 (with "SEANO" design)
Designation: 2P+E socket-outlet with shutters

Type of term.: screwless

Re	ef. r	no.	Color	Degree	of
7	651	20	white	IP20	
7	652	20	aluminium	IP20	
7	653	20	black	IP20	
7	654	20	dark grey	IP20	
7	651	22	red	IP20	
7	652	22	green	IP20	
7	653	22	yellow	IP20	
7	654	22	orange	IP20	

Type reference: SUS12 (with "SEANO" design)

Designation: 2P+E socket-outlet with shutters and lid

prot.

Type of term.: screwless

Ref. no.	Color	Degree of prot.
7 651 24	white	IP44
7 652 24	aluminium	IP44
7 653 24	black	IP44
7 654 24	dark grey	IP44
7 651 23	white	IP21
7 652 23	aluminium	IP21
7 653 23	black	IP21
7 654 23	dark grey	IP21

Type reference: SUS11 (with "SEANO" design)

Designation: 2P+E socket-outlet without shutters

Type of term.: screwless

Ref. no. Color Degree of prot. 7 651 21 white IP20
7 652 21 aluminium IP20
7 653 21 black IP20
7 654 21 dark grey IP20

Type reference: Tamper proof (with "SEANO" design)
Designation: 2P+E socket-outlet with shutters

Type of term.: with screw

Ref. no. Color Degree of prot.

7 650 22 red IP20



Date: 2023-03-20 Signature:

Tötös Tamás László

16/65