



Ref. Certif. No.

FR_723021

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Electronic remote-control switch
CONNECTED LATCHING RELAY (Electronic remote switch for fixed-electrical installations)

Name and address of the applicant

LEGRAND FRANCE
128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY
87045 LIMOGES CEDEX
FRANCE

Name and address of the manufacturer

LEGRAND FRANCE
128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY
87045 LIMOGES CEDEX
FRANCE

Name and address of the factory

BTICINO SPA
4 VIA LUCIANO MANARE
22036 ERBA
ITALY

Note: When more than one factory, please report on page 2

☐ Additional Information on page 2

Ratings and principal characteristics

See Annex

Trademark / Brand (if any)



Customer's Testing Facility (CTF) Stage used

/

Model / Type Ref.

DRIVIA Series
See Annex

Additional information (if necessary may also be reported on page 2)

Supersedes CBTC FR_715670/A1 dated 22/11/2022. Update further to the evolution of the standard(s)
Addition of product reference

☐ Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 60669-1:2017
IEC 60669-2-1:2021

As shown in the Test Report Ref. No. which forms part of this Certificate

26180375-811280


This CB Test Certificate is issued by the National Certification Body



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 13/11/2025

Signature:



ANNEX

References, ratings and main characteristics:

TRADEMARK	RANGE	REFERENCES	PRO / DIY	DESIGNATION	MAKING UP
LEGRAND	DRIVIA	4 121 70	PRO	CONNECTED LATCHING RELAY	
		1 991 21	DIY	CONNECTED LATCHING RELAY	4 121 70

"All the commercial references listed above may be supplemented with a prefix of type LG-, BT-, ... (to indicate the brand) and/or suffix of type 0, 1, 2, 3, 4, FI, EX, ... In this case, the products are technically the same."

ACCESSORIES

TYPE REFERENCE	TRADEMARK	RANGE	REFERENCE	DESIGNATION
ZLG09	LEGRAND	DRIVIA	4 121 81	ZIGBEE GATEWAY

CHARACTERISTICS

Rated current (A) or (AX)	16A / 100-240V~
Rated frequency	50/60 Hz
Load controlled	Declared load
Pattern number	1
Contact opening (gap)	micro gap
Protection degree	IP20
Method of actuating	Push-button - other external influences
Method of mounting	Panel type on rail
Method of installation	Design A
Type of terminals	screw terminals - see declared capacity



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 13/11/2025

Signature:

