



Ref. Certif. No.

FR_719537

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Switches for household and similar fixed electrical installations

Switches for fixed-electrical installations

Name and address of the applicant

NOVATEUR ELECTRICAL & DIGITAL SYSTEMS PVT. LTD
A-2, MIDC AREA, MALEGAON VILLAGE, SINNAR, DIST.
NASHIK - 422113, MAHARASHTRA - INDIA

Name and address of the manufacturer

NOVATEUR ELECTRICAL & DIGITAL SYSTEMS PVT. LTD
A-2, MIDC AREA, MALEGAON VILLAGE, SINNAR, DIST.
NASHIK - 422113, MAHARASHTRA - INDIA

Name and address of the factory

Note: When more than one factory, please report on page 2

☒ Additional Information on page 2

Ratings and principal characteristics

See Annex

Trademark / Brand (if any)



Customer's Testing Facility (CTF) Stage used

/

Model / Type Ref.

See Annex

Additional information (if necessary may also be reported on page 2)

☐ Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 60669-1:2017

As shown in the Test Report Ref. No. which forms part of this Certificate

ADQW-ESH-P24041938

This CB Test Certificate is issued by the National Certification Body



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 26/07/2024



LABORATOIRE CENTRAL DES
INDUSTRIES ELECTRIQUES
S.A.S au capital de 15,745,984 €
RCS Nanterre B 408 363 174
33 avenue du Général Leclerc
F - 92266 FONTENAY AUX ROSES

Signature:
Julien GAUTHIER
Certification Officer

ANNEX

Name and address of the factories:

NOVATEUR ELECTRICAL & DIGITAL SYSTEMS PVT. LTD

A-2, MIDC AREA, MALEGAON VILLAGE, SINNAR, DIST. NASHIK - 422113, MAHARASHTRA - INDIA

LEGRAND

AVENUE DU PARC ALATA - 60550 VERNEUIL EN HALATTE - FRANCE

RAIS HASSAN SAADI Logistics Dubai

Jebel Ali Free Zone, P.O. Box 7 Dubai - United Arab Emirates

LEGRAND FRANCE

128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY, 87045 LIMOGES CEDEX - FRANCE

Legrand Intelligent Electrical (Huizhou) Co., Ltd.

Bldg. B1-B3, East No. 39 Hechang 6th Rd., HZZK Hi-tech Industrial Development Zone, Huizhou 516001, Guangdong - CHINA

References, ratings and main characteristics:

All the commercial references listed below may be supplemented with a prefix of type LG-, BT-, ... (to indicate the brand) and/or suffix of type 1, 2, 3, 4, FI, EX, ... In this case, the products are technically the same.

CLASSIC references					
	White	Titanium	Black		
Type reference	Commercial ref	Commercial ref	Commercial ref	Module	Specificities
A028996AA	AC22112MW	AC22112MT	AC22112MB	2	Bulb+MASTER Marking
	AC22115MW	AC22115MT	AC22115MB		

Characteristics of appliance	
Pattern number	6/2
Contact opening (gap)	normal gap
Protection of degree	IP20
Method of actuating	Rocker
Method of mounting	flush type
Method of installation	design A
Type fo terminals	screw type
Rated current (A) or (AX)	20AX
Rated voltage (V)	250V~




LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE

33 avenue du Général Leclerc

92260 Fontenay-aux-Roses, FRANCE

www.lcie.fr



Date: 26/07/2024

Signature: Julien GAUTHIER
Certification Officer

ANNEX

Frame


Commercial ref	Designation
A1402	1G 1 AND 2M BRITISH STD FRAME
A1403	1G 1 AND 2M BS FRAME W/ EARTH
A1404	1G 3M HORIZO/VERTICAL BS FRAME
A1408	2G 3M BS FRAME
A1409	2G 2 X 2M BS FRAME
A1406	3M IT/FR/SCH FRAME
A1407	6M IT/FR/SCH FRAME
A1401	2M PANEL MOUNTING SUPPORT
A1405	4M FR/SCH FRAME

Blank

Commercial ref			Designation
Matt White	Matt Titanium	Matt Black	
AC150MW	AC150MT	AC150MB	1 BLANK MODULE
AC153MW	AC153MT	AC153MB	2 BLANK MODULES
AC1501MW	AC1501MT	AC1501MB	1G BS BLANKING PLATE
AC1502MW	AC1502MT	AC1502MB	2G BS BLANKING PLATE



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr



Date: 26/07/2024

Signature: **Julien GAUTHIER**
Certification Officer


ANNEX

Cover plates

Commercial ref									
Matt White	Matt Titanium	Matt Black	Frosted White	Frosted Black	Dark Aluminium	Brushed Stainless Steel	Night Blue	Solid Aluminium	Designation
AC1104 MW	AC1104 MT	AC1104 MB	AC1104 FW	AC1104 FB	AC1104D A	AC1104BS	AC1104NB	AC1104S A	1G 3M BS HORIZ/VERT PLATE
AC1105 MW	AC1105 MT	AC1105 MB	AC1105 FW	AC1105 FB	AC1105D A	AC1105BS	AC1105NB	AC1105S A	3M BS PLATE FOR 2G BOX
AC1107 MW	AC1107 MT	AC1107 MB	AC1107 FW	AC1107 FB	AC1107D A	AC1107BS	AC1107NB	AC1107S A	3M IT/US PLATE
AC1108 MW	AC1108 MT	AC1108 MB	AC1108 FW	AC1108 FB	AC1108D A	AC1108BS	AC1108NB	AC1108S A	2 X 2M BS PLATE
AC1110 MW	AC1110 MT	AC1110 MB	AC1110 FW	AC1110 FB	AC1110D A	AC1110BS	AC1110NB	AC1110S A	4M IT/FR/SCH PLATE
AC1111 MW	AC1111 MT	AC1111 MB	AC1111 FW	AC1111 FB	AC1111D A	AC1111BS	AC1111NB	AC1111S A	6M IT/FR/SCH PLATE
AC1201 MW	AC1201 MT	AC1201 MB	AC1201 FW	AC1201 FB	AC1201D A	AC1201BS	AC1201NB	AC1201S A	2M PLATE+FRAME
AC1202 MW	AC1202 MT	AC1202 MB	AC1202 FW	AC1202 FB	AC1202D A	AC1202BS	AC1202NB	AC1202S A	3M PLATE+FRAME
AC1203 MW	AC1203 MT	AC1203 MB	AC1203 FW	AC1203 FB	AC1203D A	AC1203BS	AC1203NB	AC1203S A	4M PLATE+FRAME
AC1204 MW	AC1204 MT	AC1204 MB	AC1204 FW	AC1204 FB	AC1204D A	AC1204BS	AC1204NB	AC1204S A	6M BS PLATE+FRAME
AC1205 MW	AC1205 MT	AC1205 MB	AC1205 FW	AC1205 FB	AC1205D A	AC1205BS	AC1205NB	AC1205S A	6M PLATE+FRAME
AC1206 MW	AC1206 MT	AC1206 MB	AC1206 FW	AC1206 FB	AC1206D A	AC1206BS	AC1206NB	AC1206S A	8M PLATE+FRAME
AC1207 MW	AC1207 MT	AC1207 MB	AC1207 FW	AC1207 FB	AC1207D A	AC1207BS	AC1207NB	AC1207S A	8M PLATE+FRAME
AC1208 MW	AC1208 MT	AC1208 MB	AC1208 FW	AC1208 FB	AC1208D A	AC1208BS	AC1208NB	AC1208S A	2 X 4M PLATE+FRAME
AC1209 MW	AC1209 MT	AC1209 MB	AC1209 FW	AC1209 FB	AC1209D A	AC1209BS	AC1209NB	AC1209S A	2 X 6M BS PLATE+FRAME
AC1210 MW	AC1210 MT	AC1210 MB	AC1210 FW	AC1210 FB	AC1210D A	AC1210BS	AC1210NB	AC1210S A	2 X 6M PLATE+FRAME
AC1211 MW	AC1211 MT	AC1211 MB	---	---	---	---	---	---	3 X 6M PLATE+FRAME
---	---	---	AB1100 FW	AB1100 FB	AB1100D A	AB1100BS	AB1100NB	AB1100S A	4M HYBRID PLATE 2M + 2M SWITCH
---	---	---	AB1200 FW	AB1200 FB	AB1200D A	AB1200BS	AB1200NB	AB1200S A	6M HYBRID PLATE 3M + 2M DIMMER
---	---	---	AB1201 FW	AB1201 FB	AB1201D A	AB1201BS	AB1201NB	AB1201S A	6M HYBRID PLATE 3M + 2M SWITCH
---	---	---	AB1202 FW	AB1202 FB	AB1202D A	AB1202BS	AB1202NB	AB1202S A	6M HYBRID PLATE+FRAM 3M+2M DIM
---	---	---	AB1203 FW	AB1203 FB	AB1203D A	AB1203BS	AB1203NB	AB1203S A	6M HYBRID PLATE+FRAM 3M +2M SW
---	---	---	AB1204 FW	AB1204 FB	AB1204D A	AB1204BS	AB1204NB	AB1204S A	6M HYBRID PLATE 4M + 1M SWITCH
---	---	---	AB1205 FW	AB1205 FB	AB1205D A	AB1205BS	AB1205NB	AB1205S A	6M HYBRID PLATE+FRAME 4M+1M SW
---	---	---	AB1206 FW	AB1206 FB	AB1206D A	AB1206BS	AB1206NB	AB1206S A	8M HYBRID PLATE 5M +2M DIMMER
---	---	---	AB1207 FW	AB1207 FB	AB1207D A	AB1207BS	AB1207NB	AB1207S A	8M HYBRID PLATE+FRAM 5M+2M DIM
AC1118 MW	AC1118 MT	AC1118 MB	AC1118 FW	AC1118 FB	AC1118D A	AC1118BS	AC1118NB	AC1118S A	4X4 US PLATE FOR 2M
AC1212 MW	AC1212 MT	AC1212 MB	---	---	---	---	---	---	9M PLATE+FRAME
AC1213 MW	AC1213 MT	AC1213 MB	---	---	---	---	---	---	2 X 8M PLATE+FRAME
---	---	---	AB1208 FW	AB1208 FB	AB1208D A	AB1208BS	AB1208NB	AB1208S A	4M HYBRID PLATE+FRAME 2M + 2M SWITCH



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr



Signature: *Julien GAUTHIER*
Certification Officer

Date: 26/07/2024


ANNEX

Pattern number	6/2
Contact opening	normal gap
Protection degree	IP20
Method of actuating	Rocker
Method of mounting	flush-type
Method of installation	design A
Type of terminals	screw-type (rigid and flexible)
Flexible cable outlet	without
Ratings	20AX 250V~
Color	White, Titanium, Black



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 26/07/2024



Signature: **Julien GAUTHIER**
Certification Officer