

**IEC****IECEE**

Ref. Certif. No.

**FR\_716965****IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME****CB TEST CERTIFICATE**

Product

**AC electric vehicle conductive charging station**

Name and address of the applicant

**LEGRAND FRANCE**  
6, rue Paul Nouel  
76770 MALAUNAY  
FRANCE

Name and address of the manufacturer

**LEGRAND FRANCE**  
6, rue Paul Nouel  
76770 MALAUNAY  
FRANCE

Name and address of the factory

**LEGRAND FRANCE**  
6, rue Paul Nouel  
76770 MALAUNAY  
FRANCE

Note: When more than one factory, please report on page 2

 Additional Information on page 2

Ratings and principal characteristics

See Annex

Trademark / Brand (if any)



Customer's Testing Facility (CTF) Stage used

CTF2

Model / Type Ref.

Green'up Premium IP44  
References: see Annex

Additional information (if necessary may also be reported on page 2)

Supersedes CBTC FR\_715814 dated 2022/10/26.  
Addition of alternative critical components. Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 61851-1:2017

As shown in the Test Report Ref. No. which forms part of this Certificate

13437431-775587-A V03

This CB Test Certificate is issued by the National Certification Body

LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE  
33 avenue du Général Leclerc  
92260 Fontenay-aux-Roses, FRANCE  
[www.lcie.fr](http://www.lcie.fr)

Date: 26/05/2023

LABORATOIRE CENTRAL DES  
INDUSTRIES ELECTRIQUES  
S.A.S au capital de 15.745.984 €  
RCS Nanterre R 918 361 174  
33 avenue du Général Leclerc  
F - 92266 FONTENAY AUX ROSESSignature:   
Julien GAUTHIER  
Certification Officer

## ANNEX

### Ratings and main characteristics

|                         |                            |
|-------------------------|----------------------------|
| Equipment mobility      | Stationary                 |
| Connection to the mains | Permanent connection       |
| EV charging modes       | Modes 1, 2 and 3           |
| Type of EV connection   | Case A, B                  |
| Access location         | Restricted access location |
| Over voltage category   | OVC III                    |
| Supply voltage          | 195 V to 265 V             |
| Frequency               | 50/60 Hz                   |
| Class of equipment      | Class I                    |
| Pollution degree        | PD 3                       |
| IP protection class     | IP 44                      |


### Product References

| Green' up Premium IP 44 plastic charging station |                  |                           |               |                  |        |                      |                      |               |                        |
|--|------------------|---------------------------|---------------|------------------|--------|----------------------|----------------------|---------------|------------------------|
| Charging mode                                    | Power            | Number of charging points | Socket outlet |                  |        | Rated Current Mode 2 | Rated current Mode 3 | Wall mounting | Free standing          |
|  |                  |                           | Mode 3        | Mode 2           |        |                      |                      |               |                        |
|  |                  |                           | Type 2        | GUA Franco/Belge | Shucko |                      |                      |               |                        |
| Mode 3   | 3.7 kW<br>4.6 kW | 1                         | 1             | -                | -      | -                    | 16A/20A Mono         | 0 580 00      | 0 580 00 +<br>0 590 52 |
| Mode 3   | 5.7 kW<br>7.4 kW | 1                         | 1             | -                | -      | -                    | 25A/32A Mono         | 0 580 01      | 0 580 01 +<br>0 590 52 |
| Mode 3   | 11/17/<br>22 kW  | 1                         | 1             | -                | -      | -                    | 16/25/<br>32 A Tri   | 0 580 02      | 0 580 02 +<br>0 590 52 |
| Mode 2 & 3                                       | 3.7 kW<br>4.6 kW | 1                         | 1             | 1                | -      | 16A                  | 16A/20A Mono         | 0 580 03      | 0 580 03 +<br>0 590 52 |
| Mode 2 & 3                                       | 5.7 kW<br>7.4 kW | 1                         | 1             | 1                | -      | 16A                  | 25A/32A Mono         | 0 580 04      | 0 580 04 +<br>0 590 52 |
| Mode 2 & 3                                       | 3.7 kW<br>4.6 kW | 1                         | 1             | -                | 1      | 16A                  | 16A/20A Mono         | 0 580 30      | 0 580 30 +<br>0 590 52 |
| Mode 2 & 3                                       | 5.7 kW<br>7.4 kW | 1                         | 1             | -                | 1      | 16A                  | 25A/32A Mono         | 0 580 35      | 0 580 35 +<br>0 590 52 |
| Mode 3   | 3.7 kW<br>4.6 kW | 1                         | 1             | -                | -      | -                    | 16A/20A Mono         | 0 590 05      | 0 590 05 +<br>0 590 52 |
| Mode 3   | 5.7 kW<br>7.4 kW | 1                         | 1             | -                | -      | -                    | 25A/32A Mono         | 0 590 06      | 0 590 06 +<br>0 590 52 |
| Mode 3   | 11/17/<br>22 kW  | 1                         | 1             | -                | -      | -                    | 16/25/<br>32 A Tri   | 0 590 07      | 0 590 07 +<br>0 590 52 |
| Mode 2 & 3                                       | 3.7 kW<br>4.6 kW | 1                         | 1             | 1                | -      | 16A                  | 16A/20A Mono         | 0 590 08      | 0 590 08 +<br>0 590 52 |
| Mode 2 & 3                                       | 5.7 kW<br>7.4 kW | 1                         | 1             | 1                | -      | 16A                  | 25A/32A Mono         | 0 590 09      | 0 590 09 +<br>0 590 52 |
| Mode 2 & 3                                       | 3.7 kW<br>4.6 kW | 1                         | 1             | -                | 1      | 16A                  | 16A/20A Mono         | 0 590 70      | 0 590 70 +<br>0 590 52 |
| Mode 2 & 3                                       | 5.7 kW<br>7.4 kW | 1                         | 1             | -                | 1      | 16A                  | 25A/32A Mono         | 0 590 71      | 0 590 71 +<br>0 590 52 |



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE  
 33 avenue du Général Leclerc  
 92260 Fontenay-aux-Roses, FRANCE  
[www.lcie.fr](http://www.lcie.fr)

Date: 26/05/2023



Signature: *Julien GAUTHIER*  
 Certification Officer