

LICENCE

to use the European Mark



Licence Nr. ENEC/000992

Under the conditions given in the following pages of this document, the licence to use the ENEC Mark in conjunction with the suffix 01, as shown above, has been issued to:

LEGRAND GROUP ESPAÑA, S.L.
CL HIERRO, 56
28850 TORREJON DE ARDOZ (Madrid – España / Spain)

For the product(s):

LED luminaires for emergency lighting

Trade name(s):

LEGRAND

Complying with the following European Standards:

EN IEC 60598-1:2021; EN 60598-2-22:2014;
EN 60598-2-22:2014/A1:2020;
EN 62262:2002

Date: 2023-04-10

Signature:

A handwritten signature in blue ink, appearing to read 'Rafael García'.

Name: Rafael García
Position: Chief Executive Officer

This licence has been issued under the presumption and conditional on the fact that the licensee holds all necessary legal rights with regard to the product presented for testing and certification.

CERTIFICATE OF THE ENEC EUROPEAN MARK

Type of Product	LED LUMINAIRES FOR EMERGENCY LIGHTING
r1) Certificate nº	ENEC/000992
r2) Date of the Certificate	2023-04-10
r3) report nº	2023020067B1
r4) Name and address of the licensee	LEGRAND GROUP ESPAÑA, S.L. CL HIERRO, 56 28850 TORREJON DE ARDOZ (Madrid - España / Spain)
r5) Address of the factory	CL HIERRO, 56 28850 TORREJON DE ARDOZ (Madrid - España / Spain)
r6) European Standard	EN IEC 60598-1:2021; EN 60598-2-22:2014; EN 60598-2-22:2014/A1:2020; EN 62262:2002
r7) Type reference	See above for details
r8) Trade Mark	LEGRAND
r9) Rated voltage and frequency	See above for details
r10) Nº lamps x rated power, type and lampholder	See above for details
r11) IP degree of protection	IP42; IK 07
r12) Power supply connection means	Bornes / terminals
r13) Classif. per holding surface material	Apta para superficies normalmente inflamables / suitable for normally flammable surfaces
r14) Protection against electric shocks (class)	Clase / class II
r15) Rated lumen output and duration	See above for details
r16) Battery features	See above for details
r17) Additional information	See above for details
r18) General data	See above for details
Date of expiry: 2026-06-30	This certificate supersedes certificate 007/000992, dated 2021-07-20.

CERTIFICATE OF THE ENEC EUROPEAN MARK

Type reference	Rated voltage and frequency	N° lamps x rated power, type and lampholder	Rated lumen output and duration	Battery features	Additional information	General data
660601	230 V~; 50/60 Hz	LED 2 x 0,25 W	70 lm - 1 h	2,4 V 0,8 Ah NiCd 2 elementos / cells	No permanente / non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. URA-21 Autotest
660602	230 V~; 50/60 Hz	LED 2 x 0,25 W	100 lm - 1 h	2,4 V 0,8 Ah NiCd 2 elementos / cells	No permanente / non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. URA-21 Autotest
660608	230 V~; 50/60 Hz	LED 4 x 0,25 W	200 lm - 1 h	2,4 V 1,5 Ah NiCd 2 elementos / cells	No permanente / non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. URA-21 Autotest
660609	230 V~; 50/60 Hz	LED 4 x 2 W	350 lm - 1 h	3,6 V 1,5 Ah NiCd 3 elementos / cells	No permanente / non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. URA-21 Autotest
660611	230 V~; 50/60 Hz	LED 2 x 0,25 W	100 lm - 3 h	3,6 V 1,5 Ah NiCd 3 elementos / cells	No permanente / non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. URA-21 Autotest
660612	230 V~; 50/60 Hz	LED 4 x 0,25 W	200 lm - 2 h	4,8 V 1,5 Ah NiCd 4 elementos / cells	No permanente / non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. URA-21 Autotest
660613	230 V~; 50/60 Hz	LED 4 x 2 W	350 lm - 2 h	4,8 V 2 Ah NiMH 4 elementos / cells	No permanente / non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. URA-21 Autotest
660614	230 V~; 50/60 Hz	LED 4 x 1 W	500 lm - 1 h	4,8 V 2 Ah NiMH 4 elementos / cells	No permanente / non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. URA-21 Autotest
661601E	230 V~; 50/60 Hz	LED 2 x 0,25 W	70 lm - 1 h	2,4 V 0,8 Ah NiCd 2 elementos / cells	No permanente / non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. URA-21

CERTIFICATE OF THE ENEC EUROPEAN MARK

Type reference	Rated voltage and frequency	N° lamps x rated power, type and lampholder	Rated lumen output and duration	Battery features	Additional information	General data
661601	230 V~; 50/60 Hz	LED 2 x 0,25 W	70 lm - 1 h	2,4 V 0,8 Ah NiCd 2 elementos / cells	No permanente / non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. URA-21
661602E	230 V~; 50/60 Hz	LED 2 x 0,25 W	100 lm - 1 h	2,4 V 0,8 Ah NiCd 2 elementos / cells	No permanente / non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. URA-21
661602	230 V~; 50/60 Hz	LED 2 x 0,25 W	100 lm - 1 h	2,4 V 0,8 Ah NiCd 2 elementos / cells	No permanente / non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. URA-21
661603E	230 V~; 50/60 Hz	LED 4 x 0,5 W	100 lm - 1 h	2,4 V 1,5 Ah NiCd 2 elementos / cells	Permanente, posible no permanente / maintained, possible non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. URA-21
661603	230 V~; 50/60 Hz	LED 4 x 0,5 W	100 lm - 1 h	2,4 V 1,5 Ah NiCd 2 elementos / cells	Permanente, posible no permanente / maintained, possible non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. URA-21
661605E	230 V~; 50/60 Hz	LED 4 x 0,25 W	160 lm - 1 h	3,6 V 1,5 Ah NiCd 3 elementos / cells	No permanente / non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. URA-21
661605	230 V~; 50/60 Hz	LED 4 x 0,25 W	160 lm - 1 h	3,6 V 1,5 Ah NiCd 3 elementos / cells	No permanente / non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. URA-21
661606E	230 V~; 50/60 Hz	LED 4 x 1 W	200 lm - 1 h	3,6 V 1,5 Ah NiCd 3 elementos / cells	Permanente, posible no permanente / maintained, possible non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. URA-21
661606	230 V~; 50/60 Hz	LED 4 x 1 W	200 lm - 1 h	3,6 V 1,5 Ah NiCd 3 elementos / cells	Permanente, posible no permanente / maintained, possible non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. URA-21
661607E	230 V~; 50/60 Hz	LED 4 x 1 W	350 lm - 1 h	4,8 V 1,5 Ah NiCd 4 elementos / cells	Permanente, posible no permanente / maintained, possible non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. URA-21

CERTIFICATE OF THE ENEC EUROPEAN MARK

Type reference	Rated voltage and frequency	Nº lamps x rated power, type and lampholder	Rated lumen output and duration	Battery features	Additional information	General data
661607	230 V~; 50/60 Hz	LED 4 x 1 W	350 lm - 1 h	4,8 V 1,5 Ah NiCd 4 elementos / cells	Permanente, posible no permanente / maintained, possible non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. URA-21
661608E	230 V~; 50/60 Hz	LED 4 x 1 W	200 lm - 1 h	3,6 V 1,5 Ah NiCd 3 elementos / cells	No permanente / non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. URA-21
661608	230 V~; 50/60 Hz	LED 4 x 1 W	200 lm - 1 h	3,6 V 1,5 Ah NiCd 3 elementos / cells	No permanente / non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. URA-21
661609E	230 V~; 50/60 Hz	LED 4 x 1 W	350 lm - 1 h	4,8 V 1,5 Ah NiCd 4 elementos / cells	No permanente / non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. URA-21
661609	230 V~; 50/60 Hz	LED 4 x 1 W	350 lm - 1 h	4,8 V 1,5 Ah NiCd 4 elementos / cells	No permanente / non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. URA-21
661610	230 V~; 50/60 Hz	LED 4 x 0,5 W	100 lm - 3 h	4,8 V 2,0 Ah NiMH 4 elementos / cells	Permanente, posible no permanente / maintained, possible non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. URA-21
661611	230 V~; 50/60 Hz	LED 2 x 1 W	90 lm - 3 h	3,6 V 1,5 Ah NiCd 3 elementos / cells	No permanente / non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. URA-21
661612	230 V~; 50/60 Hz	LED 4 x 1 W	200 lm - 2 h	4,8 V 2,0 Ah NiMH 4 elementos / cells	Permanente, posible no permanente / maintained, possible non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. URA-21
661614	230 V~; 50/60 Hz	LED 4 x 1 W	500 lm - 1 h	4,8 V 1,5 Ah NiCd 4 elementos / cells	No permanente / non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. URA-21
661615	230 V~; 50/60 Hz	LED 4 x 1 W	500 lm - 1 h	4,8 V 1,5 Ah NiCd 4 elementos / cells	Permanente / maintained, no permanente / non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. URA-21

CERTIFICATE OF THE ENEC EUROPEAN MARK

Type reference	Rated voltage and frequency	N° lamps x rated power, type and lampholder	Rated lumen output and duration	Battery features	Additional information	General data
661617	120 V~; 50/60 Hz	LED 4 x 0,25 W	160 lm - 1 h	3,6 V 1,5 Ah NiCd 3 elementos / cells	No permanente / non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. URA-21 120 VAC
661618	120 V~; 50/60 Hz	LED 4 x 1 W	350 lm - 1 h	4,8 V 1,5 Ah NiCd 4 elementos / cells	No permanente / non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. URA-21 120 VAC
662603	230 V~; 50/60 Hz	LED 4 x 0,5 W	100 lm - 1 h	3,6 V 1,5 Ah NiCd 3 elementos / cells	Permanente, posible no permanente / maintained, possible non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. URA-21 LVS
662606	230 V~; 50/60 Hz	LED 4 x 1 W	200 lm - 1 h	4,8 V 1,5 Ah NiCd 4 elementos / cells	Permanente, posible no permanente / maintained, possible non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. URA-21 LVS
662607	230 V~; 50/60 Hz	LED 4 x 1 W	350 lm - 1 h	4,8 V 2,0 Ah NiMH 4 elementos / cells	Permanente, posible no permanente / maintained, possible non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. URA-21 LVS
662610	230 V~; 50/60 Hz	LED 4 x 0,5 W	100 lm - 3 h	4,8 V 2,0 Ah NiMH 4 elementos / cells	Permanente, posible no permanente / maintained, possible non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. URA-21 LVS
662612	230 V~; 50/60 Hz	LED 4 x 1 W	200 lm - 2 h	4,8 V 2,0 Ah NiMH 4 elementos / cells	Permanente, posible no permanente / maintained, possible non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. URA-21 LVS
662613	230 V~; 50/60 Hz	LED 4 x 1 W	350 lm - 2 h	4,8 V 2,0 Ah NiMH 4 elementos / cells	Permanente, posible no permanente / maintained, possible non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. URA-21