

AENOR

Confía

ENEC Certification Body registered under ID # 01. For further information, please consult www.enec.com

LICENCE

to use the European Mark



Licence Nr. ENEC/000994

Under the conditions given in the following pages of this document, the licence to use the ENEC Mark in conjunction with the suffix 01, as shown above, has been issued to:

LEGRAND GROUP ESPAÑA, S.L.
CL HIERRO, 56
28850 TORREJON DE ARDOZ (Madrid – España / Spain)

For the product(s):

LED luminaires for emergency lighting

Trade name(s):

LEGRAND

Complying with the following European Standards:

EN 60598-2-22:2014; EN 60598-2-22:2014/A1:2020
EN IEC 60598-1:2021
EN 62262:2002

Date: 2022-11-03

Signature:

A handwritten signature in blue ink, appearing to read 'Rafael García', with a long horizontal stroke extending to the right.

Name: Rafael García
Position: Chief Executive Officer

This licence has been issued under the presumption and conditional on the fact that the licensee holds all necessary legal rights with regard to the product presented for testing and certification.

AENOR INTERNACIONAL, S.A.U.
Cl Génova, 6
28004 MADRID (Spain)

CERTIFICATE OF THE ENEC EUROPEAN MARK

Type of Product	LED LUMINAIRES FOR EMERGENCY LIGHTING
r1) Certificate n°	ENEC/000994
r2) Date of the Certificate	2022-11-03
r3) report n°	2016120782B1, 2019040178B1, 2020040168B1-M1, 2022070429B1
r4) Name and address of the licensee	LEGRAND GROUP ESPAÑA, S.L. CL HIERRO, 56 28850 TORREJON DE ARDOZ (Madrid - España / Spain)
r5) Address of the factory	CL HIERRO, 56 28850 TORREJON DE ARDOZ (Madrid - España / Spain)
r6) European Standard	EN 60598-2-22:2014; EN 60598-2-22:2014/A1:2020 EN IEC 60598-1:2021 EN 62262:2002
r7) Type reference	See above for details
r8) Trade Mark	LEGRAND
r9) Rated voltage and frequency	See above for details
r10) N° lamps x rated power, type and lampholder	See above for details
r11) IP degree of protection	IP 42; IK 07
r12) Power supply connection means	Bornes / terminals
r13) Classif. per holding surface material	Apta para superficies normalmente inflamables / suitable for normally flammable surfaces
r14) Protection against electric shocks (class)	Clase / class II
r15) Rated lumen output and duration	See above for details
r16) Battery features	See above for details
r17) Additional information	See above for details
r18) General data	See above for details
Date of expiry: 2025-04-30	This certificate supersedes certificate 007/000994, dated 2020-11-16.

CERTIFICATE OF THE ENEC EUROPEAN MARK

Type reference	Rated voltage and frequency	N° lamps x rated power, type and lampholder	Rated lumen output and duration	Battery features	Additional information	General data
660620	230 V~; 50/60 Hz	LED 2 x 0,25 W	70 lm - 1 h	2,4 V 0,8 Ah NiCd 2 elementos / cells	No permanente / non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. URA-ONE Autotest
660621	230 V~; 50/60 Hz	LED 2 x 0,25 W	100 lm - 1 h	2,4 V 0,8 Ah NiCd 2 elementos / cells	No permanente / non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. URA-ONE Autotest
660623	230 V~; 50/60 Hz	LED 4 x 0,25 W	200 lm - 1 h	2,4 V 1,5 Ah NiCd 2 elementos / cells	No permanente / non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. URA-ONE Autotest
660624	230 V~; 50/60 Hz	LED 4 x 2 W	350 lm - 1 h	3,6 V 1,5 Ah NiCd 3 elementos / cells	No permanente / non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. URA-ONE Autotest
660625	230 V~; 50/60 Hz	LED 4 x 1 W	500 lm - 1 h	4,8 V 2,0 Ah NiMH 4 elementos / cells	No permanente / non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. URA-ONE Autotest
661620	230 V~; 50/60 Hz	LED 2 x 0,25 W	70 lm - 1 h	2,4 V 0,8 Ah NiCd 2 elementos / cells	No permanente / non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. URA-ONE

CERTIFICATE OF THE ENEC EUROPEAN MARK

Type reference	Rated voltage and frequency	N° lamps x rated power, type and lampholder	Rated lumen output and duration	Battery features	Additional information	General data
661621	230 V~; 50/60 Hz	LED 2 x 0,25 W	100 lm - 1 h	2,4 V 0,8 Ah NiCd 2 elementos / cells	No permanente / non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. URA-ONE
661622	230 V~; 50/60 Hz	LED 4 x 0,25 W	160 lm - 1 h	3,6 V 1,5 Ah NiCd 3 elementos / cells	No permanente / non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. URA-ONE
661623	230 V~; 50/60 Hz	LED 4 x 1 W	200 lm - 1 h	3,6 V 1,5 Ah NiCd 3 elementos / cells	No permanente / non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. URA-ONE
661624	230 V~; 50/60 Hz	LED 4 x 1 W	350 lm - 1 h	4,8 V 1,5 Ah NiCd 4 elementos / cells	No permanente / non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. URA-ONE
661625	230 V~; 50/60 Hz	LED 4 x 2 W	500 lm - 1 h	4,8 V 2,0 Ah NiMH 4 elementos / cells	No permanente / non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. URA-ONE
661631	230 V~; 50/60 Hz	LED 4 x 0,5 W	100 lm - 1 h	2,4 V 1,5 Ah NiCd 2 elementos / cells	Permanente, posible no permanente / maintained, possible non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. URA-ONE

CERTIFICATE OF THE ENEC EUROPEAN MARK

Type reference	Rated voltage and frequency	N° lamps x rated power, type and lampholder	Rated lumen output and duration	Battery features	Additional information	General data
661632	230 V~; 50/60 Hz	LED 4 x 0,5 W	160 lm - 1 h	3,6 V 1,5 Ah NiCd 3 elementos / cells	Permanente, posible no permanente / maintained, possible non maintained; puesta en reposito remota / remote rest	Protección electrónica / electronic protection. URA-ONE
661633	230 V~; 50/60 Hz	LED 4 x 1 W	200 lm - 1 h	3,6 V 1,5 Ah NiCd 3 elementos / cells	Permanente, posible no permanente / maintained, possible non maintained; puesta en reposito remota / remote rest	Protección electrónica / electronic protection. URA-ONE
661634	230 V~; 50/60 Hz	LED 4 x 1 W	350 lm - 1 h	4,8 V 1,5 Ah NiCd 4 elementos / cells	Permanente, posible no permanente / maintained, possible non maintained; puesta en reposito remota / remote rest	Protección electrónica / electronic protection. URA-ONE
661635	230 V~; 50/60 Hz	LED 4 x 2 W	500 lm - 1 h	4,8 V 2,0 Ah NiMH 4 elementos / cells	Permanente, posible no permanente / maintained, possible non maintained; puesta en reposito remota / remote rest	Protección electrónica / electronic protection. URA-ONE

CERTIFICATE OF THE ENEC EUROPEAN MARK

Type reference	Rated voltage and frequency	N° lamps x rated power, type and lampholder	Rated lumen output and duration	Battery features	Additional information	General data
661637	120 V~; 50/60 Hz	LED 4 x 0,25 W	160 lm - 1 h	3,6 V 1,5 Ah NiCd 3 elementos / cells	No permanente / non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. URA-ONE 120VAC
661638	120 V~; 50/60 Hz	LED 4 x 1 W	350 lm - 1 h	4,8 V 1,5 Ah NiCd 4 elementos / cells	No permanente / non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. URA-ONE 120VAC
661640	230 V~; 50/60 Hz	LED 4 x 0,5 W	100 lm - 3 h	4,8 V 2,0 Ah NiMH 4 elementos / cells	Permanente, posible no permanente / maintained, possible non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. URA-ONE
661642	230 V~; 50/60 Hz	LED 4 x 1 W	200 lm - 2 h	4,8 V 2,0 Ah NiMH 4 elementos / cells	Permanente, posible no permanente / maintained, possible non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. URA-ONE
662631	230 V~; 50/60 Hz	LED 4 x 0,5 W	100 lm - 1 h	3,6 V 1,5 Ah NiCd 3 elementos / cells	Permanente, posible no permanente / maintained, possible non maintained; puesta en reposo remota / remote rest	Protección electrónica / electronic protection. URA-ONE LVS

CERTIFICATE OF THE ENEC EUROPEAN MARK

Type reference	Rated voltage and frequency	N° lamps x rated power, type and lampholder	Rated lumen output and duration	Battery features	Additional information	General data
662633	230 V~; 50/60 Hz	LED 4 x 1 W	200 lm - 1 h	4,8 V 1,5 Ah NiCd 4 elementos / cells	Permanente, posible no permanente / maintained, possible non maintained; puesta en reposito remota / remote rest	Protección electrónica / electronic protection. URA-ONE LVS
662634	230 V~; 50/60 Hz	LED 4 x 1 W	350 lm - 1 h	4,8 V 2,0 Ah NiMH 4 elementos / cells	Permanente, posible no permanente / maintained, possible non maintained; puesta en reposito remota / remote rest	Protección electrónica / electronic protection. URA-ONE LVS
662640	230 V~; 50/60 Hz	LED 4 x 0,5 W	100 lm - 3 h	4,8 V 2,0 Ah NiMH 4 elementos / cells	Permanente, posible no permanente / maintained, possible non maintained; puesta en reposito remota / remote rest	Protección electrónica / electronic protection. URA-ONE LVS
662642	230 V~; 50/60 Hz	LED 4 x 1 W	200 lm - 2 h	4,8 V 2,0 Ah NiMH 4 elementos / cells	Permanente, posible no permanente / maintained, possible non maintained; puesta en reposito remota / remote rest	Protección electrónica / electronic protection. URA-ONE LVS