



Ref. Certif. No.

ES1962-M1

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

FLUORESCENT LUMINAIRE FOR EMERGENCY LIGHTING

Name and address of the applicant

LEGRAND GROUP ESPAÑA, S.L.
CL HIERRO, 56
28850 TORREJON DE ARDOZ (Madrid - Spain)

Name and address of the manufacturer

LEGRAND FRANCE LAGORD
ZA DES GREFFIÈRES; 1, RUE EUGÈNE FREYSSINET
F17140 LAGORD (France)

Name and address of the factory

SAME AS ABOVE

Note: When more than one factory, please report on page 2

Additional Information on page 2

Ratings and principal characteristics

See Annex

Trademark (if any)

LEGRAND

Customer's Testing Facility (CTF) Stage used

-

Model / Type Ref.

See references on the Annex

Additional information (if necessary may also be reported on page 2)

Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 60598-1:2014
IEC 60598-2-22:2014

As shown in the Test Report Ref. No. which forms part of this Certificate

2017060340B1, 2019040179B1

This CB Test Certificate is issued by the National Certification Body

AENOR INTERNACIONAL S.A.U.
CI Génova, 6
ES-28004 MADRID (SPAIN)

Date: 2019-11-08


Signature: Rafael GARCÍA MEIRO
Chief Executive Officer

ANNEX TO CB CERTIFICATE N° ES1962-M1

CERTIFIED REFERENCES AND THEIR MAIN RATINGS

Product: FLUORESCENT LUMINAIRE FOR EMERGENCY LIGHTING
Trade Mark: LEGRAND

Type reference	No. lamps x rated wattage	Rated lumen output	Additional information
661120	Lamp 1 x 8 W	200 Lm	Non maintained; Ni-Cd 1,5 Ah. U33 (8W) EXPORT
661121	Lamp 1 x 8 W	200 Lm - emergency	Maintained; Ni-Cd 1,5 Ah. U33 (8W) EXPORT
661122	Lamp 2 x 8 W	200 Lm - emergency	Combined non maintained; Ni-Cd 1,5 Ah. U33 (8W) EXPORT

Rated voltage and frequency: 230 V~; 50/60 Hz

Type of lamps and lampholder: Fluorescent; lampholder G5

IP degree of protection: IP 42; IK 07

Means for power connection: Terminals

Classif. per holding surface material: Suitable for normally flammable surfaces

Protection against electric shocks (class): Class II

Limitations: -

Rated duration: 1 h