

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	HEBS Switches
Name and address of the applicant	LEGRAND FRANCE 128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY 87045 LIMOGES CEDEX - FRANCE
Name and address of the manufacturer	LEGRAND FRANCE 128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY 87045 LIMOGES CEDEX - FRANCE
Name and address of the factory	
Note: When more than one factory, please report on page 2	<input checked="" type="checkbox"/> Additional Information on page 2
Ratings and principal characteristics	See Annex
Trademark / Brand (if any)	
Customer's Testing Facility (CTF) Stage used	/
Model / Type Ref.	Series : ZLS28, ZLE16, ZLS26 References : See Annex
Additional information (if necessary may also be reported on page 2)	<input checked="" type="checkbox"/> Additional Information on page 2
A sample of the product was tested and found to be in conformity with	IEC 60669-1:1998(ed.3) +A1:1999 +A2:2006 IEC 60669-2-1:2002(ed.4) +A1:2008 IEC 60669-2-5:2013
As shown in the Test Report Ref. No. which forms part of this Certificate	162469-739593A, 162469-739593B, 159718-732704, 160795-735212

This CB Test Certificate is issued by the National Certification Body



LCIE – Laboratoire Central des Industries Electriques
33, avenue du Général Leclerc – BP8
FR 92 266 Fontenay aux Roses Cedex
www.lcie.fr

Date: 03/03/2020

Signature: 
Manager of Certification Operations

ANNEX

Name and address of the factories:**LEGRAND FRANCE**

128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY
87045 LIMOGES CEDEX - FRANCE

SPHERIS TECHNOLOGY CO, LTD.

9 SAIWEI ROAD, SHUIXI TOWN, HIGH AND NEW TECH DEVELOPMENT ZONE
338004 XINYU CITY
JIANGXI PROVINCE - CHINA



LCIE – Laboratoire Central des Industries Electriques
33, avenue du Général Leclerc – BP8
FR 92 266 Fontenay aux Roses Cedex
www.lcie.fr

Date: 03/03/2020



Signature: **Didier BOURGES**
Manager of Certification Operations

ANNEX (Continued)

REFERENCES – RATING AND MAIN CHARACTERISTICS

Mechanisms

Type reference	References	Color	Nominal characteristics	Terminals	Pattern	contact opening	Method of mounting	Specificity
ZLS28	0 648 79	white	14A 230V~ 50/60Hz	st	1	micro	flush	Cable outlet
	0 648 82	titanium						
	0 648 83	graphite						
	0 648 98	aluminium						
	0 648 63	ivory						
	0 648 47	black						
	0 648 51	pearl						
ZLE16	0 676 94	/	3V	/	6	/	/	remote switch for switch or push
ZLS26	0 648 88	/	300W 100-240V~ 50/60Hz	st	1	micro	/	micromodule switch

St : screw terminal

Characteristics of appliances

pattern number	see table
contacts opening (gap)	see table
degree of protection	IP 20
method of mounting	see table
method of installation	design A
type of terminals	see table



LCIE – Laboratoire Central des Industries Electriques
 33, avenue du Général Leclerc – BP8
 FR 92 266 Fontenay aux Roses Cedex
www.lcie.fr



Date: 03/03/2020

 Signature: **Didier BOURGES**
 Manager of Certification Operations

ANNEX (End)

Rated current (A) - rated load (VA or W) :

for 230V~

ZLS28 :

3000W incandescent lamps

3000W resistive for heating installations

for 240V~

ZLS26 :

300 W halogen lamps

60 W LED or 10 lamps

60 W fluorescent compact lamps

300 VA feromagnetic transformers for ELV halogen lamps

300 VA electronic transformers for ELV halogen lamps

Minimum current (A) - minimum load (VA or W) :

ZLS26 : 5W

Extension unit

ZLE18

0 677 23



LCIE – Laboratoire Central des Industries Electriques
33, avenue du Général Leclerc – BP8
FR 92 266 Fontenay aux Roses Cedex
www.lcie.fr

Date: 03/03/2020

Signature: **Didier BOURGES**
Manager of Certification Operations

