

AENOR

Confía

ENEC Certification Body registered under ID # 01. For further information, please consult www.enec.com

LICENCE

to use the European Mark



Licence Nr. ENEC/001139

Under the conditions given in the following pages of this document, the licence to use the ENEC Mark in conjunction with the suffix 01, as shown above, has been issued to:

LEGRAND GROUP ESPAÑA, S.L.
CL HIERRO, 56
28850 TORREJON DE ARDOZ (Madrid – España / Spain)

For the product(s):

LED luminaires for emergency lighting

Trade name(s):

LEGRAND

Complying with the following European Standards:

EN IEC 60598-1:2021; EN 60598-2-22:2014;
EN 60598-2-22:2014/A1:2020;
EN 62262:2002

Date: 2023-04-10

Signature:

A handwritten signature in blue ink, appearing to read 'Rafael García', written over a horizontal line.

Name: Rafael García
Position: Chief Executive Officer

This licence has been issued under the presumption and conditional on the fact that the licensee holds all necessary legal rights with regard to the product presented for testing and certification.

AENOR INTERNACIONAL, S.A.U.
Cl Génova, 6
28004 MADRID (Spain)

CERTIFICATE OF THE ENEC EUROPEAN MARK

Type of Product	LED LUMINAIRES FOR EMERGENCY LIGHTING
r1) Certificate n°	ENEC/001139
r2) Date of the Certificate	2023-04-10
r3) report n°	2023020064B1
r4) Name and address of the licensee	LEGRAND GROUP ESPAÑA, S.L. CL HIERRO, 56 28850 TORREJON DE ARDOZ (Madrid - España / Spain)
r5) Address of the factory	CL HIERRO, 56 28850 TORREJON DE ARDOZ (Madrid - España / Spain)
r6) European Standard	EN IEC 60598-1:2021; EN 60598-2-22:2014; EN 60598-2-22:2014/A1:2020; EN 62262:2002
r7) Type reference	See above for details
r8) Trade Mark	LEGRAND
r9) Rated voltage and frequency	230 V~; 50/60 Hz
r10) N° lamps x rated power, type and lampholder	See above for details
r11) IP degree of protection	IP42; IK 04
r12) Power supply connection means	Bornes terminals
r13) Classif. per holding surface material	Apta para superficies normalmente inflamables suitable for normally flammable surfaces
r14) Protection against electric shocks (class)	Clase class II
r15) Rated lumen output and duration	See above for details
r16) Battery features	See above for details
r17) Additional information	No permanente non maintained; puesta en reposo remota remote rest
r18) General data	See above for details
Date of expiry: 2026-06-30	This certificate supersedes certificate 007/001139, dated 2020-09-28.

CERTIFICATE OF THE ENEC EUROPEAN MARK

Type reference	N° lamps x rated power, type and lampholder	Rated lumen output and duration	Battery features	General data
061508LS	LED 2 x 0,5 W	70 lm - 1 h	NiCd 0,8 Ah	Protección electrónica electronic protection. C3 LED Standard
061510LA	LED 4 x 0,5 W	100 lm - 1 h	NiCd 1,5 Ah	Protección electrónica electronic protection. C3 LED Autotest
061510LS	LED 2 x 0,5 W	100 lm - 1 h	NiCd 0,8 Ah	Protección electrónica electronic protection. C3 LED Standard
061512LS	LED 4 x 0,5 W	160 lm - 1 h	NiCd 1,5 Ah	Protección electrónica electronic protection. C3 LED Standard
061513LA	LED 4 x 1 W	200 lm - 2 h	NiMH 2 Ah	Protección electrónica electronic protection. C3 LED Autotest
061513LS	LED 4 x 1 W	200 lm - 2 h	NiMH 2 Ah	Protección electrónica electronic protection. C3 LED Standard
061514LA	LED 4 x 1 W	200 lm - 1 h	NiCd 1,5 Ah	Protección electrónica electronic protection. C3 LED Autotest
061514LS	LED 4 x 0,5 W	200 lm - 1 h	NiCd 1,5 Ah	Protección electrónica electronic protection. C3 LED Standard
061515LA	LED 4 x 1 W	350 lm - 1 h	NiMH 2 Ah	Protección electrónica electronic protection. C3 LED Autotest
061515LS	LED 4 x 1 W	350 lm - 1 h	NiCd 1,5 Ah	Protección electrónica electronic protection. C3 LED Standard
061516LA	LED 4 x 1 W	500 lm - 1 h	NiMH 2 Ah	Protección electrónica electronic protection. C3 LED Autotest
061516LS	LED 4 x 1 W	500 lm - 1 h	NiCd 1,5 Ah	Protección electrónica electronic protection. C3 LED Standard