

IEC

IECEE

Ref. Certif. No.

FR_719447

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Fixed socket-outlet

Name and address of the applicant

LEGRAND FRANCE
128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY
87045 LIMOGES CEDEX
FRANCE

Name and address of the manufacturer

LEGRAND FRANCE
128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY
87045 LIMOGES CEDEX
FRANCE

Name and address of the factory

See Annex

Note: When more than one factory, please report on page 2

Additional Information on page 2

Ratings and principal characteristics

See Annex

Trademark / Brand (if any)



Customer's Testing Facility (CTF) Stage used

/

Model / Type Ref.

Series : CELIANE
References : See Annex

Additional information (if necessary may also be reported on page 2)

Supersedes CBTC 616166 dated 05/10/2011. Update further to the evolution of the standard(s)

Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 60884-1:2022


As shown in the Test Report Ref. No. which forms part of this Certificate

20757639-795909

This CB Test Certificate is issued by the National Certification Body



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr



Signature: Julien GAUTHIER
Certification Officer

Date: 03/07/2024

IEC

IECEE

Ref. Certif. No.

FR_719447

ANNEX

Name and address of the factories:

LEGRAND FRANCE

128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY
87045 LIMOGES CEDEX
FRANCE


LEGRAND MAGYARORSZAG VILLAMOSSAGI RENDSZEREK ZRT


IPARTELEPI UT 14 PF 10
6600 SZENTES
HUNGARY



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 03/07/2024



Signature: 
Julien GAUTHIER
Certification Officer

ANNEX
Mechanisms

Trademark	Reference	Characteristics	Specificities
LEGRAND	0 671 37	2x2P+E	Double socket-outlets

Characteristics

Standard sheet	V (CEE7)
Rated current (A) / rated voltage (V)	16A / 250V~
Degree de protection	IP20
Provision for earthing	With earthing contact
Method of connecting the cable	Rewirable
Type of terminals	Screwless type (rigid and flexible)
Number of socket-outlets	16A : 2
Degree of protection against electric shock	Normal protection
Existence of shutters	With shutters
Method of application - mounting	Flush type
Method of installation	Design A


Accessories

Reference White	Reference Titanium	Designation
0 686 47	0 689 47	Cover-plates



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
 33 avenue du Général Leclerc
 92260 Fontenay-aux-Roses, FRANCE

www.lcie.fr



Signature: **Julien GAUTHIER**
 Certification Officer

Date: 03/07/2024