



Ref. Certif. No.

**ES1953-M3**

**IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME**

**CB TEST CERTIFICATE**

Product

FLUORESCENT LUMINAIRE FOR EMERGENCY LIGHTING

Name and address of the applicant

LEGRAND GROUP ESPAÑA, S.L.  
CL HIERRO, 56  
28850 TORREJON DE ARDOZ (Madrid - Spain)

Name and address of the manufacturer

SAME AS ABOVE

Name and address of the factory

SAME AS ABOVE

Note: When more than one factory, please report on page 2

Additional Information on page 2

Ratings and principal characteristics

See Annex

Trademark (if any)

LEGRAND

Customer's Testing Facility (CTF) Stage used

-

Model / Type Ref.

See references on the Annex

Additional information (if necessary may also be reported on page 2)

Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 60598-1:2014  
IEC 60598-2-22:2014


As shown in the Test Report Ref. No. which forms part of this Certificate

2017030094B1, 2019040179B1

This CB Test Certificate is issued by the National Certification Body

AENOR INTERNACIONAL S.A.U.  
CI Génova, 6  
ES-28004 MADRID (SPAIN)

Date: 2019-11-20

  
Signature: Rafael GARCÍA MEIRO  
Chief Executive Officer

# ANNEX TO CB CERTIFICATE N° ES1953-M3

## CERTIFIED REFERENCES AND THEIR MAIN RATINGS

**Product: FLUORESCENT LUMINAIRE FOR EMERGENCY LIGHTING**  
**Trade Mark: LEGRAND**

Type reference	No. lamps x rated wattage	IP degree of protection	Rated lumen output	Rated duration	Additional information
066000	Lamp 1 x 8W	IP 42; IK 07	140 lm	1h	Non maintained; Ni-Cd 3,6 V 1,5 Ah 3 cells
066001	Lamp 1 x 8W	IP 42; IK 07	140 lm - emergency	1h	Permanente / maintained; Ni-Cd 3,6 V 1,5 Ah 3 cells
066002	Lamp 2 x 8W	IP 42; IK 07	140 lm - emergency	1h	Combined non-maintained; Ni-Cd 3,6 V 1,5 Ah 3 cells
066003	Lamp 1 x 8W	IP 42; IK 07	110 lm	3h	non maintained; Ni-Cd 6,0 V 1,5 Ah 5 cells
066004	Lamp 1 x 8W	IP 42; IK 07	110 lm - emergency	3h	Permanente / maintained; Ni-Cd 6,0 V 1,5 Ah 5 cells
066005	Lamp 2 x 8W	IP 42; IK 07	110 lm - emergency	3h	Combined non-maintained; Ni-Cd 6,0 V 1,5 Ah 5 cells

**Rated voltage and frequency:** 230 V~; 50/60 Hz

**Type of lamps and lampholder:** Fluorescent; lampholder G5

**IP degree of protection:** IP 42; IK 07

**Means for power connection:** Terminals

**Classif. per holding surface material:** Suitable for normally flammable surfaces

**Protection against electric shocks (class):** Class II

**Limitations:** -